

ART VERSION #: I


ART REVISION DATE: 11/10/2016

FINAL ART DATE: 11/XX/2016

SPEC #: A01-1116-1588 B

DIELINE #: 3241 642 95082

PART #: 3235 829477 02



PHILIPS LIGHTING USA	
Brand	PHILIPS
Product Family	LED
Shape	A19
Wattage	9.5W
Master Brand Template Ref.	3235 829477 01
SGS number	XXXXXXX
6NC #	464957
PKG PART #	3235 829477 02
DIE #	3241 642 95082
CRC #	CRC_XXXUS
Barcode No.	0 46677 46495 0
Operator(s)	ellen.e.smith@philips.com
VERSION No.	v1
Date	NOVEMBER 10, 2016
<input type="checkbox"/> Cyan <input type="checkbox"/> Magenta <input type="checkbox"/> Yellow <input type="checkbox"/> Black <input type="checkbox"/> Die	
Date Check	
<input type="checkbox"/> Check briefing Traffic	
Artwork document	
<input type="checkbox"/> Legend	<input type="checkbox"/> Number of colors
<input type="checkbox"/> 12NC	<input type="checkbox"/> Trapping/Bleed
<input type="checkbox"/> Barcode	<input type="checkbox"/> Images hires
<input type="checkbox"/> Diecut	<input type="checkbox"/> Jobsizes
Approval	
<input type="checkbox"/> QC Lithographer	
<input type="checkbox"/> Product Manager	
<input type="checkbox"/> Traffic Manager	

LIMITED WARRANTY for Consumers:
Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 5 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS YOUR SOLE REMEDY, EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW. ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

LIMITED WARRANTY for Professional, Industrial/Commercial Customers and Applications:
Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 3 years based on lamp operation of 3 hours average usage per day/7 days per week, when used as directed. Visit http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd for full details and restrictions.

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This Class B digital apparatus complies with Canadian ICES-005. For optimal performance, do not use with dimmers or 3-way fixtures. If used on a dimmer, set the dimmer to highest setting.

*At \$0.11 per kWh, this 9.5 watt, 800 lumen, LED A19 bulb uses \$15.67 of electricity over its 15,000 hour life. This is a \$83.33 savings when compared to the \$99.00 required to run a 60 watt, 800 lumen, incandescent A19 bulb over the same period. Actual savings will vary depending on cost per kWh.

**LED lifetime means the length of time (in years) until half of the LED light sources maintain at least 70% of their initial lumen output (B50L70), where the lamp is used on average 3 hours/day.

3235 829477 02
Model: 9290012632
Ordering Code: 9.5A19/LED/827-50-22/ND_SSCC_120V
Assembled in one or more of the following countries: China, Mexico
Philips Lighting North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873, USA
Questions or Comments:
1-800-555-0050 | www.philips.com



Brightness	Estimated Energy Cost
800/800/80 lumens	\$1.14/ \$0.96/ \$0.36 per year

soft white
Setting 1: Functional Light
• 2700 K
• 800 Lumens

daylight
Setting 2: Energizing Light
• 5000 K
• 800 Lumens

warm glow
Setting 3: Cozy Light
• 2200 K
• 80 Lumens

WARNINGS AND CAUTIONS:
Not suitable for use with dimmers. Not for use in totally enclosed or recessed luminaires (fixtures). This device is not intended for use with emergency exit fixtures or emergency lights. Risk of electric shock - Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +113°F (-20°C and +45°C).

PRECAUCIONES Y CUIDADOS:
No atenuable/dimable. No debe utilizarse en luminarias empotradas o totalmente cerradas (accesorios). Este dispositivo no está diseñado para usarse como iluminación de emergencia o dentro de luminarios de señalización de salida de emergencia. Riesgo de choque eléctrico - No utilizar con agua. Antes de reemplazar, apague la corriente eléctrica y enfríe la lámpara para evitar un choque eléctrico o incendio. Solo instalar en ambientes entre -4 grados F y + 113 grados F (-20 grados Centígrados y 45 grados C.)

Información sólo para el mercado Mexicano
Lámpara LED Omnidireccional A19/9.5W
Tensión Eléctrica 120V~
Frecuencia 60Hz
Corriente Eléctrica 130mA
Vida Nominal 15,000 h
Ensamblado en alguno de los siguientes países: México y/o China
Contenido 1 pieza

Importado y/o Distribuido por:
PHILIPS MEXICANA S.A DE C.V.
Av. La Palma No. 6
Col. San Fernando La Herradura
Huixquilucan Estado de México CP. 52784
R.F.C. PME-620620-EB4
Línea de Atención al Cliente
01800 508 9000 (55) 5269 9139
smartlight.mexico@philips.com
Garantía 3 años, para términos y condiciones consultar el siguiente link:
<http://www.lighting.philips.com.mx/connect/garantias.wpd>



SAVES \$83 IN ENERGY COST

LASTS 13+ YEARS**

E26 Standard MEDIUM BASE

SWITCH OFF & ON TO CHANGE COLOR SETTINGS

MEMORY FEATURE REMEMBERS PREVIOUS SETTING

Lighting Facts Per Bulb

Brightness	800/800/80 lumens
Estimated Yearly Energy Cost	\$1.14/\$0.96/\$0.36 Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use.
Life	13.7 years Based on 3 hrs/day
Color Temperature	2700K/5000K/2200K
Energy Used	9.5/8/3 watts

PROOF OF PURCHASE
9.5A19/LED/827-50-22/ND_SSCC_120V

0 46677 46495 0

UL LISTED

LISTED LED Lamp
3PM5
80CRI
2700K-5000K-2200K