ABB BALDOR RELIANCE

Customer information packet

EM2555T-4

100HP, 1780RPM, 3PH, 60HZ, 404T, 4484M, OPSB, F

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 11:01:35 AM

Specifications

Enclosure	OPSB
Frame	404T
Frame Material	Steel
Frequency	60.00 Hz
Motor Letter Type	Three Phase
Output @ Frequency	100.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
Agency Approvals	NEMA PREMIUM NEMA PREMIUM (OLD LOGO) CURUSEEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	118.000 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	95.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	118.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H

Part Detail

Revision	F
Type	AC
Mech. spec.	44E192
Base	
Status	PRD/A
Elec. spec.	44WGW390
Layout	44LYE192
Eff. date	11-19-2024
CD Diagram	CD0382
Poles	04
Leads	6#4
Proprietary	False
Created date	08-31-2017

Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 4 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	4484M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	36.97 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	2.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1780 rpm
Speed Code	Single Speed
Starting Method	Wye Start - Delta Run
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138LUA												
CAT.NO.	EM2555T-4			**P/N**				**ENCLOSURE**	OPSB			
SPEC.	44E192W390G1	**CC**	010A		**FRAME**	404T		**S/N**				
HP	100			**CLASS**	F		**HZ**	60				
RPM	1780			**PH**	3		**DES**	A				
VOLT	460				**KVA-CODE**	H		**ODE BRG**	6312	**DE BRG**	6316	
AMP	118											
RATING	40C AMB-CONT				**GREASE**	POLYREX EM						
NEMA-NOM-EFF	95.4	**PF**	83	**SER.F.**	1.15							
	50HZ 100HP 380V 139A SF1.0											
HTR-VOLTS		**HTR-AMPS**										

Accessories

Part number	Description	Multiplier
44-1402	C FACE KIT 44/404-5UC TC 6316 BRG	A8

AC Induction Motor Performance Data
Record # 66623
Typical performance - not guaranteed values

Winding: 44WGW390-R001	**Type:** 4484M	**Enclosure:** OPSB

Nameplate Data			
Rated Output (HP)			100
Volts			460
Full Load Amps			118
R.P.M.			1780
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	H
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	95.4	**Power Factor**	83
Rating - Duty			40C AMB-CONT
S.F. Amps			

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	295 LB-FT
Start Configuration	direct on line
Breakdown Torque	884 LB-FT
Pull-up Torque	375 LB-FT
Locked-rotor Torque	498 LB-FT
Starting Current	852 A
No-load Current	46.4 A
Line-line Res. @ 25ºC	0.045551 Ω
Temp. Rise @ Rated Load	47°C
Temp. Rise @ S.F. Load	57°C
Locked-rotor Power Factor	25.4
Rotor inertia	15.9 LB-FT2

Load Characteristics 460 V, 60 Hz, 100 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	46	70	79	83	85	86	84
Efficiency	92.6	95.3	95.7	95.6	95.2	94.6	95.4
Speed	1794	1789.8	1785.5	1780.7	1775.5	1769.8	1778
Line amperes	54.2	70.6	92.8	118	145	173	134


ABB Motors and Mechanical Inc.


WINDING # 44WGW390

100 HP 3 PH 60 HZ 1780 RPM 460 V 4484M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=884 PU=375 LR=498 LRA=852





44LYE192
(4454-4470) =35.22
(4472-4486) = 36.97
(44884492) = 37.97
7.42
7.43
7.25
.75 KEY
5.62 LONG
Ø 2.875
2.874
GREASER &
PIPE PLUG
(EA. END)
6 HOLES
Ø .81
12.25
1.25
13.75
6.62
16.62
Ø 16.79
16.40
1 LIFTING LUG
(EA. SIDE)
DIAGONALLY
SPACED
18.40
10.00 +.00 -.06
.66
LEAD HOLE
Ø 3.62
8.00
8.00
12.75
9.25
18.49
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT DRW FROM AUTOCAD TO SWD
REV: B
VERSION: 02
REVISED: 10:27:39 11/09/2023
TDR: 000001218972
MODEL NO. 44LYE192
REF: -
BY: USALMAZ
B
BALDOR
HORZ OPSB 404-5T, SUPER-E
44LYE192

CD0382







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.
5. FOR ACROSS–THE–LINE STARTING, USE 'RUN' CONNECTION.

CD0382

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: F	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\243	REVISED: 09:05:32 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 6 LEADS, Y START/D RUN

SH 1 of 1