


Highly dexterous and made with 48% Dyneema® bio-circular fiber,

## TEGERA® 906

Learn more

## THIN WITH BIO-CIRCULAR CUT PROTECTION

Thin and dexterous cut protection glove for fine assembly work with small sharp objects. The glove is made with 48% Dyneema® bio-circular fiber, an innovation that reduces dependence on fossil raw materials. The glove is extremely light, 18 gg, and has PU dipping for better grip. Cut resistance level B.

### CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

### FUNCTIONS

- Ultra thin
- Super soft

Dyneema®

OEKO TEX® STANDARD 100 SE 14-214 RISE



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*

## PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt

## PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

## PRIMARY AREAS OF USE

Fine assembly, Inspection work, Machine operating, Warehouse work

## PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Pulp and paper, Rubber and plastics manufacturing, Transport equipment manufacturing, Warehousing

## TYPE OF WORK

Light weight

## SPECIFICATION

**TYPE** Cut resistant gloves
**CATEGORY** Cat. II
**KNITTING GAUGE (GG)** 18
**LINING MATERIAL** Dyneema® fiber from bio-circular feedstock , Nylon, Spandex
**LENGTH** 210-250 mm
**DEXTERITY** 5
**GRIP DESIGN** Smooth finish
**COLOUR** Black
**PAIRS PER: BUNDLE/CARTON** 12/120
**DISPLAY TYPE** Bulk pack
**DIPPING** Palm-dipped
**DIPPING MATERIAL** PU
**CUFF STYLE** Knitwrist cuff
**CUFF MATERIAL** Textile
**CUT RESISTANCE (EN ISO 13997)** Cut resistance level B
**CUT RESISTANCE (EN ISO 13997) TDM:** 5.8 N
**INNER MATERIAL SPECIFICATION** UHMWPE (Ultra high molecular weight polyethylene), Nylon, Elastane
**OUTER MATERIAL SPECIFICATION** Polyurethane

## COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X41B

ANSI A2 CUT

ANSI 3 ABR

## FEATURES

Cut protection

| SIZE | | ARTICLE NUMBER | EAN |
|---|---|---|---|
| 5 | XXS | 906-5 | 7340118329703 |
| 6 | XS | 906-6 | 7340118324395 |
| 7 | S | 906-7 | 7340118324401 |
| 8 | M | 906-8 | 7340118324418 |
| 9 | L | 906-9 | 7340118324425 |
| 10 | XL | 906-10 | 7340118324371 |
| 11 | XXL | 906-11 | 7340118324388 |

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com



*All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.*