



MATERIAL LIFTS



**LIFT EASIER.
WORK SAFER.
MOVE MORE.**

OVERVIEW

Designed for versatility and safety, JET's Material Lifts give pros total control, confidence, and convenience with every lift. Industry-first features that boost safety, speed, and mobility. Engineered to eliminate cranking fatigue and risk, every detail works to make your lift safer and easier.

IDEAL FOR

- Mechanical Contractors
- HVAC Contractors
- Facility Maintenance Teams
- Electrical and Plumbing Contractors

THE JET ADVANTAGES

- **Work Anywhere, Store Anywhere:** Counterbalance Mode lets you lift flush against walls, while the tilting mast makes transport effortless and storage compact. Add in dual input winch control with a cordless drill or hand crank, plus integrated forklift pockets, and you've got unmatched versatility.
- **Performance That Doesn't Quit:** Lift up to 650 lbs. at 12, 18, or 24 feet with confidence. The heavy duty steel frame is built for demanding jobs, while stable lift performance at full extension and smooth rolling six inch casters keep your work moving forward.
- **Safety You Can Trust:** A built-in internal mast brake system, wide base footprint, and locking rear casters give you the stability and security to take on tall lifts without worry.
- **Competitive Edge:** Outperforms the competition with unmatched versatility, mobility, and safety features that come standard. Backed by JET's industry leading reputation, this lift is engineered to deliver reliability and results job after job.

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

**INDUSTRY-LEADING
SERVICE & SUPPORT**



MODES OF OPERATION



STANDARD LIFT MODE

Reliable, everyday lifting performance that delivers the stability and strength you need for a wide range of material handling tasks.



COUNTERBALANCE LIFT MODE*

Get right up against walls with ease. This mode places the legs behind the lift, providing unobstructed access in front of the forks. *Requires the use of JET Counterbalance Dolly JML-CBX.



STORAGE MODE

Save valuable floor space when the lift isn't in use. Folding legs store upright making storage simple.



TRANSIT MODE

Move the lift effortlessly across the jobsite and through doorways. The patent pending design eliminates the need to shoulder the and balance the lift. This configuration can also be useful for rack storage between jobs.

STOCK NO.	JT1-2411	JT1-2410	JT1-2409
Model No.	JML-24X	JML-18X	JML-12X
Lift Height	24'	18'	12'
Max Load Capacity	650 lbs.	650 lbs.	650 lbs.
Winch	16 Cranks per ft. w/Handle or 500 RPM Max Drill Drive (No load)	16 Cranks per ft. w/Handle or 500 RPM Max Drill Drive (No load)	16 Cranks per ft. w/Handle or 500 RPM Max Drill Drive (No load)
Weight	420 lbs.	376 lbs.	338 lbs.
Stabilizers	Yes	Yes	Yes
Internal Mast Brakes	Standard	Standard	Standard
Standard Lift Mode Dimensions (L x W x H)	5 ft. 7 in. x 6 ft. 5 in. x 7 ft. 3 in.	5 ft. 7 in. x 6 ft. 5 in. x 7 ft. 3 in.	5 ft. 7 in. x 6 ft. 5 in. x 7 ft. 3 in.
Counterbalance Lift Mode Dimensions (L x W x H)	8 ft. 8 in. x 6 ft. 5 in. x 7 ft. 3 in.	8 ft. 8 in. x 6 ft. 5 in. x 7 ft. 3 in.	8 ft. 8 in. x 6 ft. 5 in. x 7 ft. 3 in.

AVAILABLE ACCESSORIES	STOCK NO.	MODEL NO.	DETAILS
Counterbalance Assembly Dolly	JT1-2594	JML-CBX	250 lbs., Folding handle, Nesting design
Fork Extension Kit	JT1-2595	JML-FEX	Aluminum for corrosion resistance, Outside fit, Extends reach to 55 in.
Adjustable Pipe Cradle Kit	JT1-2596	JML-APC	Unique adjustable design, lays flat when not in use, Tool-free design



COUNTERBALANCE READY

Work right up against a wall with the optional counterbalance mode



DRILL DRIVE WINCH

Eliminates fatigue and improves safety



FORKLIFT POCKETS

Integrated forklift pockets for safer mobility



MINIMUM UPRIGHT STORAGE

Legs can easily be stowed vertically to save 30% in floor space



BIG WHEELS

6" casters provide smooth and reliable movement across the jobsite

SEE IT IN ACTION.

VISIT JETTOOLS.COM TO LEARN MORE.



DO MORE™