

SAFETY DATA SHEET



1. IDENTIFICATION

Product identifier

Product Name

BSI-104 BOWL BRITE PLUS

Recommended use of the chemical and restrictions on use

Recommended Use

Toilet bowl and urinal cleaner

Uses advised against

Follow the directions for use on the label when applying this product

Details of the supplier of the safety data sheet

Manufacturer Address

Best Sanitizers, Inc

PO Box 1360

Penn Valley, CA 95946

Emergency telephone number

Emergency Telephone

Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute toxicity - Inhalation (Dusts/Mists)	Category 4
Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1

Label elements

Emergency Overview

Danger

Hazard statements

Harmful if inhaled

Causes severe skin burns and eye damage



Appearance Aqueous solution

Physical state Liquid

Odor Mild

Precautionary Statements - Prevention

Use only outdoors or in a well-ventilated area

Do not breathe dusts or mists

Wash face, hands, and any exposed skin thoroughly after handling

Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

Immediately call a poison center or doctor

Specific treatment (see Section 4 on SDS)

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Immediately call a poison center or doctor

IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower. Wash contaminated clothing before reuse

IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a poison center or doctor

IF SWALLOWED: Rinse mouth. DO NOT induce vomiting

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Not Applicable

Other Information

- Toxic to aquatic life with long lasting effects

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No.	weight-%
Water	7732-18-5	78-82
Phosphoric acid	7664-38-2	13-17
Trade Secret 1	Proprietary	1-3
Trade Secret 2	Proprietary	< 1
Trade Secret 3	Proprietary	< 1
Trade Secret 4	Proprietary	< 0.5
Trade Secret 5	Proprietary	< 0.5
Ethyl Alcohol	64-17-5	< 0.5

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

First aid measures

Eye contact	Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses if present, after first 5 minutes, then continue rinsing eye. Seek immediate medical attention/advice.
Skin contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Wash contaminated clothing and shoes before reuse. For severe burns, immediate medical attention is required.
Inhalation	Remove to fresh air. Administer oxygen if breathing is difficult. Call a physician immediately.
Ingestion	Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Call a physician immediately.

Most important symptoms and effects, both acute and delayed

Symptoms See Section 11 for symptom information.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Dry chemical. Water spray (fog). Carbon dioxide (CO₂). Foam.

Unsuitable extinguishing media No information available.

Specific hazards arising from the chemical

No information available.

Hazardous combustion products Carbon monoxide. Carbon dioxide (CO₂). Phosphorus oxides.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Cool containers with flooding quantities of water until well after fire is out. Non-combustible, substance itself does not burn but may decompose upon heating to produce corrosive and/or toxic fumes.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment, and emergency procedures

Personal precautions Use personal protection recommended in Section 8. Ensure adequate ventilation, especially in confined areas.

For emergency responders Isolate area. Keep unnecessary personnel away.

Environmental precautions

Environmental precautions Prevent entry into waterways, sewers, basements, or confined areas. See Section 12 for additional ecological information.

Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so. Contain and collect spillage with non-combustible absorbent material, (e.g., sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see Section 13).
Methods for cleaning up	Collect spillage. Soak up with inert absorbent material. Sweep up and shovel into suitable containers for disposal. Following product recovery, flush area with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protection recommended in Section 8. Avoid contact with skin, eyes, or clothing. Use only in well-ventilated areas. Avoid breathing vapors or mists. Wash thoroughly after handling. Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool, and well-ventilated place. Keep from freezing.
Incompatible materials Chlorinated compounds. Cyanides. Alkali. Certain soft metals.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Phosphoric acid 7664-38-2	STEL: 3 mg/m ³ TWA: 1 mg/m ³	TWA: 1 mg/m ³ (vacated) STEL: 3 mg/m ³	IDLH: 1000 mg/m ³ TWA: 1 mg/m ³ STEL: 3 mg/m ³
Ethyl Alcohol 64-17-5	STEL: 1000 ppm	TWA: 1000 ppm TWA: 1900 mg/m ³	IDLH: 3300 ppm TWA: 1000 ppm TWA: 1900 mg/m ³

Appropriate engineering controls

Engineering Controls Showers, eyewash stations, ventilation system.

Individual protection measures, such as personal protective equipment

Eye/face protection Splash proof chemical goggles and face shield.
Skin and body protection Wear protective Neoprene™ gloves or rubber gloves. Normal work clothing (long sleeved shirt and long pants) is recommended. Apron recommended.
Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Wash face, hands, and any exposed skin thoroughly after handling. Wash contaminated clothing and shoes before reuse. Do not eat, drink, or smoke when using this product.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid	Odor	Mild
Appearance	Aqueous solution	Odor threshold	No information available
Color	Clear, Colorless	Remarks • Method	
Property	Values		
pH	1	±1 @ 21°C	
Melting point/freezing point	< -6.7 °C / < 20 °F		
Boiling point / boiling range	No information available		
Flash point	No information available		
Evaporation rate	No information available		
Flammability (solid, gas)	No information available		
Flammability Limit in Air			
Upper flammability limit:	No information available		
Lower flammability limit:	No information available		
Vapor pressure	No information available		
Vapor density	No information available		
Specific Gravity	1.1 g/cc		
Water solubility	Completely soluble		
Solubility in other solvents	No information available		
Partition coefficient	No information available		
Autoignition temperature	No information available		
Decomposition temperature	No information available		
Kinematic viscosity	No information available		
Dynamic viscosity	No information available		
Explosive properties	No information available		
Oxidizing properties	No information available		
VOC Content (%)	0.36% (0.033 lbs/gal)		

10. STABILITY AND REACTIVITY

Reactivity

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

None under normal processing.

Conditions to avoid

None known.

Incompatible materials

Chlorinated compounds. Cyanides. Alkali. Certain soft metals.

Hazardous Decomposition ProductsCarbon monoxide. Carbon dioxide (CO₂). Phosphorus oxides.**11. TOXICOLOGICAL INFORMATION****Information on likely routes of exposure****Product Information****Inhalation**

Inhalation of vapors in high concentration may cause irritation of respiratory system. Vapors may be irritating to eyes, nose, throat, and lungs.

Eye contact

Risk of serious damage to eyes. Corrosive to the eyes and may cause severe damage including blindness.

Skin Contact

Corrosive. Contact causes severe skin irritation and possible burns.

Ingestion

Harmful if swallowed. Can burn mouth, throat, and stomach. Ingestion causes burns of the upper digestive and respiratory tracts.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Water 7732-18-5	> 90 mL/kg (Rat)	-	-
Phosphoric acid 7664-38-2	= 1530 mg/kg (Rat)	= 2740 mg/kg (Rabbit)	> 850 mg/m ³ (Rat) 1 h
Trade Secret 1	= 1400 mg/kg (Rat) = 1378 mg/kg (Rat)	> 2 g/kg (Rabbit)	-
Trade Secret 2	= 426 mg/kg (Rat)	-	-
Trade Secret 3	= 238 mg/kg	= 3342 mg/kg	-
Trade Secret 4	= 238 mg/kg	= 3342 mg/kg	-
Trade Secret 5	= 84 mg/kg (Rat)	= > 1000 mg/kg (Rat)	-
Ethyl Alcohol 64-17-5	= 7060 mg/kg (Rat)	-	= 124.7 mg/L (Rat) 4 h

Information on toxicological effects**Symptoms**

No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure**Sensitization**

No information available.

Germ cell mutagenicity

No information available.

Carcinogenicity

Ethanol has been shown to be carcinogenic in long-term studies only when consumed as alcoholic beverage.

Chemical Name	ACGIH	IARC	NTP	OSHA
Ethyl Alcohol - 64-17-5	A3	-	Known	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity

No information available.

STOT - single exposure

No information available.

STOT - repeated exposure

No information available.

Aspiration hazard

No information available.

Numerical measures of toxicity - Product Information**Unknown Acute Toxicity**

0% of the mixture consists of ingredient(s) of unknown toxicity

The following values are calculated based on chapter 3.1 of the GHS document.

Oral LD50

10,200.00 mg/kg

Dermal LD50

15,448.00 mg/kg

Mist

1.42 mg/l

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Toxic to aquatic life with long lasting effects

2.002% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Fish	Crustacea
Phosphoric acid 7664-38-2	3 - 3.5: 96 h Gambusia affinis mg/L LC50	4.6: 12 h Daphnia magna mg/L EC50
Ethyl Alcohol 64-17-5	13400 - 15100: 96 h Pimephales promelas mg/L LC50 flow-through 12.0 - 16.0: 96 h Oncorhynchus mykiss mL/L LC50 static 100: 96 h Pimephales promelas mg/L LC50 static	9268 - 14221: 48 h Daphnia magna mg/L LC50 10800: 24 h Daphnia magna mg/L EC50 2: 48 h Daphnia magna mg/L EC50 Static

Persistence and degradability

No information available.

Bioaccumulation

Chemical Name	Partition coefficient
Ethyl Alcohol - 64-17-5	-0.32

Mobility

Soluble in water.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods****Disposal of wastes**

Disposal should be in accordance with applicable regional, national, and local laws and regulations.

Contaminated packaging

Dispose of in accordance with federal, state, and local regulations.

Chemical Name	California Hazardous Waste Status
Phosphoric acid - 7664-38-2	Corrosive
Ethyl Alcohol - 64-17-5	Toxic Ignitable

14. TRANSPORT INFORMATION**DOT**

UN/ID No.	1760
Proper shipping name	Corrosive liquids, n.o.s. (contains phosphoric acid)
Hazard Class	8
Packing Group	III
Emergency Response Guide Number	154

15. REGULATORY INFORMATION**International Inventories**

TSCA	Complies
DSL/NDSL	Complies
EINECS/ELINCS	Does not comply

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	No
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Phosphoric acid 7664-38-2	5000 lb.	-	-	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical Name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Phosphoric acid 7664-38-2	5000 lb.	-	RQ 5000 lb. final RQ 2270 kg final RQ

US State Regulations**California Proposition 65**

Warning! This product may contain trace amounts of 1,4-dioxane 123-91-1; Ethylene oxide 75-21-8.

Ethyl alcohol is only a considered a Proposition 65 developmental hazard when it is ingested as an alcoholic beverage

Chemical Name	California Proposition 65
Ethyl Alcohol - 64-17-5	Carcinogen Developmental

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Phosphoric acid 7664-38-2	X	X	X
Ethyl Alcohol 64-17-5	X	X	X

U.S. EPA Label Information

EPA Pesticide Registration Number Not Applicable

16. OTHER INFORMATION

NFPA	Health hazards	2	Flammability	0	Instability	0	Physical and Chemical Properties	Corrosive, Acid
HMIS	Health hazards	2	Flammability	0	Physical hazards	0	Personal protection	C (safety glasses, gloves, synthetic apron)

Prepared By Technical Department

Issue Date 17-Mar-2017

Revision Date 1-Jan-2026

Version 2

Revision Note

New information on raw ingredient has become available.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information, and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal, and release and is not to be considered a warranty or quality specification. The health hazards given on this SDS apply to this product in its concentrated form (as supplied) and may differ significantly at use dilution. The signs and symptoms of exposure apply only to negligence in handling or misuse of the concentrated product and not to the routine exposure of the diluted product under conditions of ordinary use.

End of Safety Data Sheet