

# Safety Data Sheet

## 1. Identification

<b>Product Information.</b>	S876 (112406)
<b>Product Name:</b>	Liquid Slurry
<b>Recommended Use.</b>	Professional Carpet Cleaning
<b>Uses advised against.</b>	Professional Use Only
<b>Supplier.</b>	Legend Brands Prochem 15180 Josh Wilson Road Burlington, WA 98233 E-Mail: sds@legendbrands.com 800-932-3030
<b>Emergency telephone number.</b>	INFOTRAC 1-800-535-5053 (North America) +1-352-323-3500 (International)

## 2. Hazards Identification

### GHS Classification in accordance with 29 CFR 1910.1200

Serious Eye Damage, category 1  
Skin Sensitizer, category 1

### GHS Pictograms



### Signal Word

Danger

### Unknown Acute Toxicity

19.6% of the mixture consists of ingredient(s) of unknown acute toxicity

### HAZARD STATEMENTS

May cause an allergic skin reaction.  
Causes serious eye damage.

### Precautionary Statements - Prevention.

Wear protective gloves, protective clothing, eye protection, face protection

### Precautionary Statements - Response.

If on skin: Wash with plenty of water.  
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
Immediately call a poison center or doctor.  
If skin irritation or rash occurs: Get medical advice/attention.

### Precautionary Statements - Disposal.

Dispose of contents in accordance with local, regional, national, international regulations.

## 3. Composition/Information on Ingredients

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>
TETRAPOTASSIUM PYROPHOSPHATE	7320-34-5	10-25
Decyl phenoxybenzenedisulfonic	36445-71-3	10-25
Ethoxylated Alcohol Mixture	proprietary	2.5-10
Benzenesulfonic acid,oxybis[decyl-, disodium salt	70146-13-3	2.5-10
Anionic polymers	mixture	1.0-2.5
Isopropyl alcohol	67-63-0	0.1-1.0
D-limonene	5989-27-5	0.1-1.0

The exact percentage (concentration) of composition has been withheld as a trade secret.

## 4. First-aid Measures

### Description of first-aid measures.

#### **General advice.**

Call a physician if irritation develops or persists. When symptoms persist or in all cases of doubt seek medical advice.

#### **Inhalation.**

Move to fresh air.

#### **Skin contact.**

Wash off immediately with soap and plenty of water. Remove all contaminated clothes and shoes.

#### **Eye contact.**

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician. Remove contact lenses, if present.

#### **Ingestion.**

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Gently wipe or rinse the inside of the mouth with water.

#### **Symptoms.**

See Section 2.2, Label Elements and/or Section 11, Toxicological effects.

#### **Notes to physician.**

Treat symptomatically.

## 5. Fire-fighting Measures

### Extinguishing media.

#### **Suitable extinguishing media.**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

#### **Extinguishing media which shall not be used for safety reasons.**

High volume water jet.

### Special hazards arising from the substance or mixture.

No information available.

### Advice for firefighters.

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. Accidental Release Measures

### Personal precautions, protective equipment and emergency procedures.

#### **Personal precautions.**

Avoid contact with skin, eyes and clothing. Ensure adequate ventilation, especially in confined areas. Do not breathe vapors or spray mist.

#### **Advice for emergency responders.**

Use personal protection recommended in Section 8.

### Environmental precautions.

Prevent product from entering drains. See Section 12 for additional Ecological information.

**Methods and materials for containment and cleaning up.****Methods for Containment.**

Prevent further leakage or spillage if safe to do so. Pick up and transfer to properly labeled containers.

**Methods for cleaning up.**

Use personal protective equipment as required.

**Reference to other sections.**

See section 8 for more information.

**7. Handling and Storage****Conditions for safe storage, including any incompatibilities.****Advice on safe handling.**

Handle in accordance with good industrial hygiene and safety practice.

**Hygiene measures.**

See section 7 for more information.

**Storage Conditions.**

Keep containers tightly closed in a cool, well-ventilated place.

**8. Exposure Controls/Personal Protection****Ingredients with Occupational Exposure Limits**

<u>Chemical Name</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH-TLV STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>
Isopropyl alcohol	200 ppm	400 ppm	400 ppm	N.E.

TLV = Threshold Limit Value TWA = Time Weighted Average PEL = Permissible Exposure Limit STEL = Short-Term Exposure Limit N.E. = Not Established

**Engineering Measures.**

Showers, eyewash stations, and ventilation systems.

**Personal protective equipment.****Eye/Face Protection.**

Safety glasses with side-shields.

**Skin and body protection.**

Wear suitable protective clothing.

**Respiratory protection.**

In case of insufficient ventilation wear suitable respiratory equipment.

**9. Physical and chemical properties.****Information on basic physical and chemical properties.**

Physical state	Liquid
Appearance	Clear
Color	Royal blue
Odor	Citrus
Odor Threshold	No Information
pH	9.45
Melting/freezing point., °C (°F)	No Information
Flash Point., °C (°F)	>94 (>201.20)
Boiling point/boiling range., °C (°F)	82 - 318 (179.6 - 604.4)
Evaporation rate	No Information
Explosive properties.	No Information
Vapor pressure.	No Information
Vapor density.	No Information
Specific Gravity. (g/cm <sup>3</sup> )	1.200

Water solubility.	Soluble
Partition coefficient.	No Information
Autoignition temperature., °C	No Information
Decomposition Temperature °C.	No Information
Viscosity, kinematic.	No Information

**Other information.**

Volatile organic compounds (VOC) content.	0%
Density, lb/gal	No Information

## 10. Stability and Reactivity

**Reactivity.**

Stable under normal conditions.

**Chemical stability.**

Stable under recommended storage conditions.

**Possibility of hazardous reactions.**

None known based on information supplied.

**Conditions to Avoid.**

None known.

**Incompatible Materials.**

None known based on information supplied.

**Hazardous Decomposition Products.**

None known.

## 11. Toxicological Information

**Information on toxicological effects.****Acute toxicity.****Product Information**

No Information

The following values are calculated based on chapter 3.1 of the GHS document.

ATEmix (oral)	4,650.0 mg/kg
ATEmix (dermal)	7,358.4 mg/kg

**Component Information.**

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>LD50 Oral</u>	<u>LD50 Dermal</u>	<u>LC50 Inhalation</u>
7320-34-5	TETRAPOTASSIUM PYROPHOSPHATE	> 2980 mg/kg	> 7940 mg/kg	6 mg/l (Dust)
36445-71-3	Decyl phenoxybenzenedisulfonic	900 mg/kg Rat	>1000 mg/kg Rabbit	N.I.
proprietary mixture	Ethoxylated Alcohol Mixture Anionic polymers	1000-2000 mg/kg 11000	2000 mg/kg 2000	No information (Dust) 1417 (Vapor)
67-63-0	Isopropyl alcohol	5840 mg/kg ( Rat )	13,900 mg/kg ( Rabbit )	N.I.
5989-27-5	D-limonene	5200 mg/kg, 4400 mg/kg Rat	>5000 mg/kg Rabbit	N.I.

N.I. = No Information

**Skin corrosion/irritation.**

SKIN IRRITANT.

**Eye damage/irritation.**

No Information

**Respiratory or skin sensitization.**

No Information

**Ingestion.**

No Information

**Germ cell mutagenicity.**

No Information

**Carcinogenicity.**

No Information

**CAS-No.**

5989-27-5

**Chemical Name**

D-limonene

**IARC**

IARC Group 3

**NTP**

-

**OSHA**

-

**Reproductive toxicity.**

No Information

**Specific target organ systemic toxicity (single exposure).**

No Information

**Specific target organ systemic toxicity (repeated exposure).**

No Information

**Aspiration hazard.**

No Information

**Primary Route(s) of Entry**

No Information

**12. Ecological Information****Toxicity.**

19.6% of the mixture consists of ingredient(s) of unknown aquatic toxicity

**Ecotoxicity effects.**

Chemical Name	Toxicity to algae	Toxicity to fish	Toxicity to daphnia and other aquatic invertebrates
TETRAPOTASSIUM PYROPHOSPHATE 7320-34-5	-	LC50 96 h Oncorhynchus mykiss >100 mg/L	EC50 48 h water flea >100 mg/L
Isopropyl alcohol 67-63-0	EC50 96 h Desmodemus subspicatus >1000 mg/L, EC50 72 h Desmodemus subspicatus >1000 mg/L	LC50 96 h Pimephales promelas 9640 mg/L, LC50 96 h Pimephales promelas 11130 mg/L, LC50 96 h Lepomis macrochirus >1400000 µg/L	EC50 48 h Daphnia magna 13299 mg/L
D-limonene 5989-27-5	-	LC50 96 h Pimephales promelas 0.619 - 0.796 mg/L, LC50 96 h Oncorhynchus mykiss 35 mg/L	-

**Persistence and degradability.**

No data are available on the product itself.

**Bioaccumulative potential.**

Discharge into the environment must be avoided.

**CAS-No.**

67-63-0

5989-27-5

**Chemical Name**

Isopropyl alcohol

D-limonene

**log POW**

0.05

4.38

**Mobility in soil.**

No information

**Other adverse effects.**

No information

**13. Disposal Considerations****Waste Disposal Guidance.**

Disposal should be in accordance with applicable regional, national and local laws and regulations.

**14. Transport Information****DOT**

No Information

**IMDG****Hazard Class:** Not regulated**IATA**

Not regulated

**15. Regulatory Information****International Inventories:**

<b>TSCA</b>	Complies
<b>DSL</b>	Complies
<b>DSL/NDSL</b>	Complies
<b>EINECS/ELINCS</b>	-
<b>ENCS</b>	-
<b>IECSC</b>	-
<b>KECI</b>	-
<b>PICCS</b>	-
<b>AIIC</b>	-
<b>NZIoC</b>	-
<b>TCSI</b>	
<b>TSCA</b>	United States Toxic Substances Control Act Section 8(b) Inventory.
<b>DSL</b>	Canadian Domestic Substances List.
<b>DSL/NDSL</b>	Canadian Domestic Substances List/Canadian Non-Domestic Substances List
<b>EINECS/ELINCS</b>	European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances.
<b>ENCS</b>	Japan Existing and New Chemical Substances.
<b>IECSC</b>	China Inventory of Existing Chemical Substances.
<b>KECL</b>	Korean Existing and Evaluated Chemical Substances.
<b>PICCS</b>	Philippines Inventory of Chemicals and Chemical Substances.
<b>AIIC</b>	Australian Inventory of Chemical Substances.
<b>NZIoC</b>	New Zealand Inventory of Chemicals.
<b>TCSI</b>	Taiwan Chemical Substance Inventory

**U.S. Federal Regulations:****SARA SECTION 313:**

This product does not contain any chemicals that are subject to the reporting requirements of SARA 313.

**TOXIC SUBSTANCES CONTROL ACT 12(b):**

This product does not contain any chemicals that are subject to the reporting requirements of TSCA 12(b).

**ADDITIONAL INFORMATION**

Additional Information - Sxn 15: No Information

**CALIFORNIA PROPOSITION 65 CARCINOGENS****WARNING**

Warning: The following ingredients present in the product are known to the state of California to cause Cancer:

<b><u>Chemical Name</u></b>	<b><u>CAS-No.</u></b>
Ethylene oxide	75-21-8
1,4-DIOXANE	123-91-1

**CALIFORNIA PROPOSITION 65 REPRODUCTIVE TOXINS****WARNING**

Warning: The following ingredients present in the product are known to the state of California to cause birth defects, or other reproductive hazards.

**Chemical Name**

Ethylene oxide

**CAS-No.**

75-21-8

**16. Other Information**

**Revision Date:** 9/29/2025 **Supersedes Date:** 6/24/2024

**Reason for revision:** Substance and/or Product Properties Changed in Section(s):  
01 - Product Information  
08 - Exposure Controls/Personal Protection  
Revision Statement(s) Changed

**Datasheet produced by:** Regulatory Department

**HMIS Ratings:**

<b>Health:</b>	3	<b>Flammability:</b>	1	<b>Physical Hazard:</b>	0	<b>Personal Protection:</b>	B
----------------	---	----------------------	---	-------------------------	---	-----------------------------	---

**NFPA Ratings:**

<b>Health:</b>	3	<b>Flammability:</b>	1	<b>Instability:</b>	0	<b>Physical &amp; Chemical:</b>	-
----------------	---	----------------------	---	---------------------	---	---------------------------------	---

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

The information provided on this SDS is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.