



Fibre-Metal®

Type II Vented, Industrial Climbing Helmet with HDPE Shell, 8-Point Textile Suspension, Wheel Ratchet Adjustment and a 4-Point Chinstrap

- Liquid Crystal Polymer (LCP) yarn in the six strap, eight-point suspension disperses force transferred from the shell to the user
- Non-Newtonian foam combined with a traditional EPS foam liner
- One-way moisture transfer and fast-dry chin strap help elevate user comfort in high-temperature work environments
- Compatible with a wide range of safety accessories such as a welding helmet, visor, faceshield, UV shade, earmuffs, or task light
- ANSI/CSA Certified, Type II, Class C



Technical Data

Color	Yellow, Multi, Dark Blue, Gray, Red, Black, White, Orange, Brown, Green
Sizes Available	OS
Packaging	Bagged Each
Packed	8/Case
Case Dimensions (in)	22.44 x 17.72 x 19.69
Case Weight (lbs)	14.99
Country of Origin	China
Shell Material	HDPE
Shell	Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Chin Strap	4-Point Polyester
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified

Performance Data

ANSI Type	Type II
Electrical Class	Class C

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
CSH11011	Black	OS	00883940436913		00883940436913
CSH11012	Brown	OS	00883940436906		00883940436906
CSH11071	Dark Blue	OS	00883940436876		00883940436876
CSH11009	Gray	OS	00883940436845		00883940436845
CSH11004	Green	OS	00883940436869		00883940436869
CSH11080	Multi	OS	00883940436920		00883940436920
CSH11046	Orange	OS	00883940436883		00883940436883
CSH11015	Red	OS	00883940436890		00883940436890
CSH11001	White	OS	00883940436838		00883940436838
CSH11002	Yellow	OS	00883940436852		00883940436852