



TEGERA® 8832R

Learn more

WHEN THE WORK IS SHARP, COLD AND WET

Glove with cold protection in combination with high cut protection (Level D). Latex, Knuckle dipped with latex, for cold and wet environments. 10 gg and CRF cut resistance technology. The glove is durable, soft and warm and the Latex-dipping with a sandy finish provides a good grip. Perfect for all-round work in in cold and wet environments.

CHARACTERISTICS

- High level of protection
- Flexible
- Good grip
- Comfortable
- Warm

FUNCTIONS

- Withstands contact heat up to 250°C
- Water repellent palm and knuckle

CRF®

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt, Contact with moisture, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Cold environments, Wet environments, Dirty environments

PRIMARY AREAS OF USE

Building and construction, Construction, Machine driving

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Facility management services, Basic metals manufacturing, Transportation and logistics, Building and construction, Mining and quarrying, Warehousing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cold insulation gloves, Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
LINING Winter-lined
KNITTING GAUGE (GG) 10, 13
LINING MATERIAL Acrylic, CRF® Technology, HPPE, Stainless steel fibre yarn
LENGTH 250-285mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/72
DISPLAY TYPE Hangtag with euro slot
DIPPING 3/4 dipped
DIPPING MATERIAL Latex
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 21.9 N
INNER MATERIAL SPECIFICATION Acrylic, HPPE (High performance polyethylene), Stainless steel fibre yarn, Polyester
OUTER MATERIAL SPECIFICATION Natural latex

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2X42D

EN 407:2020 (No flame protection) X2XXXX

EN 511:2006 12X

ANSI A4 CUT

ANSI 3 ABR

ANSI 3 PUN

Contact heat rating valid for palm area only

FEATURES

Cut protection

Warm lining

Water repellent

SIZE		ARTICLE NUMBER	EAN
7	S	8832R-7	7340118388465
8	M	8832R-8	7340118388618
9	L	8832R-9	7340118388823
10	XL	8832R-10	7340118389004
11	XXL	8832R-11	7340118389189
12	3XL	8832R-12	7340118416250

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.