PRODUCT INFORMATION PACKET

Model No: 145TTFR16122
Catalog No: FX01BK010
FLEX-IN-1™ General Purpose Motor, 1 & 1 HP, 3 Ph, 60 & 50 Hz, 208-230/460 & 190/380 V, 1200 & 1000 RPM, 145TC Frame, TEFC



Regal and LEESON are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2026 Regal Rexnord Corporation, All Rights Reserved. MC017097E

Nameplate Specifications


Phase	3	Output HP	1 & 1 Hp
Output KW	0.75 & 0.75 kW	Voltage	208-230/460 & 190/380 V
Speed	1160 & 945 rpm	Service Factor	1.15 & 1.00
Frame	145TC	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostat	Efficiency	82.5 & 80 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	3.8-3.8/1.9 & 4.2/2.1 A	Power Factor	60
Duty	Continuous	Insulation Class	F
Design Code	A	KVA Code	L
Drive End Bearing Size	6205	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		


Technical Specifications


Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	6	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Bolt-on Base
Motor Orientation	Horizontal Or Up Or Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ¿ F2/F3 CAPABLE
Inverter Load	CONSTANT 10:1		
Outline Drawing	OL56100912-001	Connection Drawing	CDTD113

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/08/2026

Uncontrolled Copy









NOTES:
1)REPOSITIONAL BASE CAN BE REMOVED FOR C-FACE MOUNTING OR REPOSITIONED TO 12:00 OR 3:00 FACING SHAFT END OF MOTOR FOR NEMA F-2 OR F-3 CONDUIT BOX LOCATION.

PLUGGED BASE MOUNTING HOLES FOR REPOSITONING BASE @12:00 OR 3:00





DRAWING REVISION: B	REVISION BY: MP	REV DATE/© DATE: 03/06/2024
REQUEST NUMBER: ECR-0231732	APPROVED BY: PVR	DATE: 03/06/2024
REQUEST NUMBER DESCRIPTION: UPDATED DWG. AS PER ECR.		

COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±0.5°
.XX	±0.02	[±0.5]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY: PS	Regal Rexnord — Regal Beloit America, Inc.
DATE: 08/28/2023	
APPROVED BY: PVR	DESCRIPTION: OUTLINE
DATE: 08/28/2023	56-140FR,TEFC, C-FACE, BOLT-ON
REFERENCE: OL56100871	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: C — DRAWING NUMBER: OL56100912-001 — SHEET: 1 OF3

Uncontrolled Copy



NOTES:
1)REPOSITIONAL BASE CAN BE REMOVED FOR C-FACE MOUNTING OR REPOSITIONED TO 12:00 OR 9:00 FACING SHAFT END OF MOTOR FOR NEMA F-1 OR F-3 CONDUIT BOX LOCATION.

DRAWING REVISION: B	REVISION BY: MP	REV DATE/© DATE: 03/06/2024
REQUEST NUMBER: ECR-0231732	APPROVED BY: PVR	DATE: 03/06/2024
REQUEST NUMBER DESCRIPTION: UPDATED DWG. AS PER ECR.		

COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


TOLERANCES (EXCEPT AS NOTED):


DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±0.5°
.XX	±0.02	[±0.5]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	


REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY


DRAWN BY: PS	Regal Rexnord — Regal Beloit America, Inc.
DATE: 08/28/2023	
APPROVED BY: PVR	DESCRIPTION: OUTLINE
DATE: 08/28/2023	56-140FR,TEFC, C-FACE, BOLT-ON
REFERENCE: OL56100871	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: C — DRAWING NUMBER: OL56100912-001 — SHEET: 2 OF3


Uncontrolled Copy











NOTES:
1)REPOSITIONAL BASE CAN BE REMOVED FOR
C-FACE MOUNTING OR REPOSITIONED TO 3:00 OR 9:00 FACING SHAFT
END OF MOTOR FOR NEMA F-1 OR F-2 CONDUIT BOX LOCATION

DRAWING REVISION: B	REVISION BY: MP	REV DATE/© DATE: 03/06/2024	
REQUEST NUMBER: ECR-0231732	APPROVED BY: PVR	DATE: 03/06/2024	
REQUEST NUMBER DESCRIPTION: UPDATED DWG. AS PER ECR.			

COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.


TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±0.5°
.XX	±0.02	[±0.5]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY: PS	Regal Rexnord — Regal Beloit America, Inc.
DATE: 08/28/2023	
APPROVED BY: PVR	DESCRIPTION: OUTLINE
DATE: 08/28/2023	56-140FR,TEFC, C-FACE, BOLT-ON
REFERENCE: OL56100871	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: C — DRAWING NUMBER: OL56100912-001 — SHEET: 3 OF3

Uncontrolled Copy




VIEW OF TERMINAL END

NOTES:

1. TO REVERSE ROTATION, INTERCHANGE ANY TWO LINE CONNECTIONS TO L1, L2, OR L3.
2. CONNECTION DIAGRAM-NAMEPLATE DD10042-002.

CCW LOW VOLTAGE

001



CCW HIGH VOLTAGE

002

DRAWING REVISION: D	REVISION BY: KHADHAR	DATE: 12/05/2018
ECO: ECO-0157853	APPROVED BY: CD	DATE: 12/05/2018
ECO DESCRIPTION: UPDATED CONNECTION DIAGRAM NAMEPLATE NUM.		

COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES UNLESS OTHERWISE SPECIFIED:

DEC.	INCH	mm	ANGLE
.X	±0.1	[±2.5]	±0.5°
.XX	±0.01	[±0.25]	
XXX	±0.005	[±0.127]	
.XXXX	±0.0005	[±0.0127]	

REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.076/.381]
CORNER FILLETS: .02 [.51]
MACHINED SURFACES: 125 INCH / 3.2 mm
mm SHOWN IN [BRACKETS]

DRAWN BY: G. RODRIGUEZ	Regal Beloit America, Inc.
DATE: 25-01-2016	
APPROVED BY: E.VILLA	DESCRIPTION: CONN DIAGRAM-EXTERNAL
DATE: 25-01-2016	
REFERENCE: EE7308T	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: CDTD113 / SHEET: 1 OF 1

EC Declaration of Conformity

The undersigned representing
the manufacturer:

Regal Beloit America
1946 West Cook Road
Fort Wayne, IN 46818

and the authorized representative
established within the Community:

Regal Beloit Italy
Via Modena, 18
24040 Ciserano(BG) - Italy

are committed to providing customers with products that comply with applicable regulations and international protocols to which they are subject, including the requirements of the European Parliament Directive on the Harmonization of the laws relating to electrical equipment designed for use within certain voltage limits (2014/35/EU).

Regal Beloit America declares that the following product(s), to which this declaration relates, are in conformity with the relevant sections of the EC standards listed below.

This statement supersedes any statements previously issued pertaining to the product(s) listed below and is subject to change without notice.

Model No : 145TTFR16122

(Model No. may contain prefix and/or suffix characters)

Catalog No : FX01BK010

Rework No : N/A

Directives :

Low Voltage Directive 2014/35/EU

Harmonized Standards Used :

EN 60034-1: 2010 (IEC 60034-1: 2010)
EN 60034-5: 2001/A1:2007 (IEC 60034-5: 2000/A1:2006)

Authorized Representative:

Zach Stauffer
Vice President, Engineering

Authorized Representative in the Community:

Stefano Casiraghi
Technology Director, Engineering

Created on 07/08/2025

CE 25