

SAFETY DATA SHEET



Issuing Date: 02-Jan-2024

Revision date 12-Dec-2024

Revision Number 2.01

1. IDENTIFICATION

Product Name	Gain Original Scent Laundry Detergent
Product Identifier	21057844_RET_NG
Product Type:	Finished Product - Retail
Recommended use	Laundry Care.
Restrictions on use	Use only as directed on label.
Manufacturer	PROCTER & GAMBLE - Fabric and Home Care Division Ivorydale Technical Centre 5299 Spring Grove Avenue Cincinnati, Ohio 45217-1087 USA Procter & Gamble Inc.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-331-3774
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

"Consumer Products", as defined by the US Consumer Product Safety Act and which are used as intended (typical consumer duration and frequency), are exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200). This SDS is being provided as a courtesy to help assist in the safe handling and proper use of the product.

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Hazard category

Acute toxicity - Oral
Eye Damage / Irritation
Signal word

Category 4
Category 2B
Warning

Hazard statements

Harmful if swallowed
Causes eye irritation

Hazard pictograms



Precautionary Statements

Keep container tightly closed
 Keep away from heat/sparks/open flames/hot surfaces. — No smoking
 Wash hands thoroughly after handling

Precautionary Statements - Response

In case of fire: Use water, CO₂, dry chemical, or foam for extinction
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention

Precautionary Statements - Storage Store in a well-ventilated place. Keep cool

Precautionary Statements - Disposal Dispose of contents/container to an approved waste disposal plant.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical name	Synonyms	Trade Secret	CAS No.	Weight-%
C14-15 Pareth-n	C14-15 Pareth-7	No	68951-67-7	5 - 10
MEA-C10-13 Alkyl Benzenesulfonate	Benzenesulfonic acid, mono-C10-16-alkyl derivs., compds. with ethanolamine/Benzene sulfonic acid, mono-C10-13-alkyl derivs., compds. with ethanolamine	No	68910-32-7	5 - 10
Propylene Glycol	Propylene Glycol	No	57-55-6	0.5 - 1.5

Additional information

Actual substance concentrations fall within the ranges stated. Maximum values do not necessarily represent the values present in the formula.

4. FIRST AID MEASURES

Description of first aid measures**Eye contact**

Rinse with plenty of water. Get medical attention immediately if irritation persists. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Skin contact

Rinse with plenty of water. Call a physician if irritation develops and persists.

Ingestion

Rinse mouth. Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur. IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

Inhalation

Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed

May cause eye irritation

Indication of any immediate medical attention and special treatment needed**Notes to Physician**

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media	Dry chemical, CO ₂ , alcohol-resistant foam or water spray. Dry chemical. Alcohol resistant foam. Carbon dioxide (CO ₂).
Unsuitable Extinguishing Media	Do not use a solid water stream as it may scatter and spread fire.
Special Hazard	Fumes may catch fire.
Special protective equipment for fire-fighters	As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.
Special Provisions	None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Use personal protective equipment as required. Do not get in eyes, on skin, or on clothing.
Advice for emergency responders	Use personal protective equipment as required.
Environmental precautions	Do not discharge product into natural waters without pre-treatment or adequate dilution

Methods and material for containment and cleaning up

Methods for containment	Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling	Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children. Keep away from open flames, hot surfaces and sources of ignition.
--------------------------------	---

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions	Keep away from open flames, hot surfaces and sources of ignition. Store away from other materials.
Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Store in a cool/low-temperature, well-ventilated, dry place away from heat and ignition sources.
Incompatible products	None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines	No exposure limits noted for ingredient(s).
----------------------------	---

No relevant exposure guidelines for other ingredients

Appropriate engineering controls

Engineering Measures

Distribution and Workplace settings:

Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Manufacturing Sites:

Not relevant

Personal protective equipment

Eye Protection

Distribution and Workplace settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Manufacturing Sites:

Wear safety glasses with side shields (or goggles)

No special protective equipment required

Hand Protection

Distribution and Workplace settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection

Distribution and Workplace settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution and Workplace settings:

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of inadequate ventilation wear respiratory protection

Hygiene Measures

Manufacturing Sites:

Wash hands thoroughly after handling

Distribution and Workplace settings:

Do not eat, drink or smoke when using this product

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state	Liquid
Appearance	green Liquid
Color	No information available
Odor	Perfumes
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks</u>
pH	8.25 - 8.95	
Melting point / freezing point	No information available	
Initial boiling point and boiling range	100 °C / 212 °F	
Flash point	No Flash to Boiling (NFTB)	
Evaporation rate	No information available	
Flammability	No information available	

Flammability Limit in Air

Upper flammability or explosive limits No information available

Lower flammability or explosive limits No information available

Vapor pressure No information available

Relative vapor density No information available

Relative density No information available

Water solubility completely soluble

Partition coefficient No information available

Autoignition temperature No information available

Decomposition temperature No information available

Viscosity No information available

VOC Content (%) Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity None under normal use conditions.

Stability Stable under normal conditions.

Hazardous polymerization Hazardous polymerization does not occur.

Hazardous Reactions None under normal processing.

Conditions to Avoid Keep away from open flames, hot surfaces and sources of ignition.

Incompatible Materials None in particular.

Hazardous decomposition products None under normal use conditions.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation No known effect.

Skin contact No known effect.

Ingestion May be harmful if swallowed. Harmful if swallowed.

Eye contact Irritating to eyes. Avoid contact with eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity May be harmful if swallowed.

Skin corrosion/irritation No known effect.

Serious eye damage/eye irritation Irritating to eyes.

Skin sensitization No known effect.

Respiratory sensitization No known effect.

Germ cell mutagenicity No known effect.

Reproductive toxicity No known effect.

Developmental toxicity No known effect.

STOT - single exposure No known effect.

STOT - repeated exposure No known effect.

Aspiration hazard No known effect.

Carcinogenicity No known effect.

Component Information

Chemical name	CAS No.	Oral LD50	Dermal LD50	Inhalation LC50
C14-15 Pareth-n	68951-67-7	2000 mg/kg (RAT)	5000 mg/kg (Rat)	-
MEA-C10-13 Alkyl Benzenesulfonate	68910-32-7	1089 mg/kg (RAT)	5001 mg/kg (RABBIT)	-

Propylene Glycol	57-55-6	22000 mg/kg (RAT)	5001 mg/kg (RABBIT)	50 mg/L (RAT)
------------------	---------	-------------------	---------------------	---------------

12. ECOLOGICAL INFORMATION

ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from Residues/Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.
California Hazardous Waste Codes (non-household setting)	331

14. TRANSPORT INFORMATION

<u>DOT</u>	Not regulated
<u>IMDG</u>	Not regulated
<u>IATA</u>	Not regulated

15. REGULATORY INFORMATION

U.S. FEDERAL REGULATIONS

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

U.S. State Regulations (RTK)

Chemical name	CAS No.	New Jersey
Propylene Glycol	57-55-6	X

Chemical name	CAS No.	Pennsylvania
Propylene Glycol	57-55-6	X

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

International Inventories**United States**

All intentionally-added components of this product(s) are listed on the US TSCA Inventory

Canada

This product is in compliance with CEPA for import by P&G

Legend

United States Toxic Substances Control Act Section 8(b) Inventory (TSCA)

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

Issuing Date: 02-Jan-2024

Revision date 12-Dec-2024

Disclaimer.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet