



H-x810 - Transition Fittings - Unions - Press

H-x810W Series

Forged DZR Brass Union


Lead-Free

Certifications

Certified to NSF/ANSI/CAN 61 & 372 - IAPMO/ANSI/CAN Z1117



Size (in)	Item#	Weight (lbs)	CTN Qty	Case Qty	A	B	C	D		
Press Union x Press									200 PSI CWP Max	200°F Max
1/2"	H-88102W	0.26	10	100	0.50	0.50	1.29	2.60		
1/2" x 3/4"	H-88103W-R	0.28	10	100	0.75	0.50	1.29	2.79		
3/4"	H-88103W	0.43	10	80	0.75	0.75	1.58	3.05		
3/4" x 1"	I-88104W-R	0.44	10	80	1.00	0.75	1.58	3.07		
1"	H-88104W	0.57	10	60	1.00	1.00	1.97	3.17		
Press x F1807 PEX Union									200 PSI CWP Max	180°F Max
NSF/ANSI 14, CSA B137.5, IGC 319										
1/2"	H-18102W	0.34	30	120	0.50	0.50	1.42	2.85		
3/4"	H-18103W	0.49	30	120	0.75	0.75	1.69	3.01		
1"	H-18104W	0.66	24	48	1.00	1.00	2.00	3.13		
Press x F1960 PEX Union									200 PSI CWP Max	180°F Max
NSF/ANSI 14, CSA B137.5, IGC 319										
1/2"	H-38102W	0.35	30	120	0.50	0.50	1.42	2.93		
3/4"	H-38103W	0.52	30	120	0.75	0.75	1.69	3.33		
1"	H-38104W	0.73	24	48	1.00	1.00	2.00	3.50		



NO.	DESCRIPTION	MATERIAL
1	Locking Nut	Brass
2	Fitting End	Lead-Free DZR Brass
3	Clamp Ring	Stainless Steel
4	Gasket	EPDM
5	O-Ring	EPDM
6	Fitting Union	Lead-Free DZR Brass
7	O-Ring	EPDM

Specifications: Designed for use with water, oil, glycol mix in residential or commercial plumbing and heating systems. EPDM o-rings for press ends. PEX ends are in accordance with the referenced ASTM specification; refer to tubing manufacturer for installation instructions.

