ABB BALDOR RELIANCE

Customer information packet

EHM4104T-5

30HP, 1770RPM, 3PH, 60HZ, 286T, 1056M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:28:38 AM

Specifications

Enclosure	TEFC
Frame	286T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR
	CSA
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 575.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	29.0 a
Insulation Class	F

Part Detail

Revision	AA
Type	AC
Mech. spec.	10H756
Base	
Status	PRD/A
Elec. spec.	10WGY759
Layout	10LYH756
Eff. date	07-10-2024
CD Diagram	CD0006
Poles	04
Leads	3#10
Proprietary	False
Created date	12-12-2011

Inverter Code	Inverter Ready
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1056M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	27.76 IN
Power Factor	83
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.875 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Mounting Provisions Only
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	NONE (OLD)
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2138L												
CAT.NO.	EHM4104T-5		**P/N**			**ENCLOSURE**	TEFC					
SPEC.	10H756Y759G1	**CC**	010A	**FRAME**	286T	**S/N**						
HP	30		**CLASS**	F	**HZ**	60						
RPM	1770		**PH**	3	**DES**	A						
VOLT	575				**KVA-CODE**	G	**ODE BRG**	6309	**DE BRG**	6311		
AMP	29											
RATING	40C AMB-CONT			**GREASE**	POLYREX EM							
NEMA-NOM-EFF	93.6	**PF**	83	**SER.F.**	1.15							
	SFA 32.9											
HTR-VOLTS		**HTR-AMPS**										

AC Induction Motor Performance Data
Record # 30991
Typical performance - not guaranteed values

Winding: 10WGY759-R001	**Type:** 1056M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			30	**Full Load Torque**	89.2 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			29	**Breakdown Torque**	255 LB-FT
R.P.M.			1770	**Pull-up Torque**	120 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	136 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	177 A
Service Factor (S.F.)			1.15	**No-load Current**	11.5 A
NEMA Nom. Eff.	93.6	**Power Factor**	83	**Line-line Res. @ 25ºC**	0.375 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	58°C
S.F. Amps				**Temp. Rise @ S.F. Load**	71°C
				Locked-rotor Power Factor	32
				Rotor inertia	4.45 LB-FT2

Load Characteristics 575 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	47	69	77	84	84	83	84
Efficiency	90.9	93.9	94.4	94	92.9	92.5	93.4
Speed	1794	1786	1780	1773	1764	1754	1768
Line amperes	13.3	17.6	23.4	28.5	35.9	43.6	32.9


ABB Motors and Mechanical Inc.


WINDING # 10WGY759

30 HP 3 PH 60 HZ 1770 RPM 575 V 1056M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=255 PU=120 LR=136 LRA=177





10LYH756
(1028-1076) = 27.26
12.88
4.25
4.13
.50 KEY
3.25 LONG
Ø 1.875
1.874
8 HOLES
Ø .53
9.50
9.50
.92
11.00
4.63
12.84
DRAIN FITTING
(EA. END)
15.30
13.12
7.33
50°
50°
2.70
3 HOLES
5-40 TAP THRU
ON Ø 2.783 B.C.
(PLUG WITH
84XN0540J08)
14.44
7.00 +.00 -.06
2 HOLES
6-32 TAP THRU
Ø 2.783 B.C.
(PLUG WITH
84XN0632J08)
LEAD HOLE
Ø 2.00
5.50
5.50
10.57
6.38
12.75
PLUGS
(EA. END)
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: ADD 6-32 TAP HOLE CALLOUT
REV: F
VERSION: 06
REVISED: 10:50:14 04/10/2024
TDR: 000001227383
MODEL NO. 10LYH756
REF: -
BY: ENSTEK0
B
BALDOR
HORZ TEFC 284-6T HVAC MOTOR W/DUAL SH GND MTG
10LYH756


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1