ABB BALDOR RELIANCE

Customer information packet

XL050545A

.5HP, 1725RPM, 1PH, 60HZ, 56, 3424L, XPFC, F1, N
Class - CLI GP C,D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 11:10:10 AM

Specifications

Enclosure	XPFC
Frame	56
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP C,D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	115.0 V @ 60 HZ
	208.0 V @ 60 HZ
Agency Approvals	CSA
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.700 A @ 230.0 V
	3.900 A @ 208.0 V
	7.400 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	64.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater

Part Detail

Revision	D
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	34WGW369
Layout	34LY6864
Eff. date	01-13-2025
CD Diagram	CD0565
Poles	04
Leads	6#18,1#16 #4TH
Proprietary	False
Created date	04-21-2021

High Voltage Full Load Amps	3.7 a
Insulation Class	B
Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3424L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.22 IN
Power Factor	66
Product Family	Hazardous Location Motor
Pulley Face Code	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	Automatic Thermal Overload
Winding Thermal 1 Location	EP
Winding Thermal 2	None

Nameplate

NP0301XPSL							
NO.			**CC**				
SER.							
SPEC.	34-0000-0420						
CAT.NO.	XL050545A						
HP	.5		**T. CODE**	T3C			
VOLTS	115/208-230						
AMPS	7.4/3.9-3.7						
RPM	1725 34WGW369						
HZ	60	**PH**	1	**CL**	B		
SER.F.	1.00	**DES**	N	**CODE**	J		
RATING	40C AMB-CONT						
FRAME	56		**NEMA-NOM-EFF**	64			
		PF	66				
BLANK	NEMA MG-1 PART 5, IP54						

AC Induction Motor Performance Data
Record # 48773
Typical performance - not guaranteed values

Winding: 34WGW369-R001	**Type:** 3424L	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			.5
Volts			115/208-230
Full Load Amps			7.4/3.9-3.7
R.P.M.			1725
Hz	60	**Phase**	1
NEMA Design Code	N	**KVA Code**	J
Service Factor (S.F.)			1
NEMA Nom. Eff.	64	**Power Factor**	66
Rating - Duty			40C AMB-CONT

115 V, 60 Hz: Low Voltage Connection	
Full Load Torque	1.5 LB-FT
Start Configuration	direct on line
Breakdown Torque	4.4 LB-FT
Pull-up Torque	4 LB-FT
Locked-rotor Torque	5.1 LB-FT
Starting Current	38.8 A
No-load Current	5.62 A
Line-line Res. @ 25ºC	0.913 Ω A Ph 2.88 Ω B Ph
Temp. Rise @ Rated Load	61°C
Locked-rotor Power Factor	89.3
Rotor inertia	0.057 LB-FT2

Load Characteristics 115 V, 60 Hz, 0.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	37	48	59	67	74	79
Efficiency	38.9	55.3	62.3	64.9	65.3	63.8
Speed	1781	1768	1753	1736	1717	1696
Line amperes	5.78	6.12	6.62	7.38	8.26	9.38


ABB Motors and Mechanical Inc.

WINDING # 34WGW369

0.5 HP 1 PH 60 HZ 1725 RPM 115 V 3424L


TORQUES(LB-FT): PO=4.4 PU=4 LR=5.1 LRA=38.8

Typical performance - not guaranteed values.



11/5/2026 ACPERF, record # 48773

34LY6864



FRONT END DETAIL

PULLEY END DETAIL

CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION


REV. DESC: LOAD TO SOLIDWORKS - REV F			
REV: G	VERSION: 07	REVISED: 03:04:45 12/16/2022	TDR: 000001201165
34LY6864	MODEL NO. 34LY6864		REF: -
	BY: ENFRAJ0		

BALDOR - RELIANCE®

HORZ X34L 56 XPFC, CL-I GP-C&D, CL-II GP-F&G, .75 NPT

34LY6864

CD0565




	LINE A	LINE B	JOIN	JOIN
HIGH STD	1	4	2,3,8	J,5
HIGH OPP	1	4	2,3,5	J.8
LOW STD	1,3,8	4	–	2,J,5
LOW OPP	1,3,5	4	–	2,J,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CONNECTIONS FOR TWO–TERMINAL THERMAL



CD0565

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: C	BY: JLP	REVISED: 04/08/99 3:25	TDR: 0178636
CD0565		FILE: AAA00014311	MDL: –
		MTL: –	

BALDOR ELECTRIC Co.

TYPE L, DV, REV, THERMAL, 7 LD, 34XP