



<b>EAN:</b>	4013288107992	<b>Size:</b>	281x26x26 mm
<b>Part number:</b>	05008009001	<b>Weight:</b>	35 g
<b>Article number:</b>	335	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Slotted screwdriver -electrician's blade
- Multi-component Kraftform handle for fast and ergonomic screwdriving
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Chrome-plated

Premium Kraftform Plus screwdriver with electrician's blade. Multi-component Kraftform Plus handle for comfortable ergonomic screwdriving, avoiding blisters and calluses. Hard handle zones for high working speeds, while soft handle zones guarantee a high torque transfer. Take it easy tool finder with colour coding by profile and size stamping - for quick and easy identification of the required tool. The hexagonal anti-roll protection avoids screwdrivers from rolling away annoyingly at the workplace.



**Web link**

<https://www.wera.de/en/05008009001>

Wera - 335

05008009001 - 4013288107992

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

**Lasertip prevents slipping out**



Kraftform Plus screwdrivers - ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Lasertip**




A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

**Reduced contact pressure**



Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

**Take it easy Tool Finder**



Screwdrivers with Take it easy tool finder: colour coding according to profile and size stamp.

**Kraftform**



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design - has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as the 1960s. After a long development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.

**Prevents hand injuries**



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

**Rapid hand repositioning**










The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Web link  
<https://www.wera.de/en/05008009001>

Wera - 335  
 05008009001 - 4013288107992

Wera Werkzeuge GmbH  
 Korzter Straße 21-25  
 D-42349 Wuppertal  
 Tel: +49 (0)2 02 / 40 45-0  
 E-Mail: info@wera.de

## Further versions in this product family:

	 mm	 mm	 mm	 mm	 mm	 inch	 inch
05008006001 <sup>1)</sup>	0.4	2.0	60	70	2.5	5/64"	2 3/8"
05110000001 <sup>1)</sup>	0.4	2.5	60	70	2.5	3/32"	2 3/8"
05008007001 <sup>1)</sup>	0.4	2.5	75	70	2.5	3/32"	3"
05110001001 <sup>1)</sup>	0.5	3.0	80	81	3.0	1/8"	3 1/8"
05008008001 <sup>1)</sup>	0.5	3.0	150	81	3.0	1/8"	6"
<b>05008009001<sup>1)</sup></b>	<b>0.5</b>	<b>3.0</b>	<b>200</b>	<b>81</b>	<b>3.0</b>	<b>1/8"</b>	<b>8"</b>
05008015001 <sup>1)</sup>	0.6	3.5	100	81	3.5	9/64"	4"
05110002001 <sup>1)</sup>	0.6	3.5	125	81	3.5	9/64"	5"
05110003001 <sup>1)</sup>	0.6	3.5	200	81	3.5	9/64"	8"
05110004001	0.8	4.0	100	98	4.0	5/32"	4"
05110005001	0.8	4.0	150	98	4.0	5/32"	6"
05110006001	0.8	4.0	200	98	4.0	5/32"	8"
05008027001 <sup>1)</sup>	0.8	4.0	300	98	4.0	5/32"	12"
05110007001	1.0	5.5	125	98	5.5	7/32"	5"
05008055001	1.0	5.5	150	98	5.5	7/32"	6"
05110008001	1.0	5.5	200	98	5.5	7/32"	8"
05008060001 <sup>1)</sup>	1.0	5.5	300	98	5.5	7/32"	12"
05008061001	1.2	6.0	100	105	6.0	15/64"	4"

1) Without Lasertip

## Web link

<https://www.wera.de/en/05008009001>

Wera - 335

05008009001 - 4013288107992

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de