

**TYPE**  
**ILSCONS**


**Features**

- Spade configuration
- Funnel wire entry
- Manufactured from high strength copper alloy
- Electro-tin plated
- Brazed barrel
- UL Listed

**Benefits**

- Same benefit as the fork configuration, but with the added benefit of sides that are able to lie flat against barrier portion of terminal blocks
- Smooth wire insertion into barrel
- Offers maximum conductivity
- Provides low contact resistance
- Stronger crimp connection that will not split open, prevents wire pull out
- Ensures reliability for copper conductor

**A1**



Catalog Number	Wire Range	Stud Size	Dimensions - in. (mm)		Installation Tool ILST-22K	Package Quantity
			L	W		
BSBR-18-4-P50	18-22	4	0.630 (16.0)	0.224 (5.7)	Die Set D1322	50
BSBR-18-6-P50	18-22	6	0.630 (16.0)	0.283 (7.2)	Die Set D1322	50
BSBR-18-8-P50	18-22	8	0.630 (16.0)	0.319 (8.1)	Die Set D1322	50
BSBR-18-10-P50	18-22	10	0.630 (16.0)	0.374 (9.5)	Die Set D1322	50
BSBR-14-6-P50	14-16	6	0.630 (16.0)	0.283 (7.2)	Die Set D1322	50
BSBR-14-8-P50	14-16	8	0.630 (16.0)	0.319 (8.1)	Die Set D1322	50
BSBR-14-10-P50	14-16	10	0.630 (16.0)	0.366 (9.3)	Die Set D1322	50
BSBR-14-14-P50	14-16	1/4	0.630 (16.0)	0.366 (9.3)	Die Set D1322	50
BSBR-10-6-P50	10-12	6	0.728 (18.5)	0.327 (8.3)	Die Set D1322	50
BSBR-10-8-P50	10-12	8	0.720 (18.3)	0.327 (8.3)	Die Set D1322	50
BSBR-10-10-P50	10-12	10	0.720 (18.3)	0.354 (9.0)	Die Set D1322	50
BSBR-10-14-P50	10-12	1/4	0.965 (24.5)	0.472 (12.0)	Die Set D1322	50
BSBR-10-516-P50	10-12	5/16	0.925 (23.5)	0.551 (14.0)	Die Set D1322	50

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)  
Tested to UL 486A/B, UL File E6207