

Rigid/intermediate grade conduit fittings

Conduit clamps, straps, hangers

CABLE AND CONDUIT HANGERS – STEEL

Certifications and compliances:

- UL Listed

With Bolt



Rigid fittings

Cat. #	Conduit sizes		Unit qty.	Wt. lbs. per 100
	EMT	Rigid		
0B	1/2"	3/8" and 1/2"	100	6
1B	3/4"	3/4"	100	6
2B	1"	1"	100	8
2 1/2 B	1 1/4"	-	100	10
3 B	1 1/2"	1 1/4"	100	11
4 B	-	1 1/2"	100	16
5 B	2"	2"	50	23
6 B	2 1/2"	2 1/2"	50	29
7 B	3"	3"	25	31
8 B	3 1/2"	3 1/2"	10	38
9 B	4"	4"	10	38

CABLE AND CONDUIT HANGERS – STEEL

Applications:

- Used to provide mechanical support to conduit and raceway systems

Certifications and compliances:

- UL Listed
- cUL Listed

With extruded hole and bolt



Cat. #	Description	Unit qty.	Wt. lbs. per 100
0BX	3/8 and 1/2 RGD 1/2 EMT	100	6
1BX	3/4 RGD 3/4 EMT	100	7
2BX	1 RGD 1 EMT	100	11
2 1/2BX	1 1/4 EMT	100	10
3BX	1 1/4 RGD 1 1/2 EMT	100	13
4BX	1 1/2 RGD	100	16
5BX	2 RGD 2 EMT	50	17

BEAM CLAMPS/INSULATOR SUPPORTS – MALLEABLE IRON

Standard finish:

- Zinc plated


UL File No. E-184283



Cat. #	Base size	Jaw opening	Max. wt. support	Tapped holes	Unit qty.	Wt. lbs. per 100
528	3/4"	5/8"	50	10 - 24	25	14
529	3/4"	5/8"	50	1/2" - 20	25	13
530	1"	3/4"	60	10 - 24	25	23
531	1"	3/4"	100	1/4" - 20	25	24
532	1 1/2"	7/4"	80	3/8" - 18	50	47
533	2"	7/8"	100	3/8" - 16	25	81
534	2 1/2"	7/8"	200	1/2" - 13	25	155

Dimensions (in inches):

Cat. #	A	B	C	Max. beam thickness
528	1.10	1.23	0.56	1/2"
529	1.10	1.25	0.57	1/2"
530	1.37	1.37	0.67	5/8"
531	1.25	1.39	0.69	5/8"
532	1.47	1.57	0.91	7/8"
533	1.75	1.82	1.12	1"
534	2.28	2.15	1.04	1"



BEAM CLAMPS/INSULATOR SUPPORTS – STEEL



Cat. #	Base Size	Jaw Opening	Tapped Holes	Unit qty.	Wt. lbs. per 100
529 S	3/4"	5/8"	1/4" - 20	50	13