

**SAFETY DATA SHEET****Oil Eater® GRAFFITI & PAINT SCUFF REMOVER**

In compliance with International Regulations: GHS -SDS

Effective Date: April 2025

Federal regulations: CFR 29 and 42 State: Illinois Public Act 83-240
Applicable Items: AOD3234101, AOD5534104**1. Identification****Product Name:** Oil Eater Graffiti Remover **Revision Date:** 8/24/2024
Supersedes Date: None**Recommended Use:** Graffiti Removal**Manufacturer:**
Kafko International, Ltd
3555 Howard St
Skokie, IL 60076**Emergency Telephone:** Chemtrec (800) 424-9300**2. Hazards Identification****Classification**Acute Toxicity (Oral) - Category 4
Eye Irritation - Category 2B

Symbol(s) of Product

Signal Word Warning:**GHS Hazard Statements:**H302: Harmful if swallowed.
H320: Causes eye irritation.**Precautionary Statements:**

P264: Wash hands thoroughly after handling.

P280: Wear protective gloves and eye protection.

P270: Do not eat, drink, or smoke when using this product.

P301+P312: IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell.

P330: Rinse mouth.

P331: Do NOT induce vomiting.

P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313: If eye irritation persists: Get medical advice/attention.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES	CAS Number	% WT Range
Benzyl Alcohol	100-51-6	10 - 25
Ethylene Glycol Mono Butyl Ether	111-76-2	2 - 4
Triethanolamine	102-71-6	1 - 2

4. First-Aid Measures

First Aid - Eye Contact: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

First Aid - Skin Contact: Flush skin with plenty of water for at least 15 minutes while removing clothing. Get medical attention immediately. Wash clothing separately before reuse.

First Aid - Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

First Aid - Ingestion: If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cups of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. Do not induce vomiting unless advised by a physician. Call nearest Poison Control Center or Physician

5. Fire-Fighting Measures

immediately.

EXTINGUISHING MEDIA: Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog Unusual Fire and Explosion Hazards: Keep containers tightly closed.

Special Fire Fighting Procedures: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred. Containers can rupture and release highly toxic material if exposed to heat. Substance is non-combustible but reacts with many metals to form explosive hydrogen gas. Special Fire and Explosion Hazard (Combustible Dust): Not a combustible dust.

6. Accidental Release Measures

Steps to Be Taken If Material Is Released or Spilled: Avoid runoff into sewers and waterways. Provide ventilation and approach spill from upwind using proper personal protective equipment as indicated in Section 8. Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

Handling: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

Storage: Store in a dry, well ventilated place. Keep container tightly closed when not in use. **Advice on Safe Handling of Combustible Dust:** No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL- TWA	OSHA PEL- CEILING
Benzyl Alcohol	100-51-6	25.0	N.E.	N.E.	N.E.	N.E.

PERSONAL PROTECTION

Engineering Controls: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

Respiratory Protection: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

Skin Protection: Use impervious gloves to prevent skin contact and absorption of this material through the skin. **Eye Protection:** Use safety eyewear designed to protect against splash of liquids.

Other Protective Equipment: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

Hygienic Practices: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance:	White Opaque		
Physical State:	Liquid		
Odor:	Mild – Typical		
Specific Gravity:	1.02		
pH:	8.0 – 9.0		
Freeze Point:	Not Determined		
VOC %	280 g/L		
Boiling Range, °C:	ND	Explosive Limits, vol%:	ND
Flammability:	Does not Support Combustion	Flash Point, °C:	ND
Evaporation Rate:	Slower than Ether		
(See "Other information" Section for abbreviation legend)			

10. Stability and Reactivity

Conditions to Avoid: Avoid excess heat.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalis. Product slowly corrodes copper, aluminum, zinc, and galvanized surfaces.

Hazardous Decomposition: When heated to decomposition, it emits acrid smoke and irritating fumes.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

Effects of Overexposure - Eye Contact: Causes eye irritation. Irritating, and may injure eye tissue if not removed promptly. High vapor concentrations can irritate eyes, nose and respiratory passages.

Effects of Overexposure - Skin Contact: Substance may be a mild irritant to those with dermal sensitivity.

Effects of Overexposure - Inhalation: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs.

Effects of Overexposure - Ingestion: Harmful if swallowed. Do not induce vomiting. Rinse mouth with water. Seek medical attention immediately.

Effects of Overexposure - Chronic Hazards: No Information

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
100-51-6	Benzyl Alcohol	1230 mg/kg Rat	2000 mg/kg Rabbit	11 mg/L Rat

12. Ecological Information

Ecological Information: No ecotoxicity data was found for this product.

13. Disposal Information

Disposal: Dispose of material in accordance to local, state, and federal regulations and ordinances. RCRA Hazardous Waste: This material, when discarded or disposed of, could be a hazardous waste according to federal regulations (40 CFR 261) due to the characteristic of corrosivity (D002). Check state and local regulations for disposal requirements. Chemical additions, processing or otherwise altering this material may make the waste management information presented in this SDS incomplete, inaccurate, or otherwise inappropriate.

14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:
CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Acute Toxicity (any route of exposure), Serious eye damage or eye irritation

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical Name **CAS-No.**

Glycol Ether Monobutyl Ether 111-76-2

Toxic Substances Control Act This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information

HMIS RATINGS

Health: 2* **Flammability:** 0 **Physical Hazard:** 0 **Personal Protection:** B

NFPA RATINGS

Health: 2 **Flammability:** 0 **Instability:** 0

Volatile Organic Compounds: 285 g/L

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.