



SAFETY DATA SHEET

1. Identification

Important information	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
Product identifier	3ED71Series
Other means of identification	None.
Recommended use	Inkjet printing
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
Telephone	650-857-1501
HP Inc. health effects line (Toll-free within the US)	1-800-457-4209
(Direct)	1-760-710-0048
HP Inc. Customer Care Line	
(Toll-free within the US)	1-800-474-6836
(Direct)	1-208-323-2551
Email:	sustainability@hp.com

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	Not available.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Hazard(s) not otherwise classified (HNOC)	Complete toxicity data are not available for this specific formulation. Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions. Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

Supplemental information

This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012). 2-pyrrolidone: OSHA Hazard Communication Standard cut-off value, Reproductive toxicity Category 1B, fertility or the unborn child 3%. Mixture classification threshold based on data related to developmental toxicity in animals. No adverse effects on sexual function or damage to fertility have been observed in an animal study. See Section 11.

3. Composition/information on ingredients**Substances**

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	60-70
Hydroxy alkylated lactam*		Proprietary*	<15
Substituted diol*		Proprietary*	<7.5
Black Pigment		Proprietary	<5
2-pyrrolidone		616-45-5	<3.0

Composition comments

This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).
Carbon black is present only in a bound form in this preparation.

2-pyrrolidone: OSHA Hazard Communication Standard cut-off value 3%. Mixture classification threshold based on data related to developmental toxicity in animals. No adverse effects on sexual function or damage to fertility have been observed in an animal study. See Section 11.

*Proprietary

4. First-aid measures

Inhalation	Move to fresh air. If symptoms persist, get medical attention.
Skin contact	Wash affected areas thoroughly with mild soap and water. If irritation persists get medical attention.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Ingestion	If ingestion of a large amount does occur, seek medical attention.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	CO2, water, dry chemical, or foam
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Not applicable.
Special protective equipment and precautions for firefighters	Not available.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate personal protective equipment.
Methods and materials for containment and cleaning up	Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.
Environmental precautions	Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling	Avoid contact with skin, eyes and clothing.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Black Pigment	PEL	3.5 mg/m3

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Black Pigment	TWA	3 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Black Pigment	TWA	0.1 mg/m3

Biological limit values No biological exposure limits noted for the ingredient(s).

Exposure guidelines Exposure limits have not been established for this product.

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

Eye/face protection Not available.

Skin protection

Hand protection Not available.

Other Use personal protective equipment to minimize exposure to skin and eye.

Respiratory protection Not available.

Thermal hazards Not available.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Form Not available.

Color Black.

Odor Not available.

Odor threshold Not available.

pH 9.2

Melting point/freezing point Not available.

Initial boiling point and boiling range Not determined

Flash point >230.0 °F (>110.0 °C) Pensky-Martens Closed Cup

Evaporation rate Not determined

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Explosive limit - lower (%) Not determined

Explosive limit - upper (%) Not available.

Vapor density >1 (air=1)

Vapor density >1 (air=1)

Solubility(ies)

Solubility (water) Soluble in water

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not determined

Decomposition temperature Not available.

Viscosity Not available.

Other information	For other VOC regulatory data/information see Section 15.
Density	1.06 g/cm ³
Flammability	Not flammable according to GHS Hazard Classification Criteria.
Oxidizing properties	Not determined
Particle size	Not applicable.
Specific gravity	1 - 1.1
VOC	<240 g/l

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under recommended storage conditions.
Possibility of hazardous reactions	Will not occur.
Conditions to avoid	Not available.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons. hydrogen fluoride, fluorinated hydrocarbons

11. Toxicological information

Information on likely routes of exposure

Inhalation	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
Skin contact	Contact with skin may result in mild irritation.
Eye contact	Contact with eyes may result in mild irritation.
Ingestion	Ingestion is not a likely route of exposure.

Symptoms related to the physical, chemical and toxicological characteristics	Not available.
---	----------------

Information on toxicological effects

Acute toxicity	Based on available data, the classification criteria are not met.
-----------------------	---

Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Acute		
Oral		
LD50	Rat	> 5000 mg/kg
Black Pigment		
Acute		
Oral		
LD50	Rat	> 10000 mg/kg

Skin corrosion/irritation	Based on available data, the classification criteria are not met. Non irritant in rabbit (OECD 404)
----------------------------------	--

Serious eye damage/eye irritation	Based on available data, the classification criteria are not met. Not classified as an irritant according to, OECD 405.
--	--

Respiratory or skin sensitization

Respiratory sensitization	Based on available data, the classification criteria are not met.
Skin sensitization	Based on available data, the classification criteria are not met.

Germ cell mutagenicity	Based on available data, the classification criteria are not met.
-------------------------------	---

Carcinogenicity	Based on available data, the classification criteria are not met.
------------------------	---

Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity	Based on available data, the classification criteria are not met. 2-pyrrolidone: This component showed developmental effects only at high doses that were toxic to pregnant test animals (OECD Testing Guideline 414: Prenatal Developmental Toxicity Study). Uptake by people of small doses is not expected to cause developmental toxicity. This component has not caused adverse effects on sexual function or damage to fertility in an animal study (OECD Testing Guideline 443: Extended One-Generation Reproductive Toxicity Study).
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.

12. Ecological information

Aquatic toxicity Not expected to be harmful to aquatic organisms.

Ecotoxicity

Product	Species	Test Results
3ED71Series		
Aquatic		
<i>Acute</i>		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) > 750 mg/l, 96 hours
Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Aquatic		
<i>Acute</i>		
Crustacea	EC50	Water flea (<i>Daphnia pulex</i>) 13.21 mg/l, 48 hours

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Partition coefficient n-octanol / water (log Kow)

2-pyrrolidone -0.85

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies.
Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations.

HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

UN number Not regulated as dangerous goods.

UN proper shipping name Not Regulated

Transport hazard class(es)

Class Not assigned.

Subsidiary risk -

Packing group Not assigned.
Environmental hazards
Marine pollutant No
Special precautions for user Not assigned.

IATA

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned
Subsidiary risk -
Packing group Not assigned
Environmental hazards No
Special precautions for user Not assigned

IMDG

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned.
Subsidiary risk -
Packing group Not assigned.
Transport hazard class(es)
Marine pollutant No
EmS Not assigned.
Special precautions for user Not assigned.

ADR

UN number Not regulated as dangerous goods.
UN proper shipping name Not Regulated
Transport hazard class(es)
Class Not assigned
Subsidiary risk -
Hazard No. (ADR) Not assigned
Tunnel restriction code Not assigned
Packing group Not assigned
Environmental hazards No
Soecial precautions for user Not assigned

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

Transport in bulk according to Annex II of MARPOL73/78 and the IBC code: Not applicable.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.

Toxic Substances Control Act (TSCA)

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

Not regulated.

Other information

VOC content (less water, less exempt compounds) = < 958 g/L (U.S. requirement, not for emissions)

VOC data based on formulation (Organic compounds minus solids)

Contains a short-chain, partially fluorinated substituted glycol at <0.1%.

Regulatory information

HP complies with chemical regulatory requirements in chemical substance notification laws, where applicable. All chemical substances are notified or exempt from notification or listed in the inventory as existing substances in the following countries: US (TSCA), Canada (DSL/NDSL), Australia (AICIS), Japan (ISHL, ENCS), Philippines (PICCS), New Zealand (NZIoC) and China (IECSC). For guidance on importation and/or additional requirements for registration schemes such as EAEU, EU, South Korea, Turkey, UK, India and Taiwan, please contact the Sustainability and Compliance Center (sustainability@hp.com).

Clean Air Act (CAA)

No intentionally added HAP substances.

16. Other information, including date of preparation or last revision

Issue date

29-Jun-2022

Revision date

01-Jul-2024

Version

04

Other information

This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

Disclaimer

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

Revision information

3. Composition / Information on Ingredients: Disclosure Overrides
15. Regulatory Information: Regulatory Information
Regulatory information: Other information

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
Acute Tox.	Acute toxicity
Aquatic Acute	Short-term (acute) aquatic hazard
Aquatic Chronic	Long-term (chronic) aquatic hazard
Asp. Tox.	Aspiration hazard
Carc.	Carcinogenicity
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
Eye Dam.	Serious eye damage
Eye Irrit.	Eye Irritation
Flam. Liq.	Flammable liquids
Flam. Sol.	Flammable solids
Lact.	Effects on or via lactation
Muta.	Germ cell mutagenicity
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
Ox. Liq.	Oxidising liquids
Ozone	Hazardous to the ozone layer
PEL	Permissible Exposure Limit
Press. Gas	Gases under pressure
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
Repr.	Reproductive toxicity
Resp. Sens.	Respiratory sensitization
SARA	Superfund Amendments and Reauthorization Act of 1986
Skin Corr.	Skin corrosion
Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitization
STEL	Short-Term Exposure Limit
STOT RE	Specific target organ toxicity - repeated exposure
STOT SE	Specific target organ toxicity - single exposure
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds