

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

SECTION 1. IDENTIFICATION

Product name : AJAX ULTRA DISHWASHING HAND LIQUID LEMON
B02902620041

Product code : 200000068204

Manufacturer or supplier's details

Company name of supplier : Colgate-Palmolive Co
300 Park Avenue
New York, NY 10022

Telephone : US: Consumer Affairs - 1-800-468-6502

Emergency telephone number : For emergencies involving spill, leak, fire, exposure or accident call CHEMTREC (24hr) at (800) 424-9300 or (703) 527-3887.

Global-CHEMTREC- +1 703-741-5970

Recommended use of the chemical and restrictions on use

Recommended use : dishwashing liquid

SECTION 2. HAZARDS IDENTIFICATION

GHS classification in accordance with the OSHA Hazard Communication Standard (29 CFR 1910.1200)

Eye irritation : Category 2A

GHS label elements

Hazard pictograms :



Signal word : Warning

Hazard statements : H319 Causes serious eye irritation.

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version 1.0	Revision Date: 05/22/2023	SDS Number: 660000018810	Date of last issue: - Date of first issue: 05/22/2023
----------------	------------------------------	-----------------------------	----------------------------------------------------------

Precautionary statements : **Prevention:**
 P264 Wash skin thoroughly after handling.
 P280 Wear eye protection/ face protection.

Response:
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P337 + P313 If eye irritation persists: Get medical advice/ attention.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Components

Chemical name	CAS-No.	Concentration (% w/w)
Sodium C10-16 Alketh-2 Sulfate	68585-34-2	>= 5 - < 10
Lauramidopropylamine Oxide	61792-31-2	>= 1 - < 5

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
 Show this safety data sheet to the doctor in attendance.
 Do not leave the victim unattended.

If inhaled : If unconscious, place in recovery position and seek medical advice.
 If symptoms persist, call a physician.

In case of skin contact : If skin irritation persists, call a physician.
 If on skin, rinse well with water.
 If on clothes, remove clothes.

In case of eye contact : Immediately flush eye(s) with plenty of water.
 Remove contact lenses.
 Protect unharmed eye.
 Keep eye wide open while rinsing.
 If eye irritation persists, consult a specialist.

If swallowed : Keep respiratory tract clear.
 Never give anything by mouth to an unconscious person.
 If symptoms persist, call a physician.

Most important symptoms and effects, both acute and delayed : Causes serious eye irritation.

Notes to physician : Treat symptomatically.



AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : No hazardous combustion products are known
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
- Environmental precautions : Prevent product from entering drains.
Prevent further leakage or spillage if safe to do so.
If the product contaminates rivers and lakes or drains inform respective authorities.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

- Advice on protection against fire and explosion : Normal measures for preventive fire protection.
- Advice on safe handling : Do not breathe vapours/dust.
Avoid contact with skin and eyes.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Dispose of rinse water in accordance with local and national regulations.



AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Electrical installations / working materials must comply with the technological safety standards.

Further information on storage stability : No decomposition if stored and applied as directed.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

Personal protective equipment

Respiratory protection : No personal respiratory protective equipment normally required.

Hand protection

Remarks : The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection : Eye wash bottle with pure water
Tightly fitting safety goggles
Wear face-shield and protective suit for abnormal processing problems.

Skin and body protection : Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures : When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Colour : yellow

Odour : No data available

pH : 7.10

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

Melting point/range : No data available

Boiling point/boiling range : No data available

Flash point : No data available

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : No data available

Relative vapour density : No data available

Density :
No data available

Solubility(ies)
Solubility in other solvents : No data available

Partition coefficient: n-octanol/water : No data available

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, kinematic : No data available

Particle size : No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : No decomposition if stored and applied as directed.

Chemical stability : No decomposition if stored and applied as directed.

Possibility of hazardous reactions : No decomposition if stored and applied as directed.

Conditions to avoid : No data available

Incompatible materials : Not applicable



AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

SECTION 11. TOXICOLOGICAL INFORMATION

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity : Acute toxicity estimate: > 5,000 mg/kg
Method: Calculation method

Components:

Sodium C10-16 Alketh-2 Sulfate:

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Method: No information available.

Acute inhalation toxicity : Remarks: No data available

Acute dermal toxicity : Remarks: No data available

Lauramidopropylamine Oxide:

Acute oral toxicity : Acute toxicity estimate: 500 mg/kg

Acute inhalation toxicity : Remarks: No data available

Acute dermal toxicity : LC50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 402

Skin corrosion/irritation

Not classified based on available information.

Components:

Sodium C10-16 Alketh-2 Sulfate:

Result : Severe skin irritation

Lauramidopropylamine Oxide:

Result : Severe skin irritation

Serious eye damage/eye irritation

Causes serious eye irritation.

Components:

Sodium C10-16 Alketh-2 Sulfate:

Result : Irritation to eyes, reversing within 21 days

Lauramidopropylamine Oxide:

Result : Irreversible effects on the eye

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

Respiratory or skin sensitisation**Skin sensitisation**

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:**Sodium C10-16 Alketh-2 Sulfate:**

Exposure routes : Inhalation
Remarks : No data available

Exposure routes : Dermal
Remarks : No data available

Lauramidopropylamine Oxide:

Exposure routes : Inhalation
Remarks : No data available

Exposure routes : Dermal
Species : Guinea pig
Method : OECD Test Guideline 406
Result : Does not cause skin sensitisation.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

Further information

Product:

Remarks : This product has not been tested as a whole. However, this formula was reviewed by expert toxicologists in the Product Safety Assurance Department of Colgate-Palmolive and is determined to be safe for its intended use. This review has taken into consideration available safety-related information including information on individual ingredients, similar formulas and potential ingredient interactions. This review is a component of the hazard determination used to prepare the statements in Section 2 of the SDS.

SECTION 12. ECOLOGICAL INFORMATION

The product has not been tested as a whole for environmental toxicity. However, environmental information on the ingredients in this product have been reviewed by the Environmental Occupational Health and Safety group of Colgate-Palmolive and determined to have an acceptable environmental profile. This evaluation is based on available information on individual ingredients, interactions of ingredients, and similar ingredients. Biodegradability claims are supported by data on ingredients (i.e., surfactants are biodegradable).

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : The product should not be allowed to enter drains, water courses or the soil.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Send to a licensed waste management company.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

SECTION 14. TRANSPORT INFORMATION

DOT :

Not regulated

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

TDG :
Not regulated

IATA :
Not regulated

IMDG :
Not regulated
IMDG EmS Number :Not applicable.

ADR :
Not regulated

SECTION 15. REGULATORY INFORMATION

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

Listed substances in the product are at low enough levels to not be expected to exceed the RQ

SARA 302 Extremely Hazardous Substances Threshold Planning Quantity

This material does not contain any components with a section 302 EHS TPQ.

SARA 311/312 Hazards : Serious eye damage or eye irritation

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 112 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

AJAX ULTRA DISHWASHING HAND LIQUID LEMON

This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	05/22/2023	660000018810	Date of first issue: 05/22/2023

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 111 SOCM1 Intermediate or Final VOC's (40 CFR 60.489).

Clean Water Act

The following Hazardous Substances are listed under the U.S. CleanWater Act, Section 311, Table 116.4A:

SULFURIC ACID 7664-93-9

The following Hazardous Chemicals are listed under the U.S. CleanWater Act, Section 311, Table 117.3:

SULFURIC ACID 7664-93-9

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

This product does not contain any priority pollutants related to the U.S. Clean Water Act

US State Regulations

Massachusetts Right To Know

WATER	7732-18-5
Sodium Chloride	7647-14-5
SULFURIC ACID	7664-93-9

Pennsylvania Right To Know

WATER	7732-18-5
Sodium C10-16 Alketh-2 Sulfate	68585-34-2
SODIUM SULFATE	7757-82-6

The components of this product are reported in the following inventories:

TSCA : All ingredients in this product are listed on the TSCA Inventory or are not required to be listed on the TSCA Inventory.

TSCA list

No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

SECTION 16. OTHER INFORMATION

Full text of other abbreviations

AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport

AJAX ULTRA DISHWASHING HAND LIQUID LEMON


This industrial Safety Data Sheet is not intended for consumers and does not address consumer use of the product. For information regarding consumer applications of this product, refer to the product label.

Version 1.0	Revision Date: 05/22/2023	SDS Number: 660000018810	Date of last issue: - Date of first issue: 05/22/2023
----------------	------------------------------	-----------------------------	----------------------------------------------------------

Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Further information

NFPA 704:



HMIS® IV:

HEALTH	/	2
FLAMMABILITY		1
PHYSICAL HAZARD		0

HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. The "*" represents a chronic hazard, while the "/" represents the absence of a chronic hazard.

Revision Date : 05/22/2023
 US / EN