DATA SHEET

Premium Efficiency Motor: **PEWWE10-12-256T** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024
Document ID:

Customer:

MOTOR INFORMATION

HP	10
RPM	1200
Phase	3
Frequency	60 Hz
Voltage	230/460 V
Frame Size	256T
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	6
Full Load Speed	1175
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	H
Duty Cycle	S1 / Continuous
Slip	2.10%
NEMA Design	B
Moment of Inertia	2.27 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	68 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40°C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class 1 Division 2 Groups A,B,C,D T3C(160°C)
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 9 Lead Δ
Approximate Weight	258 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	91.0 %	0.82
75%	91.2 %	0.76
50%	90.6 %	0.65

TORQUE

FULL LOAD	LRT	BDT
44.7 lb.ft.	180 %	280 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	25.1A	12.5A
Locked Rotor Amps	162A	81A
No Load Current	11.6A	5.8A
Usable at 208V	27.8A	

BEARING INFORMATION


DE Bearing	6309 C3
ODE Bearing	6209 C3
Grease Type	-
DE Regreasing Interval	7500 Hours
ODE Regreasing Interval	7500 Hours

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **PEWWE10-12-256T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
5	8.25	10	0.53	4.25	12.362	11.575	25.041	6.25	0.787	2.362	12.598	12.894	2.006	10.276

SHAFT & KEY				
S	ES	R	N-W	U
0.375	2.91	1.416	4	1.625

TERMINAL BOX				
AA	XB	XC	XD	XF
1 1/2	3.047	7.406	6.299	9.23

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **PEWWE10-12-256T**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	8-Oct-2024
Document ID:	

Customer:

Motor Type	PEWWE						
Output Rating (HP)	10		FL Speed	1175			
Full Load Torque	44.7	lb.ft	LRT (%FLT)	180	460 volt FLA	12.5	A
Rotor Wk^2	2.27	lb-ft^2	BDT (%FLT)	280	230 volt FLA	25.1	A





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.


NAMEPLATE / WIRING

Premium Efficiency Motor: **PEWWE10-12-256T**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 8-Oct-2024 Document ID:	Customer:

SAMPLE NAMEPLATE DATA



Model	PEWWE10-12-256T						
HP	10	S.F.	1.25	IP	IP55	Encl	TEFC
Frame	256T	P.F.	0.82	Code	H	Type	
Voltage	230/460 V	Hz	60 Hz	Ins Cl	F	Ambient	40°C
Amps	25.1/12.5	RPM	1175	Design	B	DE Brng	6309 C3
Nom.Eff.	FL 91.0%	3/4	91.2%			ODE Brng	6209 C3
Class 1 Division 2 Groups A,B,C,D T3C(160℃)						Grease type:	-

50Hz				
10 HP	200/400 V	30.1/15 A	970 rpm	87.2%

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization