

# Safety Data Sheet



## 1. Identification

<b>Name on Label:</b>	The Miracle All Purpose Floor Cleaner		
<b>Product Name:</b>	TPS AP FLOOR CLEANER 6PK	<b>Revision Date:</b>	2/23/2026
<b>Product Identifier:</b>	823785	<b>Supercedes Date:</b>	New SDS
<b>Recommended Use:</b>	Cleaner / All Purpose		
<b>Supplier:</b>	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA Tel: 1-800-466-7126	<b>Manufacturer:</b>	Star Brands Ltd Leeds UK LS15 82B Tel: +44(0)113 2666 300
<b>Preparer:</b>	Regulatory Department		
<b>Emergency Telephone:</b>	24 Hour Hotline: 847-367-7700		

## 2. Hazard Identification

### Classification

#### Symbol(s) of Product



#### Signal Word

Warning

#### Possible Hazards

1% of the mixture consists of ingredient(s) of unknown acute toxicity.

#### GHS Hazard Statements

Eye Irritation, category 2A H319 Causes serious eye irritation.

#### GHS Label Precautionary Statements

P264	Wash thoroughly after handling.
P280	Wear protective gloves, protective clothing, eye protection, and face protection.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P317	If eye irritation persists: Get medical help.

## 3. Composition / Information on Ingredients

**HAZARDOUS SUBSTANCES**

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
C9-C11 Alcohols Ethoxylated	68439-46-3	0.5-1.5	GHS05-GHS07	H302-315-318

Actual concentrations of ingredients are withheld as trade secret.

**4. First Aid Measures**

**First Aid - Eye Contact:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

**First Aid - Skin Contact:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

**First Aid - Inhalation:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**First Aid - Ingestion:** If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively.

**5. Fire-Fighting Measures**

**EXTINGUISHING MEDIA:** Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**Unusual Fire and Explosion Hazards:** Keep containers tightly closed. No unusual fire or explosion hazards noted.

**Special Fire Fighting Procedures:** Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

**Special Fire and Explosion Hazard (Combustible Dust):** Not a combustible dust.

**6. Accidental Release Measures**

**Steps to Be Taken If Material Is Released or Spilled:** If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers.

**7. Handling and Storage**

**Handling:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Do not get in eyes, on skin or clothing.

**Storage:** Store in a dry, well ventilated place. Keep container tightly closed when not in use.

**Advice on Safe Handling of Combustible Dust:** No Information

**8. Exposure Controls / Personal Protection**

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV-TWA	ACGIH TLV-STEL	OSHA PEL-TWA	OSHA PEL-CEILING
C9-C11 Alcohols Ethoxylated	68439-46-3	5.0	N.E.	N.E.	N.E.	N.E.

**PERSONAL PROTECTION**

**Engineering Controls:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**Respiratory Protection:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use.

**Skin Protection:** Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

**Eye Protection:** Use safety eyewear designed to protect against splash of liquids.

**Other Protective Equipment:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**Hygienic Practices:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

**Engineering Measures for Combustible Dust:** No Information

## 9. Physical and Chemical Properties

Physical State	Liquid	Decomposition Temperature, °C	N.D.
Color	Pink	pH	N.A.
Odor	Floral	Kinematic Viscosity	N.D.
Odor Threshold	Threshold N.E.	Solubility in Water	Slight
Freezing Point / Melting Point, °C	N.D.	Partition Coefficient, n-octanol/water	N.D.
Boiling Range, °C	100 - 111	Vapor Pressure	N.D.
Flammability	Does not Support Combustion	Evaporation Rate	Slower than Ether
Lower Explosion Limit, vol%	N.A.	Specific Gravity	1.008
Upper Explosion Limit, vol%	N.A.	Vapor Density	Heavier than Air
Flash Point, °C	102	Particle Characteristics	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**Conditions to Avoid:** Avoid excess heat.

**Incompatibility:** Incompatible with strong oxidizing agents, strong acids and strong alkalies.

**Hazardous Decomposition:** When heated to decomposition, it emits acrid smoke and irritating fumes.

**Hazardous Polymerization:** Will not occur under normal conditions.

**Stability:** This product is stable under normal storage conditions.

## 11. Toxicological Information

**Effects of Overexposure - Eye Contact:** Can cause severe eye irritation. Causes eye and skin irritation which may lead to dermatitis with repeated exposures. Irritating, and may injure eye tissue if not removed promptly.

**Effects of Overexposure - Skin Contact:** Low hazard for usual industrial handling or commercial handling by trained personnel.

**Effects of Overexposure - Inhalation:** High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

**Effects of Overexposure - Ingestion:** Substance may be harmful if swallowed.

**Effects of Overexposure - Chronic Hazards:** No Information

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
68439-46-3	C9-C11 Alcohols Ethoxylated	1400 mg/kg Rat	N.E.	N.E.

N.E. - Not Established

## 12. Ecological Information

**Ecological Information:** No ecotoxicity data was found for this product.

### 13. Disposal Considerations

**Disposal:** Dispose of material in accordance to local, state, and federal regulations and ordinances.

### 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
<b>UN Number:</b>	N.A.	N.A.	N.A.	N.A.
<b>Proper Shipping Name:</b>	Not Regulated	Not Regulated	Not Regulated	Not Regulated
<b>Hazard Class:</b>	N.A.	N.A.	N.A.	N.A.
<b>Packing Group:</b>	N.A.	N.A.	N.A.	N.A.
<b>Limited Quantity:</b>	No	No	No	No

### 15. Regulatory Information

#### U.S. Federal Regulations:

##### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Serious eye damage or eye irritation

##### SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

##### Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

### 16. Other Information

#### HMIS RATINGS

Health: 2\*    Flammability: 1    Physical Hazard: 0    Personal Protection: X

#### NFPA RATINGS

Health: 2    Flammability: 1    Instability: 0

Volatile Organic Compounds: 0.00%

SDS REVISION DATE: 2/23/2026

REASON FOR REVISION:

**Legend:**    N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.