ABB BALDOR RELIANCE

Customer information packet

L3710T

7.5HP, 1745RPM, 1PH, 60HZ, 215T, 3734LC, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:04:22 PM

Specifications

Enclosure	TEFC
Frame	215T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	7.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	29.000 A @ 230.0 V
	31.000 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	29.0 a
Insulation Class	F

Part Detail

Revision	L
Type	AC
Mech. spec.	37M307
Base	
Status	PRD/A
Elec. spec.	37WGT876
Layout	37LYM307
Eff. date	09-19-2025
CD Diagram	CD0086
Poles	04
Leads	2#10 A PH,2#14 B PH
Proprietary	False
Created date	01-21-2010

Inverter Code	Not Inverter
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 10 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3734LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.02 IN
Power Factor	97
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1745 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L								
CAT.NO.	L3710T							
SPEC.	37M307T876							
HP	7.5							
VOLTS	208-230							
AMP	31-29							
RPM	1745							
FRAME	215T	**HZ**	60			**PH**	1	
SER.F.	1.00	**CODE**	G	**DES**	L	**CLASS**	F	
NEMA-NOM-EFF	86.5	**PF**	97					
RATING	40C AMB-CONT							
CC								
DE	6307		**ODE**	6206				
ENCL	TEFC	**SN**						

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data
Record # 68287
Typical performance - not guaranteed values

Winding: 37WGT876-R012	**Type:** 3734LC	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			7.5	**Full Load Torque**	22.61 LB-FT
Volts			208-230	**Start Configuration**	direct on line
Full Load Amps			31-29	**Breakdown Torque**	70.1 LB-FT
R.P.M.			1745	**Pull-up Torque**	37.3 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	66.3 LB-FT
NEMA Design Code	L	**KVA Code**	G	**Starting Current**	184 A
Service Factor (S.F.)			1	**No-load Current**	5.37 A
NEMA Nom. Eff.	86.5	**Power Factor**	97	**Line-line Res. @ 25ºC**	0.27231 Ω A Ph 0.64764 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	86°C

Load Characteristics 230 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	91	96	97	97	97	96
Efficiency	73	84.6	87.5	87.6	85.5	81.7
Speed	1786.7	1774.6	1761.5	1745.4	1725.9	1700.6
Line amperes	9.1	14.9	21.4	28.6	36.8	46.8


ABB Motors and Mechanical Inc.


WINDING # 37WGT876

7.5 HP 1 PH 60 HZ 1745 RPM 230 V 3734LC


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=70.1 PU=37.3 LR=66.3 LRA=184




37LYM307
(717-741) = 19.02
(742-746) = 19.77
(747-753) = 20.52
(754-756) = 21.21
3.88
2.75
12.39
3.38
Ø10.28
GROUND SCREW
.31 KEY
2.38 LONG
LEAD HOLE (REF)
Ø1.3750
1.3745
2 DRAIN HOLES
6 HOLES .41 DIA.
5.50
3.50
7.00
.50
8.00
Ø9.45
9.24
TOP OF NAMEPLATE
2.36
7.25
10.04
5.25 +.00 -.06
2.50
(DRAINS)
LEAD HOLE 1.09 DIA.
4.25
4.25
7.77
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: B
VERSION: 02
REVISED: 08:24:44 10/19/2022
TDR: 000001198704
MODEL NO. 37LYM307
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ 213-5T TEFC LC 37CB3804, FINNED ENDRING, TORQ SWITCH
37LYM307

CD0086



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. OPTIONAL OIL CAPACITOR IS PROVIDED WHEN SPECIFIED.
5. CAPACITORS MAY BE SEPERATELY MOUNTED.
6. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: ADDED CK TO PLANT CODE			BALDOR ELECTRIC Co.
REV. LTR: F	BY: JD	REVISED: 16:01:12 01/07/2002	TDR: 259409
9800CD		FILE: AAA00026904	REF: CD0086
		MTL: –	TYPE L OR LC, SV, REV, 4 LEADS, CAPS MAY BE SEP MTD

CD0086