



1.1 PRODUCT IDENTIFIERS

Product Name: **Wipex Fitness Antiseptic Wipes with BZK Antibacterial**
Product Code: 1.CLS.22507.1

1.2 RELEVANT IDENTIFIED USES OF THE SUBSTANCE OR MIXTURE AND USES ADVISED AGAINST

Identified uses: Fitness Hand Wipes

1.3 DETAILS OF THE SUPPLIER OF THE SAFETY DATA SHEET

Company: **UNICO, ITC dba A WORLD OF WIPES dba
DUTCH HARBOR BRANDS**
240 W Palmetto Park Rd, Boca Raton, FL 33432, USA

FOR PRODUCT INFORMATION ONLY

Company Telephone: (561) 338-3338

SECTION II. HAZARD IDENTIFICATION

2.1 Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 (CLP) and its amendments.

This mixture is not classified as hazardous according to Regulation (EC) No. 1272/2008

2.2 Label elements

In compliance with EC regulation No. 1272/2008 (CLP) and its amendments.

This mixture is not classified as hazardous according to Regulation (EC) No. 1272/2008.

SECTION III. COMPOSITION/INFORMATION ON INGREDIENTS

3.2 Mixtures Composition:

Identification	CAS-No.	%
Benzalkonium Chloride	63449-41-2	0.1-1.0%

(Full text of H-phrases: see section 16)

SECTION IV. FIRST AID MEASURES

4.1 DESCRIPTION OF FIRST AID MEASURES

Eye Contact:	Immediately flush eye with water while lifting the upper and lower lids. Get medical attention if irritation persists.
Skin Contact:	Wash thoroughly with soap and water. Remove contaminated clothing and laundry before reuse. Get medical attention if irritation develops.
Inhalation:	Remove victim to fresh air. If breathing has stopped give artificial respiration. If breathing is difficult have qualified personnel administer oxygen. Get medical attention.
Ingestion:	Do not induce vomiting. Get immediate medical attention by calling a Poison Control Center or hospital emergency department.

4.2 MOST IMPORTANT SYMPTOMS AND EFFECTS, BOTH ACUTE AND DELAYED

May cause mild eye and skin irritation. Accidental ingestion may cause gastrointestinal effects with nausea and diarrhea.

4.3 INDICATION OF ANY IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED

Get immediate medical attention in cases of ingestion.
--

SECTION V. FIREFIGHTING MEASURES

Non-Flammable

5.1 EXTINGUISHING MEDIA

Suitable methods of extinction	In the event of a fire, use: - fog - foam - carbon dioxide (CO ₂) - Dry Chemical -Water or foam may cause frothing.
Unusual fire and explosion hazards	At elevated temperatures containers may rupture.
Combustion products	Thermal decomposition may yield carbon monoxide, carbon dioxide and hydrocarbons.

5.2 SPECIAL HAZARDS ARISING FROM THE SUBSTANCE OR MIXTURE

No data available.

5.3 ADVICE FOR FIREFIGHTERS

Special protective equipment and precautions for fire-fighters

Firefighters should wear full emergency equipment and a NIOSH approved positive pressure self-contained breathing apparatus. Cool fire exposed containers and structures with water.

SECTION VI. ACCIDENTAL RELEASE MEASURES

6.1 PERSONAL PRECAUTIONS, PROTECTIVE EQUIPMENT AND EMERGENCY PROCEDURES

Consult the safety measures listed under headings 7 and 8.

For non-first aid worker

Wear adequate protective equipment. Consult the safety measures listed under headings 7 and 8. Avoid any contact with the eyes. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personal to safe areas.

For first aid worker

First aid workers will be equipped with suitable personal protective equipment (See section 8).

6.2 ENVIRONMENTAL PRECAUTIONS

Prevent entry in storm sewers and waterways. Report spill as required by local and federal regulations.

6.3 METHODS AND MATERIAL FOR CONTAINMENT AND CLEANING UP

Dike spill and collect into closable containers for disposal with an inert absorbent.

6.4 REFERENCE TO OTHER SECTIONS

No data available.

SECTION VII. HANDLING AND STORAGE

7.1 PRECAUTIONS FOR SAFE HANDLING

Comply with the legal requirements. Do not handle until all safety precautions have been read and understood. Use personal protective equipment as required. Avoid contact with eyes.

Fire prevention:

No special precautions required.

Recommended equipment and procedures:

For personal protection, see section 8. Observe precautions stated on label and also industrial safety regulations.

	Packages which have been opened must be reclosed carefully and stored in an upright position.
Prohibited equipment and procedures:	No special precautions required.

7.2 CONDITIONS FOR SAFE STORAGE, INCLUDING ANY INCOMPATIBILITIES

	No data available.
Storage	Store products in tightly closed, original containers in cool, dry place away from oxidizers.
Packaging	Always keep in packaging made of an identical material to the original. Empty containers retain product residues. Do not cut, weld, braze, etc. on or near empty containers. Follow all SDS precautions in handling empty containers.

7.3 SPECIFIC END USE(S)

	No data available.
--	--------------------

SECTION VIII. EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 CONTROL PARAMETERS

Occupational exposure limits:	No data available.
-------------------------------	--------------------

8.2 EXPOSURE CONTROLS

Personal protection measures, such as personal protective equipment	Pictogram(s) indicating the obligation of wearing personal protective equipment (PPE): None necessary. Never eat, drink or smoke during use.
- Eye / face protection	None normally required . Avoid direct contact with eyes.
- Hand protection	None normally required.
- Respiratory Protection	Normal room ventilation is adequate
- Other Protective Equipment:	None under normal use

SECTION IX. PHYSICAL AND CHEMICAL PROPERTIES

9.1 INFORMATION ON BASIC PHYSICAL AND CHEMICAL PROPERTIES GENERAL INFORMATION:



SAFETY DATA SHEET

REVISED: SEP 2, 2024

Color/Odor/Appearance:	Colorless liquid
Solubility	SOLUBLE
Initial Boiling Point/Range	No data available
Specific Gravity (H ₂ O=1)	0.975-1.025
Vapor Pressure (@ 20 C Mm Hg)	None available
Evaporation Rate (Butyl Acetate=1)	None available
Solubility In Water	Negligible
pH	4.8-5.2
Viscosity	None available
Relative Density	None available
Molecular Formula	None available
Flammability (solid, gas):	None available
Flash Point	None available
Flammable Limits:	None available
Odor:	Characteristic
Odor Threshold	No data available
Melting/Freezing Point	Not Available
Voc	None available
Vapor Density (Air=1)	None available
Coefficient Of Water/Oil	Not Available
Volatile	Not Available
Decomposition Temperature	Not Determined
Explosive Properties	Not explosive
Oxidizing Properties	Not an oxidizer
Molecular Weight	Mixture
Autoignition Temperature	Not Determined

9.2 OTHER INFORMATION

None available

SECTION X. STABILITY AND REACTIVITY

Stable in the conditions of storage above.

No dangerous reaction known at the conditions recommended for use and storage.

10.1 REACTIVITY

Not reactive.

10.2 CHEMICAL STABILITY

This mixture is stable.

10.3 POSSIBILITY OF HAZARDOUS REACTIONS

Will not occur.

10.4 CONDITIONS TO AVOID

Avoid excessive heat

10.5 INCOMPATIBLE MATERIALS

No data available.

10.6 HAZARDOUS DECOMPOSITION PRODUCTS

No data available.

SECTION XI. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

No data is available regarding the preparation itself.
However, exposure of this preparation could lead to health problems for especially sensitive subjects or due to unforeseeable reasons.

Eye Contact	May cause Irritating to eyes. Should it occur rinse immediately with plenty of water for 15 minutes holding the eyelids open
Skin Contact	Repeated or prolonged contact can cause redness and/or irritation Should it occur, flush skin with plenty of water. Seek medical attention where necessary
Inhalation	Not expected to present a significant inhalation hazard under anticipated conditions of normal use.
Ingestion	Swallowing may cause gastrointestinal irritation, nausea, vomiting, and diarrhea.

11.1.1 Substances

Acute toxicity:	No data available.
-----------------	--------------------



11.1.2 Mixture

No data available.

Monograph(s) from the IARC (International Agency for Research on Cancer):

No data available.

SECTION XII. ECOLOGICAL INFORMATION

The product must not be allowed to run into drains or waterways, Avoid release to the environment.

12.1 TOXICITY

Mixtures No data available.

12.2 PERSISTENCE AND DEGRADABILITY

No data available.

12.3 BIOACCUMULATIVE POTENTIAL

No data available.

12.4 MOBILITY IN SOIL

No data available.

12.5 RESULTS OF PBT AND VPVB ASSESSMENT

No data available.

12.6 OTHER ADVERSE EFFECTS

No data available.

SECTION XIII. DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

13.1 WASTE TREATMENT METHODS

This product as sold does not meet the definition of a US EPA hazardous waste. Dispose in accordance with all local, state and federal regulations.

Waste:	Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals. Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.
--------	---



	Do not contaminate the ground or water with waste, do not dispose of waste into the environment.
Soiled packaging:	Empty container completely. Keep label(s) on container. Give to a certified disposal contractor.

SECTION XIV. TRANSPORT INFORMATION

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2017 - IMDG 2016 - ICAO/IATA 2017).

14.1 UN NUMBER

This product is not regulated as a hazardous material.

14.2 UN PROPER SHIPPING NAME

-

14.3 TRANSPORT HAZARD CLASS(ES)

-

14.4 PACKING GROUP

-

14.5 ENVIRONMENTAL HAZARDS

-

14.6 SPECIAL PRECAUTIONS FOR USER

No data available.

14.7 TRANSPORT IN BULK ACCORDING TO ANNEX II OF MARPOL AND THE IBC CODE

No data available.

SECTION XV. REGULATORY INFORMATION

15.1 SAFETY, HEALTH AND ENVIRONMENTAL REGULATIONS/LEGISLATION SPECIFIC FOR THE SUBSTANCE OR MIXTURE

Classification and labelling information included in section 2:


EPA SARA 302	This product does not contain chemicals regulated under SARA Section 302.
EPA SARA 311 Hazard Classification:	Not Hazardous

EPA SARA 313:	This product contains the following chemicals that are regulated under SARA Title III, section 313:
California Proposition 65:	This product is not known to contain any chemicals which are known to the State of California to cause cancer or reproductive harm.
Toxic Substances Control Act:	The components of this product is intended to be used as a cosmetic ingredient and is exempt from Toxic Substances Control Act (TSCA) regulation (40 CFR 710) when used as such. Do not use for other purposes.
Canadian Environmental Protection Act:	All of the components of this product are listed on the Canadian Domestic Substances List (DSL).
WHMIS Classification:	Not a controlled product.
	This product has been classified in accordance with the hazard criteria in the CPR and the SDS contains all the information required by the CPR.
European Inventory of Commercial Chemical Substances:	All of the components of this product are listed on the EINECS Inventory.
Australian Inventory of Chemical Substances:	All of the components of this product are listed on the AICS Inventory.
Inventory of Existing Chemical Substances of China:	All of the components of this product are listed on the Chinese IECSC.
Korean Existing Chemical List:	All of the components of this product are listed on the KECL Inventory.
Philippine Inventory of Chemicals and Chemical Substances:	All of the components of this product are listed on the PICCS.

15.2 CHEMICAL SAFETY ASSESSMENT

No data available.

SECTION XVI. OTHER INFORMATION



0	HEALTH
0	FLAMMABILITY
0	PHYSICAL HAZARD

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

Wording of the phrases mentioned in section 3:	NA
Abbreviations:	CMR: Carcinogenic, mutagenic or reprotoxic. ADR: European agreement concerning the international carriage of dangerous goods by Road. IMDG: International Maritime Dangerous Goods. IATA: International Air Transport Association. ICAO: International Civil Aviation Organization RID: Regulations concerning the International carriage of Dangerous goods by rail. WGK: Wassergefahrdungsklasse (Water Hazard Class). GHS07: Exclamation mark GHS08: Health hazard GHS09: Environment PBT: Persistent, bioaccumulable and toxic. vPvB: Very persistent, very bioaccumulable. SVHC: Substances of very high concern.
REVISED:	SEPTEMBER 2 ND , 2024