

QO2100CP

Mini circuit breaker, QO, 100A, 2 pole,
120/240VAC, 10kA, plug in mount, consumer
pack



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	100 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Plug-in
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Type of Packing	Consumer packaging

Complementary

Interrupt Rating	10 KA 120/240 V AC 50/60 Hz 10 kA 120 V AC 50/60 Hz
Number of Panel Spaces	2
Wire Size	AWG 4...AWG 2/0 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 2)
Height	3.50 in (89 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.70 lb(US) (0.318 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	01343-QO 2 POLE 70-125 AMP
Discount Schedule	CPQ
GTIN	047569522291
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	3.80 in (9.652 cm)
Package 1 Length	3.80 in (9.652 cm)
Package 1 Weight	11.20 oz (317.515 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	51
Package 2 Height	3.80 in (9.652 cm)

Package 2 Width	13.80 in (35.052 cm)
Package 2 Length	20.80 in (52.832 cm)
Package 2 Weight	36.75 lb(US) (16.67 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Halogen content performance	Halogen free product