



OSCILLATING SANDERS

MASTERFUL RESULTS, NO GUESSWORK

A new level of precision for a flawless finish.



Vertical Edge Sander
PM1-263 & PM1-264



Spindle Sander
PM1-266

POWERMATIC OSCILLATING SPINDLE SANDER


- Cast Iron Stay-Flat Table
- Oscillating Control
- Angle Display
- Angle Adjustment
- 0-45° Tilting Spindle
- Motor Access
- Spindle & Insert Storage



BRAND	POWERMATIC
MODEL NUMBER	OSS10
STOCK NUMBER	PM1-266
Table Size	24-1/2 x 24-1/2 in.
Table Height	39-13/16 in.
Spindle Tilt	0-45 deg.
Center of Spindle to Front of Table	17-61/64"
Table Inserts (pcs)	6
Spindle Sizes	1/4", 3/8", 1/2", 5/8", 3/4", 1", 1-1/2", 2", 3", 4"
Spindle RPM	600-1800 RPM
Running Direction	CCW (Viewed From Above)
Max Workpiece Height	2-1/8" to 6-1/4"
Oscillations p/Min	60 per/min
Spindle Stroke	1-1/2"
Sanding Sleeve Length	6 - 9"
Dust Port Size	4"
Base Footprint	22-7/8 x 22-7/8 in.
Power Requirement (V)	1PH 60Hz, 115V, 12A
Motor	1HP BLDC
Product Dimensions (in.)	25-13/16" x 24-1/2" x 39-13/16"
Shipping Dimensions (in.)	30" x 25-13/16" x 45-5/8"
Product Weight (lbs.)	335 lbs
Shipping Weight (lbs.)	412 lbs
Country of Manufacture	China
Warranty	5yr

POWERMATIC OSCILLATING VERTICAL EDGE SANDER

- 0-45° Tilting Belt
- Oscillating Motor
- Cast Iron Stay-Flat Table
- Vertical Table Adjustment
- Belt Speed & Oscillating Control
- 0-45° Tilt Control
- Horizontal Table Adjustment
- Premium Miter Gauge
- Single Dust Collector Port



BRAND	POWERMATIC
MODEL NUMBER	OES9138B, OES9138B-3
STOCK NUMBER	PM1-263, PM1-264
Table Travel	7-3/8 in.
End Table Travel	5 in.
Drive Roller Size	9 in.
Idler Roller Size	5 in.
Belt Length	138 in.
Belt Width	9 in.
Belt Oscillations	3/8 in.
Belt Tilt	0-45 deg.
Belt Release	Lever Quick Release
Platen Type	Graphite Coated Cast Iron
Platen Length	47-1/2 in.
Platen Width	10 in.
Sanding Belt Speed	1000 - 4200 FPM
Table Length	46 in.
Table Width	13 in.
Table Thickness	1-1/2 in.
Floor-to-Table Height	32-3/4 - 40-1/8 in.
Base	Cast Iron
Drive Roller	Aluminum w/rubber
Frame	Cast Iron
Idler Roller	Aluminum
Miter Block	Steel & Aluminum
Table	Cast Iron
Number of Dust Ports	1
Dust Port Size	4 in.
Power Requirement (V)	230V, 1PH / 230V, 3PH / 460, 3PH
Motor	3HP
Product Dimensions (in.)	75 x 29 x 45 in.
Shipping Dimensions (in.)	81 x 31 x 51 in.
Product Weight (lbs.)	660 lbs
Shipping Weight (lbs.)	810 lbs
Country of Manufacture	Taiwan
Warranty	5yr

POWERMATIC OSCILLATING SANDERS

Experience unparalleled quality, reliability, and precision with this new line of Oscillating Sanders from Powermatic. With their innovative design and enhanced features, these triple threat sanders will elevate your woodworking game.



ADVANCED OSCILLATING TECHNOLOGY

From high-quality parts to variable speed controls, you can easily increase the quality of every project.



STAY-FLAT TABLE

The fixed table design with tilting sanding surface reduces user fatigue over time by supporting the material weight.



FINE-TUNING CONTROLS

Smooth moving, easy-to-operate handles and knobs as well as the large, readable display make adjustments easy.

