ABB BALDOR RELIANCE

Customer information packet

ECTM4110T-G

40HP, 1775RPM, 3PH, 60HZ, 326T, 1254M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 1:14:49 PM

Specifications

Enclosure	TEFC
Frame	326T
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	40.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	NEMA PREMIUM
	NEMA_PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	96.000 A @ 230.0 V
	48.000 A @ 460.0 V
	102.000 A @ 208.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	94.1 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	Tapped & Key

Part Detail

Revision	F
Type	AC
Mech. spec.	12T112
Base	
Status	PRD/A
Elec. spec.	12WGY276
Layout	12LYT112
Eff. date	05-05-2026
CD Diagram	CD0180
Poles	04
Leads	9#8
Proprietary	False
Created date	04-14-2022

Heater Indicator	Heater Included, 115 V
High Voltage Full Load Amps	48.0 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Vertical Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 8 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1254M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	30.34 IN
Power Factor	82
Product Family	Chemical Processing (Not DC)
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	2.125 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1260									
CAT.NO.	ECTM4110T-G								
SPEC.	12T112Y276G1								
HP	40								
VOLTS	230/460								
AMP	96/48								
RPM	1775								
FRAME	326T	**HZ**	60		**PH**	3			
SER.F.	1.15	**CODE**	H	**DES**	A		**CL**	F	
NEMA-NOM-EFF	94.1	**PF**	82						
RATING	40C AMB-CONT								
CC	010A								
DE	6312	**ODE**	6311						
ENCL	TEFC	**SN**							
	INV DUTY 20:1VT								

AC Induction Motor Performance Data
Record # 31673
Typical performance - not guaranteed values

Winding: 12WGY276-R001	**Type:** 1254M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			40	**Full Load Torque**	119 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			96/48	**Breakdown Torque**	396 LB-FT
R.P.M.			1775	**Pull-up Torque**	198 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	222 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	347 A
Service Factor (S.F.)			1.15	**No-load Current**	21.03 A
NEMA Nom. Eff.	94.1	**Power Factor**	82	**Line-line Res. @ 25ºC**	0.15 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	54°C
S.F. Amps				**Temp. Rise @ S.F. Load**	66°C
				Locked-rotor Power Factor	27.1
				Rotor inertia	7.19 lb-ft²

Load Characteristics 460 V, 60 Hz, 40 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	45	67	77	82	84	85	83
Efficiency	89.8	93.4	94.1	94.4	93.9	93.1	94.1
Speed	1794	1788	1783	1777	1771	1765	1773
Line amperes	23.93	30.4	39.12	48.68	59.71	71.22	55.3


ABB Motors and Mechanical Inc.


WINDING # 12WGY276

40 HP 3 PH 60 HZ 1775 RPM 460 V 1254M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=396 PU=198 LR=222 LRA=347




12LYT112
(1232-1272) = 30.34
13.84
5.57
5.25
PLUG
DOME SLINGER
.50 KEY
3.88 LONG
PLUG
Ø 2.125
2.124
.62-11 TAP
1.50 DEEP
(EACH END)
3 DRAIN
FITTINGS
(EACH END)
V-RING
SLINGER
DRAIN PLUG
(EACH SIDE)
(REF)
FRAME GRND
.38-16 TAP
10.50
10.50
1.00
12.00
5.25
8 HOLES
Ø .66
14.00
17.87
14.13
8.45
3.22
16.23
8.00
7.94
LEAD
HOLE
2.00 NPT
.125 NPT
DRAIN PLUG
(EACH SIDE)
6.25
6.25
11.75
7.25
14.50
LIP SEAL
INTERNAL
SHAFT GROUND
V-RING
SLINGER
PULLEY END DETAIL
CUSTOMER ONLY NOTE: FOR VERTICAL SHAFT UP
AND VERTICAL SHAFT DOWN LIFTING, REMOVE EYEBOLT
FROM TOP OF MOTOR AND SCREW INTO END OF SHAFT.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: NEW FOR CCT STOCK DEVELOPMENT
REV: - VERSION: 00 REVISED: 04:51:51 04/21/2022 TDR: 000001185763
MODEL NO. 12LYT112 REF: -
BY: ENFRAJ0 B
BALDOR - RELIANCE®
HORZ TEFC 324-6T CP COOLING TOWER,LIFT,SLD BRGS,SEAL,SH GND
12LYT112

CD0180





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1