

# Product Specifications



## #10 x 1" Hex Washer High Head Self Drilling Screw (Tuff Pack)

Part Number TEKHT101HH

UPC 781002861225

High Head Self-Drilling Screws are made from cold-heading steel and designed with a heightened head that offers extra grip for improved driving control and holding strength. The self-drilling tip allows them to drill, tap, and fasten metal-to-metal in one step with no pre-drilling required. This ensures optimal drilling performance and smooth, reliable thread formation. While primarily used for metal-to-metal applications, these versatile screws are suitable for a wide range of fastening tasks. All material and performance requirements are covered under ASTM C954 standards.



### Physical Characteristics

|                              |                     |
|------------------------------|---------------------|
| Type                         | Self Drilling Screw |
| Style                        | High Head           |
| Drive Type                   | Slotted             |
| Head Type                    | Hex Washer          |
| Thread Type                  | DWF                 |
| Point Type                   | Sharp               |
| Size                         | #10 x 1"            |
| Dia./Thread Size             | #10                 |
| Hex Size                     | 5/16"               |
| Length (in)                  | 1"                  |
| Head Height                  | 0.165" - 0.161"     |
| Thread Pitch\Thread Per Inch | 16                  |
| Material                     | Carbon Steel        |
| Finish                       | Zinc Plated         |

### Performance Data

|                   |  |
|-------------------|--|
| Rockwell Hardness | HRC 32 - 40  |
| Special Features  | Drills and taps in one step, No pre-drilling required, Smooth and precise drilling, Zinc-plated finish |
| Applications      | Metal to Metal   |

### Packaging Details

|                |      |
|----------------|------|
| Standard Qty   | 300  |
| Master Qty     | 1800 |
| Price Per      | 100  |
| Package Length | 3.74 |
| Package Width  | 3.62 |
| Package Height | 3.54 |
| Package Weight | 2.70 |

### Certifications

|                |          |
|----------------|----------|
| UNSPSC         | 31161528 |
| RoHS Compliant | Yes      |
| Meets/Exceeds  | IFI-113  |