

SYLVANIA Lamps

SubstiTUBE® IPS LED T8

Compatible LED T8 for use with instant start and select programmed rapid start electronic T8 ballasts

SubstiTUBE IPS LED T8 lamps are an energy saving alternative, designed to replace traditional fluorescent T8 lamps. These LED T8 lamps contain no mercury, and provide instant light and a uniform light distribution. Engineered to operate on existing instant start and select program rapid start electronic T8 ballasts, these lamps minimize labor and recycling costs.

Benefits and Features

- The SubstiTUBE IPS LED T8 is not affected by switching cycles, occupancy or vacancy sensors, and thus can be installed with the existing instant start ballasts for optimal energy savings
- NSF Listed: NSF/ANSI Standard 2 – Food Equipment
- No warm-up time, instant-on with full light output and stable lamp to lamp color
- DLC listed allows for rebates in areas where applicable saving on overall project cost
- No UV emission
- Suitable for dry and damp locations (cannot come in direct contact with water)
- Maximize energy savings with occupancy sensors
- Can be used in enclosed (lens or diffuser) luminaire. Not approved for use in vapor tight or sealed luminaire.
- Glass lamps are suitable for use with tube guards
- Up to 178 LPW (Lamp efficacy)
- 3000K, 3500K, 4100K, 5000K color temperatures
- CRI: 82
- Available beam angle: 220° and Light Emitting Angle 340°

Electrical

- Compatible with instant start and select programmed rapid start electronic T8 ballasts with input voltage of 120-277V and 347V
- Dimmable down to 10% with compatible 0-10V ballast
- Power factor >0.90
- THD <10%

Rated Life

- 50,000 hours (L₇₀) at 45°C for all items
- 70,000 hours at max ambient temperature at 25°C for items 41270–41277



Wattage Comparison

	System Power ¹	Traditional System Power F032T8 (with QHE2x32 ISN)	Energy Savings/Year ²
LED12T8L48FGPDIMSUBG9	29W	55W	47%
LED10T8L48FG SUBG9	26W	55W	53%
LED9T8L48FGPDIMSUBG9	24W	55W	56%
LED10T8L36FG8XXSUBG9	26W	55W	53%
LED8T8L24FG8XXSUBG9	20W	29W	31%

1. With QHE2x32 ISN
2. 24 hours a day

Ambient Operating Range

- -4°F to 113°F (-20°C to 45°C)

Warranty

- 5 year limited lamp warranty (24/7 operation)
- NLB Trusted Warranty Program

Certifications and Listings

- cULus (UL 1993, CSA 22.2)
- RoHS
- Lead Free
- Mercury Free
- FCC*, ICES
- NSF (ANSI 2 – Food Equipment)
- DLC 5.1

*FCC Title 47 CFR, Part 18, Non-Consumer

Installation

- Please refer to the Installation manual included inside the packaging and the applications information listed below for more information. (G13 medium bi-pin base)
- For proper use and warranty coverage, installer must consult the ballast compatibility list to ensure that the lamp and ballast combination is deemed compatible and will operate as intended.

Ballast
Compatibility
Guide



LED559R7 9-25



Catalog #	Type
Project	
Comments	
Prepared by	

Ordering Guide

LED	XX	T8	LXX	FG	DIM	8	XX	SUB	G9
LED	Wattage 8 = 8 Watts 9 = 9 Watts 10 = 10 Watts 12 = 12 Watts	Lamp Type T8	Length L24 = 24" L36 = 36" L48 = 48"	FG = Frosted Glass	DIM = Dimmable	CRI 8 = 82	Color Temperature 30 = 3000K 35 = 3500K 41 = 4100K 50 = 5000K	SubstiTUBE® IPS	Generation 9

Ordering Information

Item Number	Ordering Abbreviation	Length	Lens Material	Power (W) ¹	Lamp Efficacy	Typical Lumens (lm) ¹	CCT	CRI	Life (L ₇₀) Hours	Beam Angle (°)	Case Qty	DLC Listed
40991	LED8T8L24FG830SUBG9	2ft	Frosted Glass	8	156	1250	3000K	82	50,000	220	25	Yes
40992	LED8T8L24FG835SUBG9	2ft	Frosted Glass	8	156	1250	3500K	82	50,000	220	25	Yes
40993	LED8T8L24FG841SUBG9	2ft	Frosted Glass	8	156	1250	4100K	82	50,000	220	25	Yes
40994	LED8T8L24FG850SUBG9	2ft	Frosted Glass	8	156	1250	5000K	82	50,000	220	25	Yes
40995	LED10T8L36FG830SUBG9	3ft	Frosted Glass	10	145	1450	3000K	82	50,000	220	25	Yes
40996	LED10T8L36FG835SUBG9	3ft	Frosted Glass	10	145	1450	3500K	82	50,000	220	25	Yes
40997	LED10T8L36FG841SUBG9	3ft	Frosted Glass	10	145	1450	4100K	82	50,000	220	25	Yes
40998	LED10T8L36FG850SUBG9	3ft	Frosted Glass	10	145	1450	5000K	82	50,000	220	25	Yes
41270	LED9T8L48FGDIM830SUBG9	4ft	Frosted Glass	9	178	1600	3000K	82	70,000*	220	25	Yes
41271	LED9T8L48FGDIM835SUBG9	4ft	Frosted Glass	9	178	1600	3500K	82	70,000*	220	25	Yes
41272	LED9T8L48FGDIM841SUBG9	4ft	Frosted Glass	9	178	1600	4100K	82	70,000*	220	25	Yes
41273	LED9T8L48FGDIM850SUBG9	4ft	Frosted Glass	9	178	1600	5000K	82	70,000*	220	25	Yes
41274	LED12T8L48FGDIM830SUBG9	4ft	Frosted Glass	12	167	2000	3000K	82	70,000*	220	25	Yes
41275	LED12T8L48FGDIM835SUBG9	4ft	Frosted Glass	12	167	2000	3500K	82	70,000*	220	25	Yes
41276	LED12T8L48FGDIM841SUBG9	4ft	Frosted Glass	12	175	2100	4100K	82	70,000*	220	25	Yes
41277	LED12T8L48FGDIM850SUBG9	4ft	Frosted Glass	12	175	2100	5000K	82	70,000*	220	25	Yes


*70,000 hours at max ambient temp 25°C
1. Average Lamp Power and Average Lamp Lumens rated on QHE2x32T8/UNV ISN.

Specifications & Lighting Data

Lamp	Ballast	Current (Amps)	System Power (W)	System Lumens (lm)	System Efficacy (lm/W)	No of Lamps
LED12T8L48FGPDIM	QHE 2X32T8/UNV ISN	0.24/0.10	29	4200	140+	2
LED9T8L48FGPDIM	QHE 2X32T8/UNV ISN	0.20/0.09	24	3200	133+	2
LED10T8/L36FG	QHE2X32T8/UNV/ISN	0.20/0.09	24	2900	120	2
LED8T8/L24FG	QHE2X32T8/UNV/ISN	0.17/0.08	20	2400	120	2

Note: For complete system information refer to LED495 – SubstiTUBE System Information.

Physical Information



Lamp Description	L1 End of Base Pin to End of Opposite Pin End	L2 Base Face to Opposite Base Pin	L3 Base Face to Base Face	L4 Bulb Outside Diameter
LED12T8/L48 LED9T8/L48	47.725" ± 0.055" (1212.2mm ± 1.4mm)	47.45" ± 0.05" (1205.25mm ± 1.25mm)	max 47.22" (1199.4mm)	1.02" ± 0.08" (25.9mm ± 2.0mm)
LED10T8/L36	35.72" ± 0.055" (907.4mm ± 1.4mm)	35.45" ± 0.05" (900.45mm ± 1.25mm)	max 35.22" (894.6mm)	1.02" ± 0.08" (25.9mm ± 2.0mm)
LED08T8/L24	23.72" ± 0.055" (602.6mm ± 1.4mm)	23.45" ± 0.05" (595.65mm ± 1.25mm)	max 23.22" (589.8mm)	1.02" ± 0.08" (25.9mm ± 2.0mm)

Application Information

1. Due to numerous ballast designs and topologies, this lamp should be tested on existing ballasts before mass quantities are installed.
2. Not intended for use with older dedicated voltage (120V or 277V) ballasts. These ballasts have electronic components that degrade over time and may become unsuitable for the new LED T8 lamp.
3. Not for use with ballasts more than ten years old.
4. All installation, inspection, and maintenance of lighting fixtures should be done with the power to the fixture turned off. Lamps should be installed and operated in compliance with the National Electrical Code (NEC), Underwriters Laboratories Inc. (UL) requirements, and all applicable codes and regulations.
5. Insert and align tubes properly in lamp holders. Partial insertion results in a poor or intermittent electrical contact that can result in short lamp life and arcing. Arcing at the lamp holder can result in localized overheating.
6. For instant start ballasts, use lamp holders with an internal shunt or ensure that lamp holders are wired in a shunt configuration.
7. For Programmed Rapid Start ballasts, use rapid-start lamp holders (non-shunted lamp holders).
8. De-lamp is not allowed for ISH ballasts.
9. For approved ISN and ISL ballasts, de-lamp is allowed for only 1 lamp so long as the ballast factor remains below 1.20 (for example: 4-lamp ballast can de-lamp to 3 lamps).
10. Suitable for use in dry and damp environments.
11. Maximum mounting distance between tube and ballast is 20 feet.
12. Not for use with other LED or fluorescent lamps on the same ballast.
13. Not for use with magnetic ballasts.
14. Max case temperature: 158°F (70°C).
15. Please read all installation instructions before attempting installation.
16. For detailed warranty information, please see www.ledvanceUS.com.

LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com

SYLVANIA and LEDVANCE are registered trademarks.
All other trademarks are those of their respective owners.
Licensee of product trademark SYLVANIA in general lighting.
Specifications subject to change without notice.



SCAN TO FOLLOW US
ON SOCIAL MEDIA

© 2025 LEDVANCE LLC

