

## 1 Identification

- **Product identifier**
- **Trade name:** MLH14, MLH16 Metalock Hardener
- **Article number:** MLH14, MLH16
- **Application of the substance / the mixture** Coating
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
SEM Products Inc.  
1685 Overview Drive  
Rock Hill, SC 29730  
803 207 8225
- **Information department:**  
cust\_care@semproducts.com : SEM Products, Inc. 1685 Overview Dr. Rock Hill, SC 29730 : phone 1-800-831-1122, M - TH 7am - 4pm EDT
- **Emergency telephone number:** CHEMTREC 1-800-424-9300

## 2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Liq. 3 H226 Flammable liquid and vapor.



GHS05 Corrosion

Eye Dam. 1 H318 Causes serious eye damage.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

STOT SE 3 H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.

- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms**



GHS02



GHS05



GHS07

- **Signal word** *Danger*
- **Hazard-determining components of labeling:**  
butan-1-ol  
4-chloro-alpha,alpha,alpha-trifluorotoluene  
Amine proprietary

**Trade name: MLH14, MLH16 Metallock Hardener**

(Contd. of page 1)

· **Hazard statements**

- H226 Flammable liquid and vapor.
- H315 Causes skin irritation.
- H318 Causes serious eye damage.
- H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.

· **Precautionary statements**

- P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
- P241 Use explosion-proof electrical/ventilating/lighting/equipment.
- P261 Avoid breathing dust/fume/gas/mist/vapors/spray
- P280 Wear protective gloves / eye protection / face protection.
- P240 Ground/bond container and receiving equipment.
- P242 Use only non-sparking tools.
- P243 Take precautionary measures against static discharge.
- P264 Wash thoroughly after handling.
- P271 Use only outdoors or in a well-ventilated area.
- P303+P361+P353 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
- P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P321 Specific treatment (see on this label).
- P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
- P332+P313 If skin irritation occurs: Get medical advice/attention.
- P370+P378 In case of fire: Use for extinction: CO2, powder or water spray.
- P362+P364 Take off contaminated clothing and wash it before reuse.
- P405 Store locked up.
- P403+P233 Store in a well-ventilated place. Keep container tightly closed.
- P403+P235 Store in a well-ventilated place. Keep cool.
- P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

**3 Composition/information on ingredients**

· **Chemical characterization: Mixtures**

· **Description:**

Mixture: consisting of the following components.

(Contd. on page 3)



Trade name: **MLH14, MLH16 Metallock Hardener**

(Contd. of page 2)

Weight percentages

· <b>Dangerous components:</b>		
1330-20-7	xylene	30 - 40%
98-56-6	4-chloro-alpha,alpha,alpha-trifluorotoluene	13 - 30%
71-36-3	butan-1-ol	13 - 30%
	Amine proprietary	
90-72-2	2,4,6-tris(dimethylaminomethyl)phenol	1.5 - 5%

#### 4 First-aid measures

- **Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

#### 5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

#### 6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Use neutralizing agent.  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

USA

(Contd. on page 4)



Trade name: MLH14, MLH16 Metallock Hardener

(Contd. of page 3)

## 7 Handling and storage

- **Handling:**
- **Precautions for safe handling**  
No special measures required.  
Ensure good ventilation/exhaustion at the workplace.  
Prevent formation of aerosols.
- **Information about protection against explosions and fires:**  
Keep ignition sources away - Do not smoke.  
Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

## \* 8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**

### · Components with limit values that require monitoring at the workplace:

#### 1330-20-7 xylene

PEL	Long-term value: 435 mg/m <sup>3</sup> , 100 ppm
REL	Short-term value: 655 mg/m <sup>3</sup> , 150 ppm Long-term value: 435 mg/m <sup>3</sup> , 100 ppm
TLV	Short-term value: 651 mg/m <sup>3</sup> , 150 ppm Long-term value: 434 mg/m <sup>3</sup> , 100 ppm BEI

#### 71-36-3 butan-1-ol

PEL	Long-term value: 300 mg/m <sup>3</sup> , 100 ppm
REL	Ceiling limit value: 150 mg/m <sup>3</sup> , 50 ppm Skin
TLV	Long-term value: 61 mg/m <sup>3</sup> , 20 ppm

### · Ingredients with biological limit values:

#### 1330-20-7 xylene

BEI	1.5 g/g creatinine Medium: urine Time: end of shift Parameter: Methylhippuric acids
-----	--

- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
Keep away from foodstuffs, beverages and feed.  
Immediately remove all soiled and contaminated clothing.

(Contd. on page 5)

**Trade name: MLH14, MLH16 Metallock Hardener**

(Contd. of page 4)

Wash hands before breaks and at the end of work.

Avoid contact with the skin.

Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

**9 Physical and chemical properties**

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· <b>Form:</b>	Liquid
· <b>Color:</b>	According to product specification
· <b>Odor:</b>	Characteristic
· <b>Odor threshold:</b>	Not determined.

· **pH-value:** Not determined.

· **Change in condition**

· <b>Melting point/Melting range:</b>	Undetermined.
· <b>Boiling point/Boiling range:</b>	> 66 °C

· **Flash point:** 30 °C

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 340 °C

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

(Contd. on page 6)



Trade name: MLH14, MLH16 Metallock Hardener

(Contd. of page 5)

· <b>Danger of explosion:</b>	<i>In use, may form flammable/explosive vapour-air mixture.</i>
· <b>Explosion limits:</b>	
Lower:	1.1 Vol %
Upper:	9.4 Vol %
· <b>Vapor pressure at 20 °C:</b>	6.7 hPa
· <b>Density at 20 °C:</b>	0.97169 g/cm <sup>3</sup>
· <b>Relative density</b>	<i>Not determined.</i>
· <b>Vapor density</b>	<i>Not determined.</i>
· <b>Evaporation rate</b>	<i>Not determined.</i>
· <b>Solubility in / Miscibility with Water:</b>	<i>Not miscible or difficult to mix.</i>
· <b>Partition coefficient (n-octanol/water):</b>	<i>Not determined.</i>
· <b>Viscosity:</b>	
Dynamic:	<i>Not determined.</i>
Kinematic:	<i>Not determined.</i>
· <b>Solvent content:</b>	
Organic solvents:	80.1 %
VOC content:	55.4 %
	655.7 g/l / 5.47 lb/gl
· <b>Solids content:</b>	19.9 %
· <b>Other information</b>	<i>No further relevant information available.</i>

**10 Stability and reactivity**

- **Reactivity** *No further relevant information available.*
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** *No decomposition if used according to specifications.*
- **Possibility of hazardous reactions** *No dangerous reactions known.*
- **Conditions to avoid** *No further relevant information available.*
- **Incompatible materials:** *No further relevant information available.*
- **Hazardous decomposition products:** *No dangerous decomposition products known.*

**11 Toxicological information**

- **Information on toxicological effects**
- **Acute toxicity:**

· <b>LD/LC50 values that are relevant for classification:</b>		
<b>1330-20-7 xylene</b>		
Oral	LD50	4300 mg/kg (rat)
Dermal	LD50	2000 mg/kg (rabbit)
<b>71-36-3 butan-1-ol</b>		
Oral	LD50	790 mg/kg (rat)
Dermal	LD50	3400 mg/kg (rabbit)

(Contd. on page 7)



Trade name: **MLH14, MLH16 Metallock Hardener**

(Contd. of page 6)

Inhalative	LC50/4 h	8000 mg/l (rat)
------------	----------	-----------------

· **Primary irritant effect:**

- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Strong irritant with the danger of severe eye injury.

· **Sensitization:** No sensitizing effects known.

· **Additional toxicological information:**

The product shows the following dangers according to internally approved calculation methods for preparations:  
Irritant

· **Carcinogenic categories**

· **IARC (International Agency for Research on Cancer)**

1330-20-7	xylene	3
-----------	--------	---

3

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

**12 Ecological information**

· **Toxicity**

- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability:** No further relevant information available.

· **Behavior in environmental systems:**

- **Bioaccumulative potential:** No further relevant information available.
- **Mobility in soil:** No further relevant information available.

· **Additional ecological information:**

· **General notes:**

Water hazard class 2 (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.  
Must not reach bodies of water or drainage ditch undiluted or unneutralized.  
Danger to drinking water if even small quantities leak into the ground.

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects:** No further relevant information available.

**13 Disposal considerations**

· **Waste treatment methods**

· **Recommendation:**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

· **Uncleaned packagings:**

- **Recommendation:** Disposal must be made according to official regulations.



USA

(Contd. on page 8)

Trade name: MLH14, MLH16 Metallock Hardener

(Contd. of page 7)

**14 Transport information**

· UN-Number	UN1263
· DOT, ADR, IMDG, IATA	
· UN proper shipping name	Paint
· DOT, IATA	
· ADR	1263 Paint, special provision 640E
· IMDG	PAINT
· Transport hazard class(es)	
· DOT	
	
· Class	3 Flammable liquids
· Label	3
· ADR, IMDG, IATA	
	
· Class	3 Flammable liquids
· Label	3
· Packing group	
· DOT, ADR, IMDG, IATA	III
· Environmental hazards:	
· Marine pollutant:	No
· Special precautions for user	Warning: Flammable liquids
· EMS Number:	F-E,S-E
· Stowage Category	A
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	
· DOT	
· Quantity limitations	On passenger aircraft/rail: 60 L On cargo aircraft only: 220 L
· ADR	
· Excepted quantities (EQ)	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· IMDG	
· Limited quantities (LQ)	5L
· Excepted quantities (EQ)	Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml

(Contd. on page 9)

Trade name: **MLH14, MLH16 Metallock Hardener**

(Contd. of page 8)

· UN "Model Regulation": UN 1263 PAINT, SPECIAL PROVISION 640E, 3, III

**15 Regulatory information**

- Safety, health and environmental regulations/legislation specific for the substance or mixture
- Sara

· Section 355 (extremely hazardous substances):

None of the ingredient is listed.

· Section 313 (Specific toxic chemical listings):

1330-20-7 xylene

71-36-3 butan-1-ol

· TSCA (Toxic Substances Control Act):

1330-20-7 xylene

98-56-6 4-chloro-alpha,alpha,alpha-trifluorotoluene

71-36-3 butan-1-ol

90-72-2 2,4,6-tris(dimethylaminomethyl)phenol

· Proposition 65

· Chemicals known to cause cancer:

1330-20-7 xylene

· Chemicals known to cause reproductive toxicity for females:

None of the ingredients is listed.

· Chemicals known to cause reproductive toxicity for males:

None of the ingredients is listed.

· Chemicals known to cause developmental toxicity:

None of the ingredients is listed.

· Cancerogenity categories

· EPA (Environmental Protection Agency)

1330-20-7 xylene I

71-36-3 butan-1-ol D

· TLV (Threshold Limit Value established by ACGIH)

1330-20-7 xylene A4

· NIOSH-Ca (National Institute for Occupational Safety and Health)

None of the ingredients is listed.

· GHS label elements The product is classified and labeled according to the Globally Harmonized System (GHS).

· Hazard pictograms



GHS02 GHS05 GHS07

· Signal word **Danger**

(Contd. on page 10)

**Trade name: MLH14, MLH16 Metallock Hardener**

(Contd. of page 9)

· **Hazard-determining components of labeling:**

butan-1-ol  
4-chloro-alpha,alpha,alpha-trifluorotoluene  
Amine proprietary

· **Hazard statements**

H226 Flammable liquid and vapor.  
H315 Causes skin irritation.  
H318 Causes serious eye damage.  
H335-H336 May cause respiratory irritation. May cause drowsiness or dizziness.

· **Precautionary statements**

P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.  
P241 Use explosion-proof electrical/ventilating/lighting/equipment.  
P261 Avoid breathing dust/fume/gas/mist/vapors/spray  
P280 Wear protective gloves / eye protection / face protection.  
P240 Ground/bond container and receiving equipment.  
P242 Use only non-sparking tools.  
P243 Take precautionary measures against static discharge.  
P264 Wash thoroughly after handling.  
P271 Use only outdoors or in a well-ventilated area.  
P303+P361+P353 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.  
P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P310 Immediately call a POISON CENTER/doctor.  
P321 Specific treatment (see on this label).  
P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P332+P313 If skin irritation occurs: Get medical advice/attention.  
P370+P378 In case of fire: Use for extinction: CO2, powder or water spray.  
P362+P364 Take off contaminated clothing and wash it before reuse.  
P405 Store locked up.  
P403+P233 Store in a well-ventilated place. Keep container tightly closed.  
P403+P235 Store in a well-ventilated place. Keep cool.  
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## 16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing SDS:** Environment protection department.

· **Contact:** Steve Gaver (sgaver@semproducts.com)

· **Date of preparation / last revision** 02/22/2016 / 6

· **Abbreviations and acronyms:**

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)  
ICAO: International Civil Aviation Organisation  
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)  
IMDG: International Maritime Code for Dangerous Goods  
DOT: US Department of Transportation  
IATA: International Air Transport Association  
ACGIH: American Conference of Governmental Industrial Hygienists

(Contd. on page 11)



Printing date 02/22/2016

Reviewed on 01/08/2016

**Trade name: MLH14, MLH16 Metallock Hardener**

(Contd. of page 10)

EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
CAS: Chemical Abstracts Service (division of the American Chemical Society)  
NFPA: National Fire Protection Association (USA)  
HMIS: Hazardous Materials Identification System (USA)  
VOC: Volatile Organic Compounds (USA, EU)  
LC50: Lethal concentration, 50 percent  
LD50: Lethal dose, 50 percent  
PBT: Persistent, Bioaccumulative and Toxic  
vPvB: very Persistent and very Bioaccumulative  
NIOSH: National Institute for Occupational Safety  
OSHA: Occupational Safety & Health  
TLV: Threshold Limit Value  
PEL: Permissible Exposure Limit  
REL: Recommended Exposure Limit  
BEI: Biological Exposure Limit  
Flam. Liq. 3: Flammable liquids, Hazard Category 3  
Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2  
Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1  
STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3  
· **\* Data compared to the previous version altered.**

USA