



Arm & Hammer™ Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations
Revision Date: 06/02/2015 Date of issue: 06/02/2015

Version: 1.0

SECTION 1: IDENTIFICATION

Product Identifier

Product Form: Mixture

Product Name: Arm & Hammer™ Trash Can & Dumpster Deodorizer

Synonyms: Deodorizer

Intended Use of the Product

Deodorizer.

Name, Address, and Telephone of the Responsible Party

Company

Church & Dwight
500 Charles Ewing Blvd
Ewing Township, NJ 08628
T 1-800-236-4175

www.churchdwight.com

Emergency Telephone Number

Emergency Number : For Medical Emergency: 1-888-234-1828, For Chemical Emergency: 1-800-424-9300 (CHEMTREC)

SECTION 2: HAZARDS IDENTIFICATION

Classification of the Substance or Mixture

Classification (GHS-US)

Not classified

Label Elements

GHS-US Labeling

No labeling applicable

Other Hazards

May cause an allergic reaction in sensitive individuals. Exposure may aggravate those with pre-existing eye, skin, or respiratory conditions.

Unknown Acute Toxicity (GHS-US) Not available

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Mixture

Name	Product Identifier	% (w/w)	Classification (GHS-US)
Sodium bicarbonate	(CAS No) 144-55-8	60 - 100	Not classified
Calcium silicate	(CAS No) 1344-95-2	0.1 - 1	Not classified

SECTION 4: FIRST AID MEASURES

Description of First Aid Measures

General: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice.

Inhalation: When symptoms occur: go into open air and ventilate suspected area.

Skin Contact: Brush off loose particles from skin. Rinse immediately with plenty of water. Obtain medical attention if irritation develops or persists.

Eye Contact: Rinse cautiously with water for at least 15 minutes. Remove contact lenses, if present and easy to do so. Continue rinsing. Obtain medical attention if irritation persists.

Ingestion: Rinse mouth. Do not induce vomiting. Seek medical attention if a large amount is swallowed.

Most Important Symptoms and Effects Both Acute and Delayed

General: None expected under normal conditions of use.

Inhalation: Prolonged inhalation of dust may cause respiratory irritation.

Arm & HammerTM Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Skin Contact: Skin contact with large amounts of dust may cause mechanical irritation.

Eye Contact: Contact may cause irritation due to mechanical abrasion.

Ingestion: Large doses may produce systemic alkalosis and expansion in extracellular fluid volume with edema.

Chronic Symptoms: None expected under normal conditions of use.

Indication of Any Immediate Medical Attention and Special Treatment Needed

If exposed or concerned, get medical advice and attention.

SECTION 5: FIRE-FIGHTING MEASURES

Extinguishing Media

Suitable Extinguishing Media: Use extinguishing media appropriate for surrounding fire.

Unsuitable Extinguishing Media: For surrounding fire. Use of heavy stream of water may spread fire.

Special Hazards Arising From the Substance or Mixture

Fire Hazard: Not flammable. Under fire conditions, hazardous fumes will be present.

Explosion Hazard: Product is not explosive.

Reactivity: Hazardous reactions will not occur under normal conditions.

Advice for Firefighters

Precautionary Measures Fire: Wear self-contained breathing apparatus when entering area unless atmosphere is proved to be safe.

Firefighting Instructions: Exercise caution when fighting any chemical fire.

Protection During Firefighting: Do not enter fire area without proper protective equipment, including respiratory protection.

Hazardous Combustion Products: Carbon oxides (CO, CO₂). Sodium oxides.

Reference to Other Sections

Refer to section 9 for flammability properties.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions, Protective Equipment and Emergency Procedures

General Measures: Do not breathe dust or fumes. Avoid skin and eye contact. Handle in accordance with good industrial hygiene and safety practice.

For Non-Emergency Personnel

Protective Equipment: Use appropriate personal protection equipment (PPE).

Emergency Procedures: Evacuate unnecessary personnel.

For Emergency Personnel

Protective Equipment: Equip cleanup crew with proper protection.

Emergency Procedures: Upon arrival at the scene, a first responder is expected to recognize the presence of dangerous goods, protect oneself and the public, secure the area, and call for the assistance of trained personnel as soon as conditions permit.

Environmental Precautions Prevent entry to sewers and public waters. Avoid release to the environment.

Methods and Material for Containment and Cleaning Up

For Containment: Contain and collect as any solid.

Methods for Cleaning Up: Clean up spills immediately and dispose of waste safely. Avoid generation of dust during clean-up of spills. Keep in suitable, closed containers for disposal. Contact competent authorities after a spill.

Reference to Other Sections

See Section 8, Exposure Controls and Personal Protection. See Section 13, Disposal Considerations.

SECTION 7: HANDLING AND STORAGE

Precautions for Safe Handling

Additional Hazards When Processed: When heated, material emits irritating fumes.

Hygiene Measures: Handle in accordance with good industrial hygiene and safety procedures. Wash hands and other exposed areas with mild soap and water before eating, drinking, or smoking and again when leaving work.

Conditions for Safe Storage, Including Any Incompatibilities

Storage Conditions: Store in a dry, cool and well-ventilated place. Keep container closed when not in use.

Incompatible Materials: Acids. Water.

Storage Temperature: < 65 °C (150 °F)

Specific End Use(s) Deodorizer.

Arm & HammerTM Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

For substances listed in section 3 that are not listed here, there are no established Exposure limits from the manufacturer, supplier, importer, or the appropriate advisory agency including: ACGIH (TLV), NIOSH (REL), OSHA (PEL), Canadian provincial governments, or the Mexican government

Calcium silicate (1344-95-2)		
Mexico	OEL TWA (mg/m ³)	10 mg/m ³ (inhalable fraction)
USA ACGIH	ACGIH TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous-particulate matter containing no asbestos and <1% crystalline silica)
USA ACGIH	ACGIH chemical category	Not Classifiable as a Human Carcinogen synthetic nonfibrous
USA OSHA	OSHA PEL (TWA) (mg/m ³)	15 mg/m ³ (total dust) 5 mg/m ³ (respirable fraction)
USA NIOSH	NIOSH REL (TWA) (mg/m ³)	10 mg/m ³ (total dust) 5 mg/m ³ (respirable dust)
Alberta	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic, nonfibrous)
British Columbia	OEL TWA (mg/m ³)	10 mg/m ³ (total particulate matter containing no Asbestos and <1% Crystalline silica-total particulate) 3 mg/m ³ (particulate matter containing no Asbestos and <1% Crystalline silica-respirable particulate)
Manitoba	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous, particulate matter containing no Asbestos and <1% Crystalline silica)
New Brunswick	OEL TWA (mg/m ³)	10 mg/m ³ (particulate matter containing no Asbestos and <1% Crystalline silica)
Newfoundland & Labrador	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous, particulate matter containing no asbestos and <1% crystalline silica)
Nova Scotia	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous, particulate matter containing no Asbestos and <1% Crystalline silica)
Nunavut	OEL TWA (mg/m ³)	5 mg/m ³ (respirable mass) 10 mg/m ³ (total mass)
Northwest Territories	OEL TWA (mg/m ³)	5 mg/m ³ (respirable mass) 10 mg/m ³ (total mass)
Ontario	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous, containing no Asbestos and <1% Crystalline silica)
Prince Edward Island	OEL TWA (mg/m ³)	10 mg/m ³ (synthetic nonfibrous; particulate matter containing no Asbestos and <1% Crystalline silica)
Québec	VEMP (mg/m ³)	10 mg/m ³ (synthetic, containing no Asbestos and <1% Crystalline silica-total dust)
Saskatchewan	OEL STEL (mg/m ³)	20 mg/m ³ (nonfibrous)
Saskatchewan	OEL TWA (mg/m ³)	10 mg/m ³ (nonfibrous)
Yukon	OEL TWA (mg/m ³)	30 mppcf 10 mg/m ³

Exposure Controls

Appropriate Engineering Controls: Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure. Ensure adequate ventilation, especially in confined areas. Ensure all national/local regulations are observed.

Personal Protective Equipment: Gloves. Safety glasses. Dust formation: dust mask.



Materials for Protective Clothing: Chemically resistant materials and fabrics.

Hand Protection: Wear chemically resistant protective gloves.

Arm & HammerTM Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Eye Protection: Chemical safety goggles.

Respiratory Protection: Use a NIOSH-approved respirator or self-contained breathing apparatus whenever exposure may exceed established Occupational Exposure Limits.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Information on Basic Physical and Chemical Properties

Physical State	: Solid
Appearance	: White Granular
Odor	: As per label
Odor Threshold	: Not available
pH	: 8.2
Evaporation Rate	: Not available
Melting Point	: Not available
Freezing Point	: Not available
Boiling Point	: Not available
Flash Point	: Not available
Auto-ignition Temperature	: Not available
Decomposition Temperature	: Not available
Flammability (solid, gas)	: Not available
Upper/Lower Flammable Limit	: Not available
Vapor Pressure	: Not available
Relative Vapor Density at 20 °C	: Not available
Specific Gravity	: ≈ 1 @ 20 °C
Solubility	: Water: 8 % @ 20 °C
Partition Coefficient: N-Octanol/Water	: Not available
Viscosity	: Not available
Explosion Data – Sensitivity to Mechanical Impact	: Not expected to present an explosion hazard due to mechanical impact.
Explosion Data – Sensitivity to Static Discharge	: Not expected to present an explosion hazard due to static discharge.

SECTION 10: STABILITY AND REACTIVITY

Reactivity: Hazardous reactions will not occur under normal conditions.

Chemical Stability: Decomposes slowly on exposure to water (moisture).

Possibility of Hazardous Reactions: Hazardous polymerization will not occur.

Conditions to Avoid: Exposure to moisture or moist air. Temperatures above 150°F (65.6°C).

Incompatible Materials: Acids. Water. Lime.

Hazardous Decomposition Products: None known. At high temperature may liberate toxic gases.

SECTION 11: TOXICOLOGICAL INFORMATION

Information on Toxicological Effects - Product

Acute Toxicity: Not classified

LD50 and LC50 Data: Not available

Skin Corrosion/Irritation: Not classified

Serious Eye Damage/Irritation: Not classified

Respiratory or Skin Sensitization: Not classified

Germ Cell Mutagenicity: Not classified

Teratogenicity: Not classified

Carcinogenicity: Not classified

Specific Target Organ Toxicity (Repeated Exposure): Not classified

Reproductive Toxicity: Not classified

Specific Target Organ Toxicity (Single Exposure): Not classified

Aspiration Hazard: Not classified

Symptoms/Injuries After Inhalation: Prolonged inhalation of dust may cause respiratory irritation.

Symptoms/Injuries After Skin Contact: Skin contact with large amounts of dust may cause mechanical irritation.

Symptoms/Injuries After Eye Contact: Contact may cause irritation due to mechanical abrasion.

Chronic Symptoms: None expected under normal conditions of use.

Arm & Hammer™ Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

Information on Toxicological Effects - Ingredient(s)

LD50 and LC50 Data:

Calcium silicate (1344-95-2)	
LD50 Oral Rat	3400 mg/kg
Sodium bicarbonate (144-55-8)	
LD50 Oral Rat	7.3 g/kg

SECTION 12: ECOLOGICAL INFORMATION

Toxicity

Ecology - General: Not classified.

Sodium bicarbonate (144-55-8)	
LC50 Fish 1	8250 - 9000 mg/l (Exposure time: 96 h - Species: Lepomis macrochirus [static])
EC50 Daphnia 1	2350 mg/l (Exposure time: 48 h - Species: Daphnia magna)

Persistence and Degradability Not available

Bioaccumulative Potential Not available

Mobility in Soil Not available

Other Adverse Effects Not available

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Recommendations: Dispose of waste material in accordance with all local, regional, national, provincial, territorial and international regulations.

SECTION 14: TRANSPORT INFORMATION

In Accordance with DOT Not regulated for transport

In Accordance with IMDG Not regulated for transport

In Accordance with IATA Not regulated for transport

In Accordance with TDG Not regulated for transport

SECTION 15: REGULATORY INFORMATION

US Federal and International Regulations

Calcium silicate (1344-95-2) Listed on the AICS (Australian Inventory of Chemical Substances) Listed on the Canadian DSL (Domestic Substances List) Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China) Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances) Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory Listed on the Korean ECL (Existing Chemicals List) Listed on NZIoC (New Zealand Inventory of Chemicals) Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances) Listed on the United States TSCA (Toxic Substances Control Act) inventory
Sodium bicarbonate (144-55-8) Listed on the AICS (Australian Inventory of Chemical Substances) Listed on the Canadian DSL (Domestic Substances List) Listed on IECSC (Inventory of Existing Chemical Substances Produced or Imported in China) Listed on the EEC inventory EINECS (European Inventory of Existing Commercial Chemical Substances) Listed on the Japanese ENCS (Existing & New Chemical Substances) inventory Listed on the Korean ECL (Existing Chemicals List) Listed on NZIoC (New Zealand Inventory of Chemicals) Listed on PICCS (Philippines Inventory of Chemicals and Chemical Substances) Listed on the United States TSCA (Toxic Substances Control Act) inventory

US State Regulations

Calcium silicate (1344-95-2) U.S. - Massachusetts - Right To Know List U.S. - New Jersey - Right to Know Hazardous Substance List
--

Arm & Hammer™ Trash Can & Dumpster Deodorizer

Safety Data Sheet

According To Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules And Regulations

U.S. - Pennsylvania - RTK (Right to Know) List

Canadian Regulations

Arm & Hammer™ Trash Can & Dumpster Deodorizer

WHMIS Classification	Uncontrolled product according to WHMIS classification criteria
----------------------	---

Calcium silicate (1344-95-2)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification	Uncontrolled product according to WHMIS classification criteria
----------------------	---

Sodium bicarbonate (144-55-8)

Listed on the Canadian DSL (Domestic Substances List)

WHMIS Classification	Uncontrolled product according to WHMIS classification criteria
----------------------	---

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all of the information required by CPR.

SECTION 16: OTHER INFORMATION, INCLUDING DATE OF PREPARATION OR LAST REVISION

Revision Date : 06/02/2015

Other Information : This document has been prepared in accordance with the SDS requirements of the OSHA Hazard Communication Standard 29 CFR 1910.1200.

Party Responsible for the Preparation of This Document

Church & Dwight
500 Charles Ewing Blvd
Ewing Township, NJ 08628
T 1-800-236-4175

This Product Safety Data Sheet is offered solely for your information, consideration and investigation. Church & Dwight Co., Inc. provides no warranties; either expressed or implied, and assumes no responsibility for the accuracy or completeness of data contained herein. Church & Dwight Co., Inc. urges persons receiving this information to make their own determination as to the information suitability for their particular application.

Church&Dwight NA GHS SDS