


Part #	Power			Capacitor: 70µF/250V (MA0460X-9); 30µF/450V (MA0460X-9A)	Flow GPM								Weight (lbs)
	HP	Volt	Amp		0	4.6	8.8	17.5	20.2	22.3	24.2	25.5	
MA0460X-9 SS.MA0460X-9-115	1	115	12	Head (ft)	247	234	227	150	91	79	49	24	28
MA0460X-9A SS.MA0460X-9A-230	1	230	5.8	Head (ft)	247	234	227	150	91	79	49	24	28

A	B	C	D	E	MAX
33.2"	17.3"	17.7"	1.25" NPT	3.5"	3.8"

### Features & Technical Specifications:

- 3.8" deep well submersible pump, 9 stage, 240 feet max head (open tank).
- Patented impeller provides high flow: 25GPM (max), 13 GPM (rated).
- Water temperature: (32 ~113°F) Trans medium's Ph: 6.5~ 8.5
- Solid stainless steel body with heavy duty cast iron or stainless discharge
- Industrial grade heavy duty, also good for home usage
- Built in capacitor start, and thermal protection for longer life and powerful start.
- Built in control box. This pump DOES NOT require an external control box!
- This pump uses high quality UL approved motor, UL file No.: E233961
- This is a 2 wire pump with 3-Wire (2 wires + ground wire)
- 10' long electric cord comes with this submersible deep well pump.
- 1¼" NPT discharge. No check valve for easy winterization.
- Designed to fit inside 4" ID or larger pipe/well casing
- Heavy-duty thermoplastic impellers, diffusers, and intake screen.
- High efficiency, hermetically sealed motor is thermally protected to prevent overheating



Cool Resistance (Ω): 1.17 (115V), 3.87 (220V)