

MAX1100 S - HDS



1177 x 450 x H158 mm
46.34 x 17.72 x 6.22 inch



1100 x 370 x H140 mm
43.30 x 14.57 x 5.51 inch



45 + 95 mm
1.77 + 3.74 inch



S : 8,82 kg / 19.44 lb
HDS : 10,25 kg / 22.59 lb



-51 / 90 °C / -59.8 / 194° F




Capacità / Capacity
56.98 lt



Stampaggio: ad iniezione
Process: Injection molding



Materiale / Materials
POLIPROPILENE/POLYPROPYLENE
NYLON (Serrature / Latches)
Assale Ruote in ACCIAIO INOX /
Stainless steel wheel pins
POLIURETANO/POLYURETHANE
(Spugna / foam)



VIDEO S & HDS



- Guarnizione ermetica / Watertight seal around lid
- Valvola automatica di pressurizzazione
Automatic pressure release valve
- Sistema di impilabilità / Stackable interlocking system
- Resistenza agli urti / Thick body material
- Chiusure di sicurezza a doppio step / Easy to open double throw latches
- Manico morbido ad alta ergonomia / Load tested soft grip handle
- Pareti spesse ANTIURTO / Thick body material
- Punti di fissaggio per varie applicazioni / Extra fixing points
- Cerniera lungo tutto il profilo della valigia / Fully length hinges
- Perni in nylon ANTI corrosione / Nylon pins corrosion free

Shipping & Logistic info

1 pz. per cartone
1 pc. x carton



10,17 Kg per cartone
22.42 lb gross weight



IP67

RATING


MIL SPECS

DEF STAN 81-41
STANAG 4280
MIL STD 810G

ATA300



SCREEN PRINTING &
CUSTOM LABEL
SERIGRAFIA &
ETICHETTA CUSTOM



CUSTOMIZED
FOAM INLAY
INTERNI IN SPUGNA
FUSTELLATA



LASER MARKING
OR ENGRAVING
INCISIONE O
MARCATURA LASER



CUSTOM COLOUR
COLORI CUSTOM