

Garant**Circular mill, Carbide, Type: 18L****Order data**

Order number	217252 18L
GTIN	4045197216533
Item class	21Q

Description**Note:**

The actual groove depth $S_{\max}$ is calculated as follows: $(D-d_1) / 2$.

Technical description

maximum cutting depth $S_{\max}$	5 mm
Shank $\varnothing D_s$ h6	12 mm
Internal $\varnothing d_1$	12 mm
smallest hole $\varnothing D$	14 - 22 mm
Overall length L_{tot}	86.5 mm
Overhang L_1	37.4 mm
Shank type	cylindrical
Set of insert screws	219818 (8IP; 1.2 Nm)
Shank	DIN 6535 HA
for insert type	P16
Through-coolant	yes
Thread depth	35.4 mm
Material of milling tool	Carbide
Tool exchange	PowerCard

Type of product	Circular mills
-----------------	----------------

Accessories

Set of insert screws10-piece	219818
------------------------------	--------