

Flexible metallic conduit fittings

Squeeze type – zinc die cast

SQUEEZE TYPE – ZINC DIE CAST

Applications:

- Used to squeeze and secure AC/MC cable to a box or enclosure

Features:

- Zinc connectors assembled with die cast locknuts and zinc plated screws
- 105°C temperature rating
- Used with armored cable and flexible metal conduit
- Male threads – NPSM

Standard materials:

- Zinc die cast
- Zinc die cast locknut

Standard finish:

- Natural

Squeeze type[®] 90° angle – insulated

UL File No. 19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
1724DC	3/8"	50	8
1736DC	1/2"	25	11
1738DC	3/4"	10	15
1739DC	1"	5	25
1740DC	1 1/4"	10	41
1741DC	1 1/2"	1	117
1742DC	2"	1	119
1744DC	2 1/2"	1	286
1745DC	3"	1	405
1746DC	3 1/2"	1	560
1747DC	4"	1	642

⁵UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class 1, Division 2, NEC 501-4(b).

Squeeze type[®] 90° angle – non-insulated

UL File No. 19189



Cat. #	Trade size	Unit qty.	Wt. lbs. per 100
724DC ¹	3/8"	50	8
736DC	1/2"	25	11
738DC ²	3/4"	10	15
739DC	1"	5	25
740DC	1 1/4"	10	41
741DC	1 1/2"	1	117
742DC	2"	1	119
744DC	2 1/2"	1	286
745DC	3"	1	405
746DC	3 1/2"	1	560
747DC	4"	1	642

²UL approved for use with aluminum interlocking grounding metal-clad cable, Type MClA (Southwire MCAP[®]).

MCAP[®] is a registered trademark of Southwire Company.

⁵UL Listed flexible metallic conduit fittings are suitable as grounding means under NEC 350-5 and suitable for hazardous location use per Class 1, Division 2, NEC 501-4(b).

¹UL approved for use with MC-PCS cable.