



METAL HANGER STRAP TECHNICAL SPECIFICATION

Job Name _____	Item # _____
Location _____	
Engineer _____	Contractor _____
PO # _____	Tag _____
Representative _____	

SPECIFICATIONS

Oatey Metal Hanger Strap provides a fast and economical method for hanging piping. Metal Hanger Strap can be used as a pipe hanger, conduit and duct hanger, tubing strap, utility strap and more. Metal Hanger Strap has alternating (1/4 in. and 1/8 in. diameter) nail holes to speed installation.

APPLICATION / USES

- Provides a fast and economical method for hanging piping. Metal Hanger Strap can be used as a pipe hanger, conduit and duct hanger, tubing strap, utility strap and more.
- Consult Oatey Technical Department for applications not specifically referenced above.

PHYSICAL PROPERTIES

Material	24 Gauge Copper 24/28 Gauge Galvanized Steel
Safe Work Load	Copper Strap= 70 lbs. Galvanized Strap = 46 lbs.



PRECAUTIONS

Check with local codes to ensure proper spacing requirements for piping support. Read cautions and directions on packaging carefully before using this product. KEEP OUT OF REACH OF CHILDREN.

PRODUCT SELECTOR

METAL HANGER STRAP				
✓	Product Number	Description	Pack	Carton Weight
	33918	¾ in. x 10 ft. Copper Plated Steel Hanger Strap – 24 Gauge (bagged)	12	5 lbs.
	33730	¾ in. x 10 ft. Galvanized Hanger Strap – 24 Gauge (bagged)	12	24 lbs.
	33923	¾ in. x 10 ft. Galvanized Hanger Strap – 28 Gauge (bagged)	12	6 lbs.
	33929	¾ in. x 25 ft. Galvanized Hanger Strap – 28 Gauge (bagged)	12	10 lbs.
	33922	¾ in. x 50 ft. Galvanized Hanger Strap – 28 Gauge (boxed)	10	24 lbs.
	33889	¾ in. x 100 ft. Galvanized Hanger Strap – 28 Gauge (boxed)	10	52 lbs.

Access BIM/Revit content through www.oatey.com