ABB BALDOR RELIANCE

Customer information packet

L1319T

1.5HP, 1740RPM, 1PH, 60HZ, 145T, 3528L, OPEN, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 4:07:37 PM

Specifications

Enclosure	OPEN
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Induction Run
Output @ Frequency	1.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	18.600 A @ 115.0 V
	9.200 A @ 208.0 V
	9.300 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	66.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	9.3 a
Insulation Class	F

Part Detail

Revision	C
Type	AC
Mech. spec.	35DD001
Base	
Status	PRD/A
Elec. spec.	35WGG408
Layout	35LYDD001
Eff. date	07-02-2024
CD Diagram	CD0001
Poles	04
Leads	4#16 A PH,2#18 B PH Y
Proprietary	False
Created date	02-23-2023

Inverter Code	Not Inverter
IP Rating	NONE
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	4 @ 16 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3528L
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.13 IN
Power Factor	78
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1740 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L								
CAT.NO.	L1319T							
SPEC.	35DD001G408							
HP	1.5							
VOLTS	115/230							
AMP	18.6/9.3							
RPM	1740							
FRAME	145T	**HZ**	60			**PH**	1	
SER.F.	1.15	**CODE**	K	**DES**	L	**CLASS**	F	
NEMA-NOM-EFF	66	**PF**	78					
RATING	40C AMB-CONT							
CC								
DE	6205	**ODE**	6203					
ENCL	OPEN	**SN**						

Accessories

Part number	Description	Multiplier
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	

AC Induction Motor Performance Data
Record # 89158
Typical performance - not guaranteed values

Winding: 35WGG408-R001	**Type:** 3528L	**Enclosure:** OPEN

Nameplate Data				**115 V, 60 Hz: Low Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	4.49 LB-FT
Volts			115/230	**Start Configuration**	direct on line
Full Load Amps			18.6/9.3	**Breakdown Torque**	11.26 LB-FT
R.P.M.			1740	**Pull-up Torque**	10.23 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	14.53 LB-FT
NEMA Design Code	L	**KVA Code**	K	**Starting Current**	116 A
Service Factor (S.F.)			1.15	**No-load Current**	12.73 A
NEMA Nom. Eff.	66	**Power Factor**	78	**Line-line Res. @ 25ºC**	0.503 Ω A Ph 1.14 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	59°C
S.F. Amps				**Temp. Rise @ S.F. Load**	68°C
				Locked-rotor Power Factor	94.9
				Rotor inertia	0.203 lb-ft²

Load Characteristics 115 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	39	56	70	78	85	87	82
Efficiency	48.4	62.7	64.3	66.8	65.1	64	65.8
Speed	1791	1782	1768	1742	1726	1698	1732
Line amperes	13.16	14.14	16.31	18.62	21.62	25.38	20.4


ABB Motors and Mechanical Inc.


WINDING # 35WGG408

1.5 HP 1 PH 60 HZ 1740 RPM 115 V 3528L


Typical performance - not guaranteed values.

TORQUES(LB-FT): PO=11.26 PU=10.23 LR=14.53 LRA=116




35LYDD001
510-520 = 11.12
521-528 = 12.13
529-535 = 13.00
536-546 = 14.38
2.60
2.50
2.25
NAMEPLATE
.19 KEY
1.38 LONG
Ø .8750
.8745
4.00
2.25
6 HOLES
.34 DIA.
5.00
.50
5.94
Ø 6.62
5.61
2.17
6.77
3.50
3.44
LEAD HOLE
1.09 DIA.
2.75
2.75
4.55
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CORRECT OVERALL LENGTH FOR 536-546 STACK RANGE
REV: D
VERSION: 04
REVISED: 03:38:01 11/03/2022
TDR: 000001199141
MODEL NO. 35LYDD001
REF: -
BY: USBUFRA
B
BALDOR - RELIANCE®
STD HORZ 143-5T OPEN 35L W/1.09 DIA. LEAD HOLE
SH 1 OF 1
35LYDD001

CD0001



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0001

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:16	TDR: 0178636
CD0001		FILE: AAA00007405	MDL: –
		MTL: –	TYPE L, DV, REV, 6 LEADS