ABB BALDOR RELIANCE

Customer information packet

CEWDM3615T-5

5HP, 1750RPM, 3PH, 60HZ, 184TC, 3642M, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 1:52:11 PM

Specifications

Enclosure	TEFC
Frame	184TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR
	CSA
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	5.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	5.3 a
Insulation Class	F

Part Detail

Revision	Q
Type	AC
Mech. spec.	36K190
Base	
Status	PRD/A
Elec. spec.	36WGS551
Layout	36LYK190
Eff. date	10-17-2025
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	08-03-2010

Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 16 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3642M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.04 IN
Power Factor	78
Product Family	Wash Down
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1750 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1669L								
CAT.NO.	CEWDM3615T-5							
SPEC.	36K190S551G1							
HP	5							
VOLTS	575							
AMP	5.3							
RPM	1750							
FRAME	184TC	**HZ**	60			**PH**	3	
SER.F.	1.15	**CODE**	J	**DES**	B	**CLASS**	F	
NEMA-NOM-EFF	89.5	**PF**	78					
RATING	40C AMB-CONT							
CC	010A							
DE	6206	**ODE**	6205					
ENCL	TEFC	**SN**						
BLANK	SFA 6							

AC Induction Motor Performance Data
Record # 32022
Typical performance - not guaranteed values

Winding: 36WGS551-R001	**Type:** 3642M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (HP)			5	**Full Load Torque**	14.9 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			5.3	**Breakdown Torque**	52.2 LB-FT
R.P.M.			1750	**Pull-up Torque**	31.6 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	35 LB-FT
NEMA Design Code	B	**KVA Code**	J	**Starting Current**	39.3 A
Service Factor (S.F.)			1.15	**No-load Current**	2.6 A
NEMA Nom. Eff.	89.5	**Power Factor**	78	**Line-line Res. @ 25ºC**	3.57 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	77°C
S.F. Amps				**Temp. Rise @ S.F. Load**	94°C
				Locked-rotor Power Factor	40
				Rotor inertia	0.391 LB-FT2

Load Characteristics 575 V, 60 Hz, 5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	38	60	72	78	83	83	81
Efficiency	84.8	89.6	90.5	89.5	88.5	86.9	88.9
Speed	1789	1776	1762	1750	1733	1714	1740
Line amperes	2.85	3.45	4.35	5.33	6.36	7.72	5.95


ABB Motors and Mechanical Inc.


WINDING # 36WGS551

5 HP 3 PH 60 HZ 1750 RPM 575 V 3642M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=52.2 PU=31.6 LR=35 LRA=39.3





36LYK190
614-623 = 15.17
624-634 = 16.54
635-646 = 18.04
(635-646) ONLY
4.27
2.75
2.62
.25
.25 KEY
1.75 LONG
Ø8.60
NAMEPLATE
8.85
Ø8.500
Ø8.497
1.1250
1.1245
FORSHEDA
SLINGER
(BOTH ENDS)
4 HOLES
3 W/PLUGS
(EA. END)
6 HOLES
.44 DIA.
4.50
.50
5.50
3.50
6.50
Ø7.86
6.91
45°
45°
2.22
8.43
4.50 +.00 -.06
4 HOLES
.50-13 TAP
Ø7.25 B.C.
LEAD HOLE
.75 NPT
3.75
3.75
5.76
4.31
8.63
APPLY SEALER
UNDER RETAINER SCREW
HEADS BEFORE INSTALLING
APPLY COAT OF SEALER
TO HOUSING BEFORE
PRESSING SEAL IN
OPPOSITE DRIVE DETAIL
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT FROM AUTOCAD TO SWD
REV: E
VERSION: 05
REVISED: 02:11:48 10/25/2023
TDR: 000001218972
MODEL NO. 36LYK190
REF: -
BY: USALMAZ
B
BALDOR - RELIANCE®
STD HORZ 182-4TC TEFC 36M WD (S/P #9)
36LYK190


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: E	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1