



MCR
SAFETY

R2

Safety Glasses

Plus Series

Specification Sheet

PRODUCT DESCRIPTION:

The RT2 series has the squared look of trend-setting designer eyewear with the protection that meets ANSI Z87.1 standards. The durability of lightweight metal alloy frames is combined with the custom fit of non-slip rubber head-grips and adjustable PVC nose pads. Available in brass or chrome frames. Rugged polycarbonate lens filters 99.9% of harmful U.V. rays. Choose the best safety glasses, choose MCR Safety!



FEATURES:

- Chrome Frame Color
- Exclusive Duramass® scratch resistant coating
- Adjustable Nose Pads
- Built on Side Shields for added protection
- Non-Slip soft temple material
- Rugged polycarbonate lens filters 99.9% of harmful U.V. rays

TECHNICAL DATA FOR: R2120

Series	R2	ANSI Z87+	Yes
Category	Safety Glasses	AS/NZS 1337.1	Yes
Scratch Resistant	Yes		
Frame Material	Metal		
Packaging	White Inner Box		
Case Pack	144	Case Weight	15.120 lb.
Case Dimensions	20.866 x 11.024 x 11.417	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
R2110	Clear	Duramass Hard Coat	Yes	90	Brass Metal	Brass Metal	Black
R2120	Clear	Duramass Hard Coat	Yes	90	Chrome Metal	Chrome Metal	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2021 MCR Safety - All Rights Reserved