



jalas® 1228W

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2011 S3, SRC, CI, HRO, HI, WG EN ISO 20349-2:2017 S3, SRC, CI, HRO, HI, WG

Learn more

MID-CUT BOOT WITH HIDDEN BOA® FIT SYSTEM

Our most comfortable and durable welding boot with the best possible protection. The BOA® Fit system enables perfect fit and for extra protection it is covered by PU-coated leather. Specially treated leather with heat resistance para-aramid thread in the seams provides a max operating heat limit of 400°C/752°F for 30 minutes. The oil and heat-resistant nitrile outer sole means excellent grip and JALAS® composite toe cap, steel nail penetration insert and double impact protection zones in PORON® XRD® help prevent injuries.

CHARACTERISTICS

- Good grip
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- ProNose toe reinforcement
- KEVLAR® thread in the seams which resists 427° C short-term heat exposure (max operating limit) and 204° C longer-term heat exposure (constant operating limit)
- Heat-resistant upper
- Heat-resistant outsole
- Oil-resistant outsole
- Anti-static properties
- Padded boot shaft
- Ventilating insole
- BOA® Fit System
- Water repellent

BOA DIALED IN. PRECISION FIT. XRD PROTECTION LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, All-year use, Warm surfaces, Environments with risk for outsole penetration, Oily and greasy environments, Dirty environments, Harsh environments

SPECIFICATION

TYPE Safety footwear, Boots/Ankle boots
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Steel
FITTING Regular
UPPER MATERIAL PU-coated leather
PRONOSE MATERIAL PU
TOECAP MATERIAL Composite
LINING MATERIAL Polyamide
INSOLE JALAS 8217 FX2 Climate
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL Nitrile rubber outsole
FASTENING BOA® Fit System
COLOUR Black
NET WEIGHT, (SIZE 42) 1.42 kg

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2011
S3, SRC, CI, HRO, HI, WG

EN ISO 20349-2:2017
S3, SRC, CI, HRO, HI, WG

FEATURES

- Anti-static properties
- Composite toecap
- Ergothan Shock Absorption System
- Heat-resistant upper
- Oil-resistant outsole
- ProNose toe reinforcement
- Nail protection in steel
- Heat-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	1228W-35	6408487523571
36	3	4	5	1228W-36	6408487523618
37	4	5	6	1228W-37	6408487523656
38	5	5.5	6.5	1228W-38	6408487523694
39	6	6.5	7.5	1228W-39	6408487523731
40	6.5	7.5	8.5	1228W-40	6408487523779
41	7	8	9	1228W-41	6408487523816
42	8	9	10	1228W-42	6408487523854
43	9	9.5	11	1228W-43	6408487523892
44	10	10.5	11.5	1228W-44	6408487523939
45	10.5	11	12.5	1228W-45	6408487523977
46	11	12	13	1228W-46	6408487524011
47	12	13	14	1228W-47	6408487524059
48	13	13.5	14.5	1228W-48	6408487524097

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.