



# SAFETY DATA SHEET

## 1. Identification

<b>Important information</b>	*** This Safety Data Sheet is only authorised for use by HP for HP Original products. Any unauthorised use of this Safety Data Sheet is strictly prohibited and may result in legal action being taken by HP. ***
<b>Product identifier</b>	4K0T7Series
<b>Other means of identification</b>	None.
<b>Recommended use</b>	Inkjet printing
<b>Recommended restrictions</b>	None known.
<b>Manufacturer/Importer/Supplier/Distributor information</b>	
	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 United States
<b>Telephone</b>	650-857-1501
<b>HP Inc. health effects line</b>	
<b>(Toll-free within the US)</b>	1-800-457-4209
<b>(Direct)</b>	1-760-710-0048
<b>HP Inc. Customer Care Line</b>	
<b>(Toll-free within the US)</b>	1-800-474-6836
<b>(Direct)</b>	1-208-323-2551
<b>Email:</b>	sustainability@hp.com

## 2. Hazard(s) identification

<b>Physical hazards</b>	Not classified.
<b>Health hazards</b>	Not classified.
<b>Environmental hazards</b>	Not classified.
<b>OSHA defined hazards</b>	Not classified.
<b>Label elements</b>	
<b>Hazard symbol</b>	None.
<b>Signal word</b>	None.
<b>Hazard statement</b>	Not available.
<b>Precautionary statement</b>	
<b>Prevention</b>	Not available.
<b>Response</b>	Not available.
<b>Storage</b>	Not available.
<b>Disposal</b>	Not available.
<b>Hazard(s) not otherwise classified (HNOC)</b>	Potential routes of exposure to this product are skin and eye contact, ingestion, and inhalation. Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. Complete toxicity data are not available for this specific formulation. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

**Supplemental information** This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

## 3. Composition/information on ingredients

### Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	70-90
Hydroxy alkylated lactam*		Proprietary*	<15
Black Pigment		Proprietary	<5

**Composition comments** This ink supply contains an aqueous ink formulation. This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

\*Proprietary

Carbon black is present only in a bound form in this preparation.

#### 4. First-aid measures

<b>Inhalation</b>	Remove to fresh air. If symptoms persist, get medical attention.
<b>Skin contact</b>	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
<b>Eye contact</b>	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
<b>Ingestion</b>	If ingestion of a large amount does occur, seek medical attention.
<b>Most important symptoms/effects, acute and delayed</b>	Not available.

#### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	For small (incipient) fires, use media such as foam, sand, dry chemical, or carbon dioxide. For large fires use very large (flooding) quantities of water and/or foam, applied as a mist or spray.
<b>Unsuitable extinguishing media</b>	None known.
<b>Specific hazards arising from the chemical</b>	Not applicable.
<b>Special protective equipment and precautions for firefighters</b>	Not available.
<b>Specific methods</b>	None established.

#### 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures</b>	Wear appropriate personal protective equipment.
<b>Methods and materials for containment and cleaning up</b>	Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.
<b>Environmental precautions</b>	Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

#### 7. Handling and storage

<b>Precautions for safe handling</b>	Avoid contact with skin, eyes and clothing.
<b>Conditions for safe storage, including any incompatibilities</b>	Keep out of the reach of children. Keep away from excessive heat or cold.

#### 8. Exposure controls/personal protection

##### Occupational exposure limits

##### US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Black Pigment	PEL	3.5 mg/m3

##### US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Black Pigment	TWA	3 mg/m3	Inhalable fraction.

**US. NIOSH: Pocket Guide to Chemical Hazards**

<b>Components</b>	<b>Type</b>	<b>Value</b>
Black Pigment	TWA	0.1 mg/m3
<b>Biological limit values</b>	No biological exposure limits noted for the ingredient(s).	
<b>Exposure guidelines</b>	Exposure limits have not been established for this product.	
<b>Appropriate engineering controls</b>	Use in a well ventilated area.	
<b>Individual protection measures, such as personal protective equipment</b>		
<b>Eye/face protection</b>	Not available.	
<b>Skin protection</b>		
<b>Hand protection</b>	Not available.	
<b>Other</b>	Not available.	
<b>Respiratory protection</b>	Not available.	
<b>Thermal hazards</b>	Not available.	
<b>General hygiene considerations</b>	Handle in accordance with good industrial hygiene and safety practice.	

---

**9. Physical and chemical properties****Appearance**

<b>Physical state</b>	Liquid.
<b>Form</b>	Not available.
<b>Color</b>	Black.
<b>Odor</b>	Not available.
<b>Odor threshold</b>	Not available.
<b>pH</b>	7.5 - 9
<b>Melting point/freezing point</b>	Not available.
<b>Initial boiling point and boiling range</b>	Not available.
<b>Flash point</b>	>230.0 °F (>110.0 °C) Pensky-Martens Closed Cup
<b>Evaporation rate</b>	Not available.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	
<b>Explosive limit - lower (%)</b>	Not available.
<b>Explosive limit - upper (%)</b>	Not available.
<b>Vapor pressure</b>	Not available.
<b>Relative vapor density</b>	Not available.
<b>Solubility(ies)</b>	
<b>Solubility (water)</b>	Not available.
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Other information</b>	For other VOC regulatory data/information see Section 15.
<b>Density</b>	1.05 g/cm3
<b>Oxidizing properties</b>	Not determined
<b>VOC</b>	<229 g/L

---

**10. Stability and reactivity**

<b>Reactivity</b>	Not available.
<b>Chemical stability</b>	Stable under recommended storage conditions.

<b>Possibility of hazardous reactions</b>	Will not occur.
<b>Conditions to avoid</b>	Not available.
<b>Incompatible materials</b>	Incompatible with strong bases and oxidizing agents.
<b>Hazardous decomposition products</b>	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.

## 11. Toxicological information

### Information on likely routes of exposure

<b>Inhalation</b>	Under normal conditions of intended use, this material is not expected to be an inhalation hazard.
<b>Skin contact</b>	Contact with skin may result in mild irritation.
<b>Eye contact</b>	Contact with eyes may result in mild irritation.
<b>Ingestion</b>	Health injuries are not known or expected under normal use.

**Symptoms related to the physical, chemical and toxicological characteristics** Not available.

### Information on toxicological effects

**Acute toxicity** Based on available data, the classification criteria are not met.

Components	Species	Test Results
------------	---------	--------------

Black Pigment

#### Acute

#### Oral

LD50	Rat	> 10000 mg/kg
------	-----	---------------

**Skin corrosion/irritation** Based on available data, the classification criteria are not met.

**Serious eye damage/eye irritation** Based on available data, the classification criteria are not met. Not classified as an irritant according to, OECD 405.

### Respiratory or skin sensitization

**Respiratory sensitization** Based on available data, the classification criteria are not met.

**Skin sensitization** Based on available data, the classification criteria are not met.

**Germ cell mutagenicity** Based on available data, the classification criteria are not met.

**Carcinogenicity** Based on available data, the classification criteria are not met.

Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation.

#### IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

#### OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

#### US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

**Reproductive toxicity** Based on available data, the classification criteria are not met.

**Specific target organ toxicity - single exposure** Based on available data, the classification criteria are not met.

**Specific target organ toxicity - repeated exposure** Based on available data, the classification criteria are not met.

**Aspiration hazard** Based on available data, the classification criteria are not met.

**Further information** Complete toxicity data are not available for this specific formulation. Refer to Section 2 for potential health effects and Section 4 for first aid measures.

## 12. Ecological information

**Aquatic toxicity** This product has not been tested for ecological effects.

<b>Ecotoxicity</b>	No ecotoxicity data noted for the ingredient(s).
<b>Persistence and degradability</b>	Not available.
<b>Bioaccumulative potential</b>	Not available.
<b>Mobility in soil</b>	Not available.
<b>Other adverse effects</b>	Not available.

---

### 13. Disposal considerations

<b>Disposal instructions</b>	Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <a href="http://www.hp.com/recycle">http://www.hp.com/recycle</a> .
------------------------------	---

---

### 14. Transport information

#### DOT

<b>UN number</b>	Not regulated as dangerous goods.
<b>UN proper shipping name</b>	Not Regulated
<b>Transport hazard class(es)</b>	
<b>Class</b>	Not assigned.
<b>Subsidiary risk</b>	-
<b>Packing group</b>	Not assigned.
<b>Environmental hazards</b>	
<b>Marine pollutant</b>	No
<b>Special precautions for user</b>	Not assigned.

#### IATA

<b>UN number</b>	Not regulated as dangerous goods.
<b>UN proper shipping name</b>	Not Regulated
<b>Transport hazard class(es)</b>	
<b>Class</b>	Not assigned
<b>Subsidiary risk</b>	-
<b>Packing group</b>	Not assigned
<b>Environmental hazards</b>	No
<b>Special precautions for user</b>	Not assigned

#### IMDG

<b>UN number</b>	Not regulated as dangerous goods.
<b>UN proper shipping name</b>	Not Regulated
<b>Transport hazard class(es)</b>	
<b>Class</b>	Not assigned.
<b>Subsidiary risk</b>	-
<b>Packing group</b>	Not assigned.
<b>Transport hazard class(es)</b>	
<b>Marine pollutant</b>	No
<b>EmS</b>	Not assigned.
<b>Special precautions for user</b>	Not assigned.

#### ADR

<b>UN number</b>	Not regulated as dangerous goods.
<b>UN proper shipping name</b>	Not Regulated
<b>Transport hazard class(es)</b>	
<b>Class</b>	Not assigned
<b>Subsidiary risk</b>	-
<b>Hazard No. (ADR)</b>	Not assigned
<b>Tunnel restriction code</b>	Not assigned
<b>Packing group</b>	Not assigned
<b>Environmental hazards</b>	No
<b>Soecial precautions for user</b>	Not assigned

<b>Further information</b>	Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.  Transport in bulk according to Annex II of MARPOL73/78 and the IBC code: Not applicable.
----------------------------	--

---

## 15. Regulatory information

**US federal regulations** US TSCA 12(b): Does not contain listed chemicals.

### Toxic Substances Control Act (TSCA)

#### TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

### CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

### SARA 304 Emergency release notification

Not regulated.

### OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

## Superfund Amendments and Reauthorization Act of 1986 (SARA)

### SARA 302 Extremely hazardous substance

Not listed.

### SARA 311/312 Hazardous chemical

No

## Other federal regulations

### Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

No intentionally added HAP substances.

### Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

### Safe Drinking Water Act (SDWA)

Not regulated.

## Other information

VOC content (less water, less exempt compounds) = < 884 g/L (U.S. requirement, not for emissions)

VOC data based on formulation (Organic compounds minus solids)

## Regulatory information

HP complies with chemical regulatory requirements in chemical substance notification laws, where applicable. All chemical substances are notified or exempt from notification or listed in the inventory as existing substances in the following countries: US (TSCA), Canada (DSL/NDSL), Australia (AICIS), Japan (ISHL, ENCS), Philippines (PICCS), New Zealand (NZIoC) and China (IECSC). For guidance on importation and/or additional requirements for registration schemes such as EAEU, EU, South Korea, Turkey, UK, India and Taiwan, please contact the Sustainability and Compliance Center (sustainability@hp.com).

## Clean Air Act (CAA)

No intentionally added HAP substances.

---

## 16. Other information, including date of preparation or last revision

**Issue date** 14-Nov-2023

**Version #** 01

**Other information** This SDS was prepared in accordance with USA OSHA Hazard Communications regulation (29 CFR 1910.1200).

## Disclaimer

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

This safety data sheet is meant to convey information about HP inks (toners) provided in HP Original ink (toner) supplies. If our Safety Data Sheet has been provided to you with a refilled, remanufactured, compatible or other non-HP Original supply please be aware that the information contained herein was not meant to convey information about such products and there could be considerable differences from information in this document and the safety information for the product you purchased. Please contact the seller of the refilled, remanufactured or compatible supplies for applicable information, including information on personal protective equipment, exposure risks and safe handling guidance. HP does not accept refilled, remanufactured or compatible supplies in our recycling programs.

## Revision information

1. Product and Company Identification: Alternate Trade Names

## Explanation of abbreviations

<b>ACGIH</b>	American Conference of Governmental Industrial Hygienists
<b>Acute Tox.</b>	Acute toxicity
<b>Aquatic Acute</b>	Short-term (acute) aquatic hazard
<b>Aquatic Chronic</b>	Long-term (chronic) aquatic hazard
<b>Asp. Tox.</b>	Aspiration hazard
<b>Carc.</b>	Carcinogenicity
<b>CAS</b>	Chemical Abstracts Service
<b>CERCLA</b>	Comprehensive Environmental Response Compensation and Liability Act
<b>CFR</b>	Code of Federal Regulations
<b>COC</b>	Cleveland Open Cup
<b>DOT</b>	Department of Transportation
<b>EPCRA</b>	Emergency Planning and Community Right-to-Know Act (aka SARA)
<b>Eye Dam.</b>	Serious eye damage
<b>Eye Irrit.</b>	Eye Irritation
<b>Flam. Liq.</b>	Flammable liquids
<b>Flam. Sol.</b>	Flammable solids
<b>Lact.</b>	Effects on or via lactation
<b>Muta.</b>	Germ cell mutagenicity
<b>IARC</b>	International Agency for Research on Cancer
<b>NIOSH</b>	National Institute for Occupational Safety and Health
<b>NTP</b>	National Toxicology Program
<b>OSHA</b>	Occupational Safety and Health Administration
<b>Ox. Liq.</b>	Oxidising liquids
<b>Ozone</b>	Hazardous to the ozone layer
<b>PEL</b>	Permissible Exposure Limit
<b>Press. Gas</b>	Gases under pressure
<b>RCRA</b>	Resource Conservation and Recovery Act
<b>REC</b>	Recommended
<b>REL</b>	Recommended Exposure Limit
<b>Repr.</b>	Reproductive toxicity
<b>Resp. Sens.</b>	Respiratory sensitization
<b>SARA</b>	Superfund Amendments and Reauthorization Act of 1986
<b>Skin Corr.</b>	Skin corrosion
<b>Skin Irrit.</b>	Skin irritation
<b>Skin Sens.</b>	Skin sensitization
<b>STEL</b>	Short-Term Exposure Limit
<b>STOT RE</b>	Specific target organ toxicity - repeated exposure
<b>STOT SE</b>	Specific target organ toxicity - single exposure
<b>TCLP</b>	Toxicity Characteristics Leaching Procedure
<b>TLV</b>	Threshold Limit Value
<b>TSCA</b>	Toxic Substances Control Act
<b>VOC</b>	Volatile Organic Compounds