ABB BALDOR RELIANCE

Customer information packet

VXM05162

1//.75HP, 1155//970RPM, 3PH, 60//50HZ, 56C, 3
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 9:22:04 AM

Specifications

Enclosure	XPFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz
	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	1.000 HP @ 60 HZ
	.750 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
	380.0 V @ 50 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA EEV
	UL
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.500 A @ 208.0 V
	3.200 A @ 190.0 V
	3.000 A @ 230.0 V
	1.600 A @ 380.0 V
	1.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT

Part Detail

Revision	D
Type	AC
Mech. spec.	35Q643
Base	
Status	PRD/A
Elec. spec.	35WGG019
Layout	35LYQ643
Eff. date	05-27-2026
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	02-23-2023

Efficiency @ 100% Load	82.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3526M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	15.12 IN
Power Factor	67
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1155 rpm
	970 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSL											
NO.				**CC**							
S/N				**TEMP CODE**	T3C						
SPEC.	35Q643G019			**INV.TYPE**	PWM						
CAT.NO.	VXM05162			**C HP FR**	60	**C HP TO**	90				
HP	1//.75			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	3/1.5//3.2/1.6		**MAG CUR**	2/1							
RPM	1155//970		**MX RPM**	1800							
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	82.5				
SER.F.	1.00	**DES**	B	**SL HZ**	1.5	**WK2**	0.189				
FRAME	56C	**RATING**	40C AMB-CONT								
	NEMA MG-1 PART 5, IP54										
	1.15 SF ON SINE WAVE										

AC Induction Motor Performance Data
Record # 73789
Typical performance - not guaranteed values

Winding: 35WGM497-R087	**Type:** 3526M	**Enclosure:** XPFC

Nameplate Data			
Rated Output (HP)			1//.75
Volts			230/460//190/380
Full Load Amps			3.6/1.8//3.4/1.7
R.P.M.			1155//960
Hz	60//50	**Phase**	3
NEMA Design Code	B	**KVA Code**	K
Service Factor (S.F.)			1
NEMA Nom. Eff.	82.5	**Power Factor**	64
Rating - Duty			40C AMB-CONT

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	4.51 LB-FT
Start Configuration	direct on line
Breakdown Torque	15.23 LB-FT
Pull-up Torque	11.1 LB-FT
Locked-rotor Torque	11.9 LB-FT
Starting Current	10.8 A
No-load Current	1.21 A
Line-line Res. @ 25ºC	16.1 Ω
Temp. Rise @ Rated Load	48°C
Locked-rotor Power Factor	41.5
Rotor inertia	0.155 LB-FT2

Load Characteristics 460 V, 60 Hz, 1 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	28	44	56	65	71	75
Efficiency	66	77	80.7	81.4	80.9	79.5
Speed	1190	1180	1170	1158	1145	1129
Line amperes	1.25	1.37	1.54	1.77	2.04	2.35


ABB Motors and Mechanical Inc.


WINDING # 35WGM497

1 HP 3 PH 60 HZ 1158 RPM 460 V 3526M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=15.23 PU=11.1 LR=11.9 LRA=10.8




35LYQ643
510-520 = 14.30
521-528 = 15.12
529-535 = 16.05
536-546 = 17.42
2.06
1.88
.19 KEY
1.38 LONG
.12
Ø7.19
Ø6.45
Ø 4.500
4.497
Ø .6250
.6245
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
4.72
6.71
6.97
45°
45°
LEAD HOLE
.50 N.P.T.
5.38
4 HOLES
.38-16 TAP
.56 DEEP
ON Ø5.88 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CLI GP D & CLII GP F&G WAS CLII GP D & CLII GP F&G
REV: B
VERSION: 02
REVISED: 04:12:50 03/09/2021
TDR: 000001162618
MODEL NO. 35LYQ643
REF: -
BY: ENADAF0
B
BALDOR - RELIANCE®
VERT 56C XPFC 35M CLI GP D & CLII GP F&G, INVERTER DUTY
35LYQ643

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS