ABB BALDOR RELIANCE

Customer information packet

EM3710T-BG

7.5HP, 1770RPM, 3PH, 60HZ, 213T, 3738M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 12:15:22 PM

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	7.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.500 A @ 460.0 V
	20.000 A @ 208.0 V
	19.000 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part Detail

Revision	G
Type	AC
Mech. spec.	37N339
Base	
Status	PRD/A
Elec. spec.	37WGL864
Layout	37LYN339
Eff. date	04-01-2026
CD Diagram	CD0005
Poles	04
Leads	9#14
Proprietary	False
Created date	02-01-2021

Heater Indicator	No Heater
High Voltage Full Load Amps	9.5 a
Insulation Class	H
Inverter Code	Inverter Ready
KVA Code	J
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3738M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	19.01 IN
Power Factor	80
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.375 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1770 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3441LUA										
CAT.NO.	EM3710T-BG									
SPEC	37N339L864G1									
HP	7.5									
VOLTS	230/460									
AMPS	19/9.5									
RPM	1770									
FRAME	213T	**HZ**	60	**PH**	3					
SF	1.15	**CODE**	J	**DES**	A	**CLASS**	H			
NEMA NOM. EFF	91.7	**PF**	80							
RATING	40C AMB-CONT									
CC	010A									
ENCL	TEFC	**SER**								
DE	6307	**ODE**	6206							
VPWM INVERTER READY	SFA 21.6/10.8									
CT6-60H(10:1)VT3-60H(20:1										
	50HZ 7.5HP 190/380V 22.4/11.2A									SF1.0

AC Induction Motor Performance Data
Record # 86486
Preliminary Data Sheet

Winding: 37WGL864-R002	**Type:** 3738M	**Enclosure:** TEFC

Nameplate Data			
Rated Output (HP)			7.5
Volts			230/460
Full Load Amps			19.0/9.5
R.P.M.			1770
Hz	60	**Phase**	3
NEMA Design Code	A	**KVA Code**	J
Service Factor (S.F.)			1.15
NEMA Nom. Eff.	91.7	**Power Factor**	80
Rating - Duty			40C AMB-CONT
S.F. Amps			21.4/10.7

460 V, 60 Hz: High Voltage Connection	
Full Load Torque	22.2 LB-FT
Start Configuration	direct on line
Breakdown Torque	69.8 LB-FT
Pull-up Torque	31.5 LB-FT
Locked-rotor Torque	41 LB-FT
Starting Current	70.7 A
No-load Current	4.32 A
Line-line Res. @ 25ºC	1.48 Ω
Temp. Rise @ Rated Load	64°C
Temp. Rise @ S.F. Load	84°C
Locked-rotor Power Factor	41.9
Rotor inertia	0.934 lb-ft²

Load Characteristics 460 V, 60 Hz, 7.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	42	64	75	80	83	84	83
Efficiency	87.1	91.4	92	91.7	90.7	89.6	90.7
Speed	1793	1786	1778	1770	1760	1750	1761
Line amperes	4.83	6.03	7.64	9.5	11.6	13.9	10.7


ABB Motors and Mechanical Inc.


WINDING # 37WGL864

7.5 HP 3 PH 60 HZ 1770 RPM 460 V 3738M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=69.8 PU=31.5 LR=41 LRA=70.7




37LYN339
717-735 = 17.89
736-744 = 19.02
745-750 = 19.77
751-756 = 20.52
3.88
5.01
GREASE FITTINGS (EACH END)
3.38
Ø 10.28
.31 KEY 2.38 LONG
1.3750
1.3745
6 HOLES Ø .43
5.50
3.50
7.00
.50
8.00
9.56
7.93
2.39
10.02
5.25 +.00 -.06
LEAD HOLE Ø 1.38
4.25
4.25
6.69
9.50
INTERNAL SHAFT GROUND
PULLEY END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD TO SOLIDWORKS
REV: B
VERSION: 02
REVISED: 11:26:03 08/26/2022
TDR: 000001195814
MODEL NO. 37LYN339
REF: -
BY: ENFRAJ0
B
BALDOR - RELIANCE®
HOR 213-5T TEFC M, BALDOR INT SHAFT GND
37LYN339

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS