ABB BALDOR RELIANCE

Customer information packet

ECS101M0H5DC4

5HP, 1800RPM, 3PH, 60HZ, 145TC, 3548B, TEFC, F1
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 4:51:18 PM

Specifications

Enclosure	TEFC
Frame	145TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Brushless Wound Field PM Rotor
Output @ Frequency	5.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	WEEE
	CULUS
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	10.400 A @ 230.0 V
	5.200 A @ 460.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	93.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Heater Indicator	No Heater
High Voltage Full Load Amps	5.2 a
Insulation Class	H


Part Detail

Revision	C
Type	AC
Mech. spec.	35E5350
Base	
Status	PRD/A
Elec. spec.	35WGG930
Layout	35LYE5350
Eff. date	02-12-2026
CD Diagram	CD0005A25
Poles	04
Leads	9#14
Proprietary	False
Created date	03-15-2024


Inverter Code	Inverter Duty
KVA Code	-
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 14 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3548B
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.54 IN
Power Factor	97
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
RoHS Status	Y
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Speed	1800 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None


Nameplate


NP3968A01A01									
CAT.NO.	ECS101M0H5DC4								
SPEC.	35E5350G930								
FRAME	145TC			**ENCL.**	TEFC		**IP**	54	
HP	5		40	**C AMB**		CONT			
NOM. EFF.	93	**PF**	97		**SF**	1.4			
VOLTS	230/460			**FLA**	10.4/5.2				
RPM	1800			**RPM-MAX**	4000				
HZ	60		**PH.**	3	**CLASS**	H			
BEMF (V)	113/227				**RS (OHMS)**	0.79/3.18			
LD (MH)	4.2/16.8				**LQ (MH)**	18.5/74			
VPWM	**CHP**	60	**TO**	133					
CT	6	**TO**	60	**VT**	6	**TO**	60		
MATCHED INV	ACS380-04XX-12A2-1 / 07A2-4								
DE	6205			**ODE**	6203				
SERIAL #									


35LYE5350
516, 524 = 12.29
532 = 13.29
548 = 15.54
2.25
2.13
.13
Ø7.19
.19 KEY
1.38 LG
Ø6.49
Ø4.500
4.497
Ø.8750
.8745
FORSHEDA
SLINGER
3.75
DRAIN FITTING
(EACH END)
Ø6.61
5.71
45°
45°
TOP OF
NAMEPLATE
LEAD HOLE
Ø1.09
4.59
4 HOLES
.38-16 TAP
ON Ø5.88 B.C.
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE DIMENSION GRAPHICS
REV: D
VERSION: 04
REVISED: 11:34:53 11/21/2024
TDR: 000001245032
MODEL NO. 35LYE5350
REF: -
BY: ENJEFD0
B
BALDOR - RELIANCE®
VER 143-5TC TEFC B INT SH GND ECS
35LYE5350

CD0005A25







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
3. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005A25

REV. DESC: NEW		
REV. LTR: –	VERSION: 00	TDR: 000001135746
FILE: \AAA\00253\082	REVISED: 01:10:57 03/30/2020	BY: ENMARSO
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, ECS

SH 1 of 1