



SAFETY DATA SHEET

Supersedes Date: 28 Jul 2022

Revision Date: 13 Feb 2023

Version: 2.0

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product identifier

Product Label Name Flex Powder with Citrus Solv
Other means of identification
UPC Code(s) Not applicable
Product code CC21
Synonyms None

Recommended use of the chemical and restrictions on use

Recommended Use Carpet cleaning solution
Uses advised against Follow label instructions. Not recommended for any use except intended use.

Supplier's details

Supplier Address Aramco Inc. 4282 South 590 West Salt Lake City, UT 84123 USA	Manufacturer Address Aramco Inc. 4282 South 590 West Salt Lake City, UT 84123 USA
--	--

Emergency telephone number

Supplier Phone Number	1-800-658-5314
Manufacture Phone Number	1-800-658-5314
Company Emergency Phone Number	United States: 1-800-535-5053 (INFOTRAC – 24 hours, 7 days a week)
Emergency telephone	International: 1-352-323-3500 (INFOTRAC – 24 hours, 7 days a week) Poison Control: 1-800-222-1222 (24 hour)

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin corrosion/irritation	Category 1
Serious eye damage/eye irritation	Category 1
Skin sensitization	Category 1

GHS Label elements, including precautionary statements

Emergency Overview

Danger

Hazard Statements

Causes severe skin burns and eye damage
May cause an allergic skin reaction

**Appearance** powder**Physical state** solid**Odor** Orange**Precautionary Statements - Prevention**

Do not breathe dust/fume/gas/mist/vapors/spray
 Wash face, hands and any exposed skin thoroughly after handling
 Wear protective gloves/protective clothing/eye protection/face protection
 Contaminated work clothing should not be allowed out of the workplace

Precautionary Statements - Response

Immediately call a POISON CENTER or doctor/physician
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 Wash contaminated clothing before reuse
 If skin irritation or rash occurs: Get medical advice/attention.
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 Call a POISON CENTER or doctor/physician if you feel unwell
 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting

Precautionary Statements - Storage

Store locked up

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)**Other information**

- May be harmful if swallowed

General Hazards

Keep out of reach of children

Please see Section 11. Toxicological Information for further information

2.568% of the mixture consists of ingredient(s) of unknown toxicity

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS-No	Weight %	Trade Secret
Sodium carbonate	497-19-8	10 - 30	*
Sodium metasilicate	6834-92-0	10 - 30	*
ALCOHOLS, C9-11, ETHOXYLATED	68439-46-3	5 - 10	*
D-Limonene	5989-27-5	1 - 5	*

*The exact percentage (concentration) of composition has been withheld as a trade secret

4. FIRST AID MEASURES

First aid measures for different exposure routes**General advice**

Immediate medical attention is required.

Eye contact

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected

area.

Skin contact	Immediate medical attention is required. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.
Toxic - Inhalation	Move to fresh air. Call a physician or Poison Control Center immediately. If not breathing, give artificial respiration. If breathing is difficult, give oxygen.
Ingestion	Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person. Remove from exposure, lie down. Clean mouth with water and drink afterwards plenty of water. Call a physician or Poison Control Center immediately.
Protection of First-aiders	Use personal protective equipment. Avoid contact with skin, eyes and clothing.

Most important symptoms/effects, acute and delayed

Main Symptoms No information available.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to physician Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating gases and vapors. In the event of fire and/or explosion do not breathe fumes.

Hazardous Combustion Products No information available.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions	Evacuate personnel to safe areas. Use personal protective equipment. Avoid contact with skin, eyes and clothing. Keep people away from and upwind of spill/leak.
Other information	Refer to protective measures listed in Sections 7 and 8.
Advice for emergency responders	For personal protection see section 8.

Environmental precautions

Environmental precautions Do not allow material to contaminate ground water system. Should not be released into the environment. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains.

Methods and materials for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal. Clean contaminated surface thoroughly. Use personal protective equipment. Cover powder spill with plastic sheet or tarp to minimize spreading and keep powder dry. Avoid dust formation. Dam up. After cleaning, flush away traces with water.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Wear personal protective equipment. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. In case of insufficient ventilation, wear suitable respiratory equipment. Handle product only in closed system or provide appropriate exhaust ventilation at machinery.

Conditions for safe storage, including any incompatibilities

Technical measures/Storage conditions Keep container tightly closed in a dry and well-ventilated place. Keep out of the reach of children. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers.

Packaging material Keep product in packaging product is initially sold in.

Incompatible products Incompatible with strong acids and bases. Incompatible with oxidizing agents.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Appropriate engineering controls

Engineering Measures Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection Tightly fitting safety goggles. Face-shield.

Skin and body protection No special protective equipment required.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene measures When using, do not eat, drink or smoke. Remove and wash contaminated clothing before re-use. Keep away from food, drink and animal feeding stuffs. Contaminated work clothing

should not be allowed out of the workplace. Provide regular cleaning of equipment, work area and clothing. Avoid contact with skin, eyes and clothing. For environmental protection, remove and wash all contaminated protective equipment before re-use. Wear suitable gloves and eye/face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical and chemical properties

Physical state	solid	Odor	Orange
Appearance	powder	Odor threshold	No information available
Color	orange		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	12.0	(as 1% solution)
Melting point	No information available	
Boiling point/boiling range	No information available	
Flash Point	No information available	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper Flammability Limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	2.5	
Vapor density	4.7	
Specific Gravity	0.814	
Water solubility	Soluble in water	
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Viscosity, kinematic	No information available	200 cps
Viscosity, dynamic	No information available	
Explosive properties	No information available	
Oxidizing Properties	No information available	

Other information

Softening point	No information available
Molecular weight	No information available
VOC Content(%)	No information available
Density VALUE	8.232
Bulk Density VALUE	43.6 lb/ft3

10. STABILITY AND REACTIVITY

Reactivity

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Hazardous Polymerization None under normal processing.

Conditions to Avoid

Exposure to air or moisture over prolonged periods.

Incompatible Materials

Incompatible with strong acids and bases. Incompatible with oxidizing agents.

Hazardous Decomposition Products

Thermal decomposition can lead to release of irritating gases and vapors.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Toxic - Inhalation	Avoid breathing vapors or mists. Irritating to respiratory system. May be harmful by inhalation. May cause drowsiness or dizziness.
Eye contact	Avoid contact with eyes. May cause burns. Risk of serious damage to eyes. May cause irreversible damage to eyes.
Skin contact	Avoid contact with skin. Prolonged or repeated contact may dry skin and cause irritation. Prolonged skin contact may cause burns.
Ingestion	Do not taste or swallow. Ingestion may cause irritation to mucous membranes. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Can burn mouth, throat, and stomach.

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Sodium carbonate 497-19-8	= 4090 mg/kg (Rat)	2210 mg/kg (rat)	= 2300 mg/m ³ (Rat) 2 h
Sodium metasilicate 6834-92-0	= 1153 mg/kg (Rat)	>5000 mg/kg (rat)	
ALCOHOLS, C9-11, ETHOXYLATED 68439-46-3	= 1400 mg/kg (Rat) = 1378 mg/kg (Rat)	> 2 g/kg (Rabbit)	
D-Limonene 5989-27-5	= 4400 mg/kg (Rat)	> 5 g/kg (Rabbit)	

Information on toxicological effects

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation No information available.
Eye damage/irritation No information available.
Sensitization No information available.
Germ cell mutagenicity No information available.
Carcinogenicity No information available.
Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
D-Limonene 5989-27-5	-	Group 3	-	X

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

IARC: (International Agency for Research on Cancer)

Group 3 - Not Classifiable as to Carcinogenicity in Humans

Reproductive toxicity No information available.
Developmental Toxicity No information available.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Chronic toxicity Chronic exposure to corrosive fumes/gases may cause erosion of the teeth followed by jaw necrosis. Bronchial irritation with chronic cough and frequent attacks of pneumonia are common. Gastrointestinal disturbances may also be seen. Avoid repeated exposure. Possible risks of irreversible effects.
Aspiration hazard No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity 2.568% of the mixture consists of ingredient(s) of unknown toxicity
The following values are calculated based on chapter 3.1 of the GHS document .

ATEmix (oral) 3282 mg/kg
ATEmix (dermal) 5159 mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity

57.5414% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical Name	Toxicity to algae	Toxicity to fish	Toxicity to daphnia and other aquatic invertebrates
Sodium carbonate 497-19-8	242: 120 h Nitzschia mg/L EC50	300: 96 h Lepomis macrochirus mg/L LC50 static 310 - 1220: 96 h Pimephales promelas mg/L LC50 static	265: 48 h Daphnia magna mg/L EC50
Sodium metasilicate 6834-92-0		210: 96 h Brachydanio rerio mg/L LC50 semi-static 210: 96 h Brachydanio rerio mg/L LC50	216: 96 h Daphnia magna mg/L EC50
D-Limonene 5989-27-5		0.619 - 0.796: 96 h Pimephales promelas mg/L LC50 flow-through 35: 96 h Oncorhynchus mykiss mg/L LC50	

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste Disposal Methods

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging

Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDSL Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations

California Proposition 65

This product can expose you to chemicals including Acetaldehyde and Lead, which are known to the State of California to cause cancer, and Ethylene Glycol, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
None			

U.S. EPA Label information

EPA Pesticide Registration Number Not applicable

16. OTHER INFORMATION

NFPA	Health hazard 2	Flammability 0	Instability 0	Physical and chemical hazards -
HMIS	Health hazard 2	Flammability 0	Physical Hazard 0	Personal protection X

Prepared By Aramsco
Environmental Health & Safety
Revision Date 13 Feb 2023

Revision Note
13 Feb 2023 – Update Prop 65 Warning
11 Feb 2022 – Review, no changes made

Disclaimer

The (M)SDS is intended to provide a brief summary of our knowledge and guidance regarding the use of this material. The information contained here has been compiled from sources considered by Bridgewater LLC to be dependable and is accurate to the best of the Company’s knowledge. It is not meant to be an all-inclusive document on worldwide hazard communication regulations.

This information is offered in good faith. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage or release to the environment. Bridgewater LLC assumes no responsibility for injury to the recipient of third persons, or for any damage to any property resulting from misuse of the product.

End of Material Safety Data Sheet