

Special Tec V SAE 0W-20

Description

Fully synthetic superior, low friction motor oil. Developed specifically for use in various late model Volvo vehicles and also suitable for use in several other manufacturers vehicles. The low viscosity ensures excellent cold start behavior, improves engine efficiency and reduces fuel consumption. Use with extended oil change intervals as per manufacturer.



Properties

- excellent resistance to aging
- outstanding engine cleanliness
- ideal with turbochargers and catalytic converters
- minimizes friction
- ensures maximum engine performance

Specifications / Approvals

ACEA C5 • API SP • Volvo VCC RBS0-2AE

Technical data

SAE class (engine oils)	0W-20 SAE J300
Density at 59 °F	0,845 g/cm ³ DIN 51757
Viscosity at 104 °F	44,0 mm ² /s ASTM D7042
Viscosity at 212°F	8,8 mm ² /s ASTM D7042
Viscosity at -40 °F (MRV)	< 60000 mPas ASTM D4684
Viscosity at -31 °F (CCS)	≤ 6200 mPas ASTM D5293
Viscosity index	180 DIN ISO 2909
HTHS at 302 °F	≥ 2,6 mPas ASTM D5481
Pour point	-49 °F DIN ISO 3016
Evaporation loss (Noack)	13,0 % CEC-L-10-A-93
Flash point	446 °F DIN ISO 2592
Total base number	8,5 mg KOH/g DIN ISO 3771
Sulfate ash	≤ 0,8 % DIN 51575
Color number (ASTM)	L 3,5 DIN ISO 2049

Areas of application

For gasoline or diesel engines where a motor oil according to current specifications is required or recommended. Tested safe with catalytic converters and turbochargers.

⚠ WARNING: This product can expose you to chemicals including toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Application

Observe the manufacturers instructions!

Available pack sizes

1 l Canister plastic	20198 CAEN-CAFR-USEN
5 l Canister plastic	20200 CAEN-CAFR-USEN
60 l Black plate barrel	20355 CAEN-CAFR-USEN
1.000 l Container	22172 CAEN-CAFR-USEN

Our information is based on thorough research and may be considered reliable, although not legally binding.