

JWBS-14SFX
STOCK NO. JT9-714400K



14SFX 14" BANDSAW

SPECIFICATION	DESCRIPTION
Model Number	JWBS-14SFX
Stock Number	JT9-714400K
Bandsaw Wheel Diameter (in.)	14"
Blade Speed (FPM)	3000
Wheel Speed (RPM)	765
Cutting Capacity Height (in.)	13"
Cutting Capacity Width (in.)	13-1/2"
Dust Port Diameter (in.)	4"
Dust Collection Minimum CFM Required (CFM)	400
Motor Phase	1
Motor Power (HP)	1.75
Motor Speed (RPM)	1720
Sound Emission without Load	75 dB at 3ft
Voltage (V)	115/230V (rewired 115V)

SPECIFICATION	DESCRIPTION
Recommended Circuit Size	20A (for 115V), 15A (for 230V)
Resaw Fence Size (L x W) (in.)	18-1/4" L x 6" H
Miter T-Slot (in.)	3/4"
Table Material	Cast Iron
Table Insert Material	Anodized Aluminum
Table Tilt	0° to 45°
Stand Type	Closed
Frame Material	Steel
Wheels	Cast Iron
Blade Guides	Ball Bearing Guides
Prop 65	Cancer and Reproductive Harm
Overall Assembled Dimensions (L x W x H) (in.)	37" x 27-1/2" x 75-3/8"
Footprint (L x W) (in.)	24-5/12" x 17-2/3"
Net Weight (lbs.)	272 lbs. (approx.)

OPTIONAL EQUIPMENT & ACCESSORIES

For both coated (JWBS-14SFX-BLK) and non-coated (JWBS-14SFX) 14" Bandsaws.

STOCK NUMBER	DESCRIPTION
JT9-708118	JMB-UMB Universal Mobile Base, 18" x 18" to 28" x 28"
JT9-714403	JWBS-14LIT Bandsaw Light Kit
JT9-JWBS14SFX-104	Push Stick
JT9-JWBS14SFX-300	Miter Gauge Assembly
JT9-WBSB-116124	Replacement Blade, 116" x 1/2" x 4 TPI
JT9-WBSB-116144	Replacement Blade, 116" x 1/4" x 4 TPI
JT9-WBSB-116583G	Replacement Blade, 116" x 5/8" x 3 TPI

SEE IT IN ACTION.
VISIT JETTOOLS.COM TO LEARN MORE.

**INDUSTRY-LEADING
SERVICE & SUPPORT**

