



TEGERA® PRO 9121

Learn more

FOR EXCELLENT GRIP AND CUT RESISTANCE

This synthetic leather glove has an outstanding combination of two of the world's leading materials. Microthan®+ with diamond grip pattern for the best grip and durability, and Kevlar® that provide cut resistance level B. It has hook and loop closure for a more secure fit and reinforced seams is another feature of this versatile glove.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Perfect fit
- Excellent grip
- Extra comfortable

FUNCTIONS

- Cut protection in the palm only
- Reinforced index finger
- Reinforced seams
- Reinforced fingertips
- Pre-curved fingers
- Specially designed thumb
- Ergonomically shaped
- Reflector
- Specially designed details

Kevlar® MICROTHAN®+

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Chrome allergy, Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dark environments, Dry environments, Moist environments, Oily and greasy environments, Dirty environments, Slippery environments

PRIMARY AREAS OF USE

Fine assembly, Installation work, Soil preparation, Warehouse work, Airport work, Paper industry work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Light weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves, Cut resistant gloves
CATEGORY Cat. II
COLLECTION Pro
PALM MATERIAL Microthan®+
BACK MATERIAL Polyester
LINING Half-lined
LINING MATERIAL KEVLAR® fiber
LENGTH 207-243 mm
DEXTERITY 5
GRIP DESIGN Diamond grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Hook with hangtag
FASTENING Hook-and-loop
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 8.5 N
INNER MATERIAL SPECIFICATION Para-aramid
OUTER MATERIAL SPECIFICATION Polyurethane, Nylon, Polyester

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC
EN 388:2016+A1:2018 2X32B

ANSI A2 CUT
ANSI 3 ABR

FEATURES

Breathable
Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	9121-6	7392626020887
7	S	9121-7	7392626020894
8	M	9121-8	7392626020900
9	L	9121-9	7392626020917
10	XL	9121-10	7392626020924
11	XXL	9121-11	7392626020931

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.