

Safety Data Sheet



1. Identification

Product Information: L42W5560L1,L42W5560L5/S

Product Name: DURACOAT® PRE-CAT WHITE LACQUER 60 SHEEN - 550 VOC

Recommended Use: Surface Preparation or Protection

Supplied by: Finishworks
Division of RPM Industrial Coatings Group
3194 B Hickory Blvd
Hudson, NC 28638
USA

Company Phone No: (800) 522-8266

Emergency Phone No. CHEMTREC: (800) 424-9300

International Emergency No. CHEMTREC: (703) 527-3887 (Collect calls are accepted)

2. Hazards Identification

GHS Classification

Carc. 2, Eye Dam. 1, Flam. Liq. 2, STOT SE 3 NE

Symbol(s) of Product



Signal Word

Danger

GHS HAZARD STATEMENTS

Flammable Liquid, category 2	H225	Highly flammable liquid and vapour.
STOT, single exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Carcinogenicity, category 2	H351	Suspected of causing cancer.
Serious Eye Damage, category 1	H318	Causes serious eye damage.

GHS LABEL PRECAUTIONARY STATEMENTS

P403+P235 Store in a well-ventilated place. Keep cool.

GHS SDS PRECAUTIONARY STATEMENTS

P210	Keep away from heat. - No smoking.
P240	Ground/Bond container and receiving equipment.
P241	Use explosion-proof electrical/ ventilating/ lighting/ equipment.
P242	Use only non-sparking tools.
P243	Take precautionary measures against static discharge.
P280	Wear eye protection/ face protection.
P405	Store locked up.

P303+P361+P353	IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P201	Obtain special instructions before use.
P304+P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P308+P313	IF exposed or concerned: Get medical advice/attention.
P310	Immediately call a POISON CENTER or doctor/physician.

3. Composition/Information on ingredients

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
n-butyl acetate	123-86-4	10-30	GHS02-GHS07	H226-336
acetone	67-64-1	10-30	GHS02-GHS07	H225-302-319-332-336
titanium dioxide	13463-67-7	10-30	GHS08	H351
ethanol	64-17-5	5-10	GHS02	H225
cellulose nitrate, cellulose ester	9004-70-0	5-10	GHS01	H201
butanol	71-36-3	5-10	GHS02-GHS05-GHS07	H226-302-315-318-332-335-336
isopropanol	67-63-0	1-5	GHS02-GHS07	H225-302-319-336
butyl cellosolve	111-76-2	1-5	GHS06-GHS07	H302-315-319-330
butyl dihydrogen phosphate	1623-15-0	0.1-1	No Information	No Information
toluene	108-88-3	0.1-1	GHS02-GHS07-GHS08	H225-304-315-332-336-373
formaldehyde	50-00-0	<0.1	GHS05-GHS06-GHS07-GHS08	H302-311-314-317-330-335-341-350

The exact percentage (concentration) of ingredients is being withheld as a trade secret.

The text for GHS Hazard Statements shown above (if any) is given in the "Other information" Section.

4. First-aid Measures



FIRST AID - EYE CONTACT: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

FIRST AID - SKIN CONTACT: IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.

FIRST AID - INGESTION: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician.

FIRST AID - INHALATION: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

5. Fire-fighting Measures

SPECIAL FIREFIGHTING PROCEDURES: Evacuate all persons from the fire area to a safe location. Move non-burning material, as feasible, to a safe location as soon as possible. Fire fighters should be protected from potential explosion hazards while extinguishing the fire. Wear self-contained breathing apparatus (SCBA) and full fire-fighting protective clothing. Thoroughly decontaminate all protective equipment after use. Containers of this material may build up pressure if exposed to heat (fire). Use water spray to cool fire-exposed containers. Use water spray to disperse vapors if a spill or leak has not ignited. DO NOT extinguish a fire resulting from the flow of flammable liquid until the flow of the liquid is effectively shut off. This precaution will help prevent the accumulation of an explosive vapor-air mixture after the initial fire is extinguished.

FIREFIGHTING EQUIPMENT: This is a NFPA/OSHA Class 1B or less flammable liquid. Follow NFPA30, Chapter 16 for fire protection and fire suppression. Use a dry chemical, carbon dioxide, or similar ABC fire extinguisher for incipient fires. Water may be

used to cool and prevent rupture of containers that are exposed to heat from fire.

6. Accidental Release Measures

ENVIRONMENTAL MEASURES: No Information

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED: Follow personal protective equipment recommendations found in Section VIII. Personal protective equipment needs must be evaluated based on information provided on this sheet and the special circumstances created by the spill including; the material spilled, the quantity of the spill, the area in which the spill occurred, and the training and the expertise of employees in the area responding to the spill. Never exceed any occupational exposure limits. Shut off ignition sources; including electrical equipment and flames. Do not allow smoking in the area. Do not allow the spilled product to enter public drainage system or open waterways.

7. Handling and Storage



HANDLING: Avoid inhalation and contact with eyes, skin, and clothing. Wash hands thoroughly after handling and before eating or drinking. In keeping with safe handling practices, avoid ignition sources (smoking, flames, pilot lights, electrical sparks); ground and bond containers when transferring the material to prevent static electricity sparks that could ignite vapor and use spark proof tools and explosion proof equipment. Empty containers may retain product residue or vapor. Do not pressurize, cut, weld, braze, solder, drill, grind, or expose container to heat, flame, sparks, static electricity, or other sources of ignition. Any of these actions can potentially cause an explosion that may lead to injury.

STORAGE: Keep containers closed when not in use. Store in cool well ventilated space away from incompatible materials.

8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>ACGIH TLV-TWA</u>	<u>ACGIH-TLV STEL</u>	<u>OSHA PEL-TWA</u>	<u>OSHA PEL-CEILING</u>
n-butyl acetate	50 ppm	150 ppm	150 ppm	N.D.
acetone	250 ppm	500 ppm	1000 ppm	N.D.
titanium dioxide	0.2 mg/m ³	N.D.	15 mg/m ³	N.D.
ethanol	N.D.	1000 ppm	1000 ppm	N.D.
cellulose nitrate, cellulose ester	N.D.	N.D.	N.D.	N.D.
butanol	20 ppm	N.D.	100 ppm	N.D.
isopropanol	200 ppm	400 ppm	400 ppm	N.D.
butyl cellosolve	20 ppm	N.D.	50 ppm	N.D.
butyl dihydrogen phosphate	N.D.	N.D.	N.D.	N.D.
toluene	20 ppm	N.D.	200 ppm	300 ppm
formaldehyde	0.1 ppm	0.3 ppm	0.75 ppm	N.D.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation
Sk = Skin Sensitizer N.E. = Not Established N.D. = Not Determined

Personal Protection



RESPIRATORY PROTECTION: Use adequate engineering controls and ventilation to keep levels below recommended or statutory exposure limits. If exposure levels exceed limits use appropriate approved respiratory protection equipment.



SKIN PROTECTION: Wear chemical resistant footwear and clothing such as gloves, an apron or a whole body suit as appropriate.



EYE PROTECTION: Wear chemical-resistant glasses and/or goggles and a face shield when eye and face contact is possible due to splashing or spraying of material.

**OTHER PROTECTIVE EQUIPMENT:** No Information**HYGIENIC PRACTICES:** It is good practice to avoid contact with the product and/or its vapors, mists or dust by using appropriate protective measures. Wash thoroughly after handling and before eating or drinking.

9. Physical and Chemical Properties

Appearance:	Colored Liquid	Physical State:	Liquid
Odor:	Strong Solvent	Odor Threshold:	Not Determined
Density, g/cm3:	1.016	pH:	Not Determined
Freeze Point, °F:	Not Determined	Viscosity:	Not Determined
Solubility in Water:	Not Determined	Partition Coefficient, n-octanol/ water:	Not Determined
Decomposition temperature, °F:	Not Determined	Explosive Limits, %:	Not Determined
Boiling Range, °F:	> 100 °F	Flash Point, °F:	-4 ° F
Combustibility:	Supports Combustion	Auto-Ignition Temperature, °F:	Not Determined
Evaporation Rate:	Faster than Diethyl Ether	Vapor Pressure, mmHg:	Not determined
Vapor Density:	Not Determined	Color:	White

N.I. = No Information

10. Stability and reactivity

STABILITY: Stable under normal conditions.**CONDITIONS TO AVOID:** Heat, flames and sparks.**INCOMPATIBILITY:** Acids, Bases, Oxidizing agents**HAZARDOUS DECOMPOSITION PRODUCTS:** Not determined.

11. Toxicological information



Practical Experiences

EMERGENCY OVERVIEW: No Information**EFFECT OF OVEREXPOSURE - EYE CONTACT:** No Information**EFFECT OF OVEREXPOSURE - INGESTION:** No Information**EFFECT OF OVEREXPOSURE - INHALATION:** No Information**EFFECT OF OVEREXPOSURE - SKIN CONTACT:** No Information

CARCINOGENICITY: May cause cancer.

This product contains Titanium Dioxide, which is listed by IARC as possibly carcinogenic to humans (Group 2B). This listing is based on inadequate evidence of carcinogenicity in humans and sufficient evidence in experimental animals. This classification is relevant when exposed to titanium dioxide in dust or powder form only, including cured product that is subject to sanding, grinding, cutting, or other surface preparation activities.

PRIMARY ROUTE(S) OF ENTRY:

Eye Contact, Skin Contact, Inhalation

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
123-86-4	n-butyl acetate	14130 mg/kg Rat	>17600 mg/kg Rabbit	23.4 mg/l Rat
67-64-1	acetone	1800 mg/kg Rat	20000 mg/kg Rabbit	50.1 mg/L Rat
13463-67-7	titanium dioxide	>10000 mg/kg Rat	>10000 mg/kg Rabbit	>20 mg/l
64-17-5	ethanol	7060 mg/kg Rat	15,800 mg/kg	124.7 mg/L Rat
9004-70-0	cellulose nitrate, cellulose ester	>5000 mg/kg Rat	>5000 mg/kg	>20 mg/l
71-36-3	butanol	700 mg/kg Rat	3402 mg/kg Rabbit	8000 mg/l Rat
67-63-0	isopropanol	1870 mg/kg Rat	4059 mg/kg Rabbit	72.6 mg/L Rat
111-76-2	butyl cellosolve	470 mg/kg Rat	>2000 mg/kg Rabbit	>4.9 mg/l
108-88-3	toluene	2600 mg/kg Rat	12000 mg/kg Rabbit	12.5 mg/L Rat
50-00-0	formaldehyde	600 mg/kg Rat	270 mg/kg Rabbit	0.578 mg/L Rat

N.I. = No Information

12. Ecological information

ECOLOGICAL INFORMATION: Ecological evaluation of this material has not been performed; however, do not allow the product to be released to the environment without governmental approval/permits.

13. Disposal Information



Product

DISPOSAL METHOD: Waste from this material may be a listed and/or characteristic hazardous waste. Dispose of material, contaminated absorbent, container and unused contents in accordance with local, state, and federal regulations.

STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED: Follow personal protective equipment recommendations found in Section VIII. Personal protective equipment needs must be evaluated based on information provided on this sheet and the special circumstances created by the spill including; the material spilled, the quantity of the spill, the area in which the spill occurred, and the training and the expertise of employees in the area responding to the spill. Never exceed any occupational exposure limits. Shut off ignition sources; including electrical equipment and flames. Do not allow smoking in the area. Do not allow the spilled product to enter public drainage system or open waterways.

14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: No Information

DOT: UN1263, PAINT, 3, II

IATA: UN1263, PAINT, 3, II

IMDG: UN1263, PAINT, 3, II

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Fire Hazard, Acute Health Hazard, Chronic Health Hazard

SARA SECTION 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt. %</u>
butanol	71-36-3	5.04
isopropanol	67-63-0	2.77
butyl cellosolve	111-76-2	1.78

TOXIC SUBSTANCES CONTROL ACT

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(B) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
octamethylcyclotetrasiloxane	556-67-2

U.S. State Regulations:

CALIFORNIA PROPOSITION 65



WARNING: Risk of cancer from exposure to titanium dioxide and reproductive harm from exposure to toluene. See www.P65Warnings.ca.gov.

16. Other Information

Revision Date: 6/18/2026 Supersedes Date: 6/9/2026

Reason for revision: Product Composition Changed
Substance and/or Product Properties Changed in Section(s):
09 - Physical & Chemical Information
16 - Other Information

Datasheet produced by: Regulatory Department

HMIS Ratings:

Health:	2	Flammability:	3	Reactivity:	0	Personal Protection:	X
---------	---	---------------	---	-------------	---	----------------------	---

Volatile Organic Compounds, gr/ltr: 520

The information on this sheet corresponds to our present knowledge. It is not a specification and it does not guarantee specific properties. The information is intended to provide general guidance as to health and safety based upon our knowledge of the handling, storage, and use of the product. It is not applicable to unusual or non-standard uses of the product where instructions and recommendations are not followed.

Only the original U.S. - English version is authoritative.