



TEGERA® INFINITY 8811

Learn more

SUPER SOFT, LONG CUFF, CUT LEVEL D

Dexterous glove with long cuff and cut resistant level D, suitable for fine assembly work. Extended knitted cuff for extra protection of the wrist. 15 gg knitted with CRF® cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip on dry surfaces. Reinforced thumb crotch for improved longevity. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Extra comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Extra long
- Reinforcement between index finger and thumb
- Thin

CRF®

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Sheet-metal work, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Metalwork, Glass industry work, Repair work, Paper industry work, Service work, Shop work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Public safety, security and defence, Pulp and paper, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
COLLECTION Infinity
KNITTING GAUGE (GG) 15
LINING MATERIAL CRF® Technology, Glass fibre thread, HPPE, Nylon, Spandex
LENGTH 240-300 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam, Waterbased PU
CUFF STYLE Extended knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level D
CUT RESISTANCE (EN ISO 13997) TDM: 17.5 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Nylon, Glass fibre thread, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X43D

EN 407:2020 (No flame protection) X1XXXX

ANSI A3 CUT

ANSI 5 ABR

Contact heat rating valid for palm area only

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	8811-5	7340118328386
6	XS	8811-6	7340118321585
7	S	8811-7	7340118321608
8	M	8811-8	7340118321622
9	L	8811-9	7340118321646
10	XL	8811-10	7340118321547
11	XXL	8811-11	7340118321561

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.