


A blue industrial electric motor with a silver shaft and mounting base. The motor has a cylindrical body with a flange on the right side where the shaft is attached. There are some small labels on the motor body, but they are not legible. The motor is shown from a three-quarter perspective.

- Totally Enclosed Fan Cooled (TEFC) enclosure
- Dual mounting with NEMA 56C and removable base
- Class F insulation
- Rolled steel shell frame / cast aluminum end bell
- Removable base / bolt-on/bolt-off mounting feet
- Large all-metal capacitor cover with rubber gasket
- Large easy-to-wire junction box with rubber gasket
- Heavy duty oversized ball bearings
- High tensile strength steel shaft
- Electrically reversible
- NEMA design B
- Service Factor: 1.15

Item #	HP	RPM	Voltage	Frame	Encl.	O (max)	C (max)	F.L Amps	S. F.	Weight
MA0503A	1/3	1725	115/208-230	56C	TEFC	6.5	12.5	6.6/3.3	1.15	22
MA0505A	1/2	1725	115/208-230	56C	TEFC	6.5	12.5	8.8/4.4	1.15	24
MA0507A	3/4	1725	115/208-230	56C	TEFC	6.5	13.5	11.0/5.5	1.15	29
MA0510A	1	1725	115/208-230	56C	TEFC	6.5	13.5	13.6/6.8	1.15	37
MA0515A	1.5	1725	115/208-230	56C	TEFC	6.5	15.1	15.2/7.6	1.15	43
MA0520A	2	1725	115/208-230	56C	TEFC	6.5	15.1	20/10	1.15	48



HALLMARK INDUSTRIES, INC.